



Product Information

MONOCLONAL ANTI-FIBROBLAST GROWTH FACTOR-9 (FGF-9), CLONE FG9-77 Purified Mouse Immunoglobulin

Product Number **F1672**

Product Description

Monoclonal Anti-Fibroblast Growth Factor-9 (FGF-9) (mouse IgG1 isotype) is derived from the FG9-77 hybridoma produced by the fusion of mouse myeloma cells and splenocytes from an immunized mouse. A recombinant FGF-9 of murine origin was used as the immunogen. The isotype is determined using Sigma ImmunoType Kit (Sigma ISO-1) and by a double diffusion immunoassay using Mouse Monoclonal Antibody Isotyping Reagents (Sigma ISO-2). The product is provided as (protein A) purified and 0.2 μ m-filtered antibody, in 0.01M phosphate buffered saline, pH 7.4.

Monoclonal Anti-FGF-9 may be used for the localization of FGF-9 using various immunochemical assays such as ELISA, dot-blot and immunoblotting.

Fibroblast growth factors (FGFs) are members of a family of polypeptides that are potent regulators of cell proliferation, differentiation and function.¹⁻³ FGFs play crucial roles in normal development, maintenance of tissues and wound healing and repair. Also, they are implicated in a wide range of pathological conditions, including tumorigenesis and metastasis. FGFs exert their mitogenic influence via saturable high-affinity receptors on a wide variety of cell types of mesodermal and neuroectodermal origin, including endothelial cells, smooth muscle cells, fibroblasts, gliomas, chondrocytes, hepatocytes, epithelial cells and myoblasts. The FGF family consists of at least nine members (FGF-1 to FGF-9), with a 30-50% sequence identity at the amino acid level. All besides FGF-8 contain two conserved positions of two cysteine residues. FGF-9, also known as glia activating factor (GAF), was initially identified in the culture supernatant of a human glioma cell line as having the capability to promote glial cell proliferation.^{4,5} FGF-9 is a heparin binding molecule, which is a glycosylated single polypeptide of 208 amino acids (23-30 kD, depending on rate of glycosylation), with a 30% sequence similarity with other members of the FGF family.⁶ The molecule is conserved across species (rat FGF-9 is

94% identical to the human molecule). FGF-9 has a unique spectrum of activity on cells, and it acts on the central nervous system. Although it has a mitogenic effect on fibroblasts like other FGFs, FGF-9 has no effect on human umbilical vein endothelial cells. FGF-9 stimulates the proliferation of oligodendrocyte type 2 astrocyte progenitor cells, Balb/c 3T3 fibroblasts and rat pheochromocytoma cell line PC-12. Human FGF-9 is oncogenic when transfected into murine fibroblasts. Studies have identified FGF-9 expression in brain and kidney.⁵ FGF-9 binds specifically to FGF receptors 2 and 3, but not to FGF receptors 1 and 4.⁷ Like all other FGF ligands, FGF-9 requires heparin sulfate for high affinity receptor binding and biological activities.⁷ Since FGF-9 plays major roles in biological responses and pathological states, an in vitro assay for FGF-9 detection is desirable. Monoclonal antibodies reacting specifically with FGF-9 may be used in diverse cellular and molecular approaches to the study of fibroblast growth factors and their properties, and to correlate their expression pattern with physiological functions or pathological conditions.

Reagents

Monoclonal Anti-FGF-9 reacts specifically with recombinant FGF-9 (fibroblast growth factor 9). It does not cross-react with human FGF-Acidic and FGF-Basic. The product may be used for ELISA, dot-blot and immunoblotting (25 kD). Reactivity has been observed with human and mouse FGF-9.

Antibody Concentration: 2 mg/ml

Storage/Stability

For continuous use, store sterile at 2-8°C for up to one month. For extended storage freeze in sterile working aliquots. Repeated freezing and thawing is not recommended. Storage in "frost-free" freezers is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use.

Product Profile

A working concentration of at least 5 µg/ml is determined by dot-blot assay, using a recombinant FGF-9 preparation of human origin.

Note: In order to obtain best results in different techniques and preparations we recommend determining optimal working concentration by titration test.

References

1. Baird, A., et al., Recent Prog. Horm. Res., **42**, 143 (1986).
2. Gospodarowicz, D., Meth. Enzymol., **147**, 106 (1987).
3. Burgess, W.H., and Maciag, T., Annu. Rev. Biochem., **58**, 575 (1989).
4. Naruo, K., et al., J. Biol. Chem., **268**, 2857 (1993).
5. Miyamoto, M., et al., Mol. Cell. Biol., **13**, 4251 (1993).
6. Seo, M., et al., FEBS Lett., **370**, 231 (1995).
7. Hecht, D., et al., Growth Factors, **12**, 223 (1995).

lpg 4/98

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.