

Product Information

Monoclonal Anti-polyHistidine Peroxidase Conjugate Clone HIS-1

Catalog Number **A7058**

Product Description

Anti-polyHistidine (mouse IgG2a isotype) is derived from the HIS-1 hybridoma produced by the fusion of mouse myeloma cells and splenocytes from a mouse immunized with a polyhistidine-tagged fusion protein. The isotype is determined by double diffusion assay using Mouse Monoclonal Antibody Isotyping Reagents (Catalog Number ISO2). Monoclonal anti-polyHistidine, Peroxidase conjugate is prepared by conjugation of horseradish peroxidase to mouse monoclonal anti-polyHistidine purified from ascites fluid of the HIS-1 hybridoma.

Monoclonal anti-polyHistidine, Peroxidase conjugate, recognizes native as well as reduced, denatured forms of synthetic polyhistidine or polyhistidine-tagged fusion proteins. The product is reactive with fusion proteins expressed by prokaryotic pET, pRSET, and pTrc expression vectors. The antibody is reactive in immunoblotting, dot blot, and ELISA.

Recombinant DNA technology enables the attachment of genes of interest to specific sequences or genes that can provide 'affinity handles' (tags) designed to enable the selective identification of the protein of interest. The sequences of tails or tags are genetically engineered away from the protein active site, by insertion at the N- or C-terminus. It has been reported that the addition of a consecutive histidine amino acid residue tail creates a stable fusion product that does not appear to interfere with the bioactivity of the protein or with the biodistribution of the histidine tagged product.

Monoclonal antibody reacting specifically with poly-histidine may be useful in various immunotechniques, to identify the expression of a polyhistidine fusion protein in bacteria, bacterial lysates, or cells and tissues transfected with a polyhistidine-tagged fusion protein expressing vectors.

Reagent

Monoclonal anti-polyHistidine, Peroxidase conjugate is supplied as a lyophilized powder. After reconstitution the solution contains 1% BSA and 0.01% thimerosal in 0.01 M sodium phosphate buffered saline.

Antibody concentration: 5–11 mg/ml
Molar ratio Ab/Enzyme: 0.8–1.5
Enzyme activity: ≥400 units/ml

Preparation Instructions

Reconstitute the contents of the vial with 0.5 ml of water. This results in a solution of antibody conjugate in 0.01 M sodium phosphate buffered saline containing 1 % BSA and 0.01 % thimerosal.

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

Storage/Stability

Store the lyophilized product at 2–8 °C.

For extended storage after reconstitution with water, keep at –20 °C in working aliquots. Avoid repeated freeze-thaw cycles. Do not store in frost-free freezers. For continuous use after reconstitution, keep at 2–8 °C for up to 1 month. Solutions at working dilution should be discarded if not used within 12 hours.

Product Profile

Immunoblotting: a minimum working dilution of 1:2,000 is determined by using bacteria lysates expressing a recombinant histidine-tagged fusion protein.

Note: in order to obtain the best results using various techniques and preparations, we recommend determining optimal working dilutions by titration.

Procedure

Immunoblotting

All incubation steps should be performed at room temperature.

1. Separate the proteins present in sample lysates using a standard sodium dodecyl sulfate polyacrylamide gel electrophoresis (SDS-PAGE) protocol. Load 2.5–20 µg of total lysate protein per lane. The amount of lysate to be loaded per lane depends on the level of protein expression and may vary between experiments.
2. Transfer proteins from the gel to a nitrocellulose membrane.
3. Block the membrane using a solution of 5% non-fat dry milk in phosphate buffered saline (PBS, Catalog Number D8537) for at least 60 minutes.
4. Wash the membrane three times for 5 minutes each in PBS containing 0.05% TWEEN[®] 20 (Catalog Number P3563).

5. Incubate the membrane with Anti-polyHistidine, Peroxidase conjugate using an optimized concentration in PBS containing 0.05% TWEEN 20 and 1% bovine serum albumin (BSA, Catalog Number A9647) for two hours.
6. Wash the membrane three times for 5 minutes each in PBS containing 0.05% TWEEN 20.
7. Treat the membrane with a peroxidase substrate.

TWEEN is a registered trademark of Uniqema, a business unit of ICI Americas, Inc.

This product is covered by patent DE 19507166 and foreign equivalents exclusively licensed to QIAGEN GmbH, Qiagen Strasse 1, D-40724 Hilden, Germany

SC,SN,AC,MAM 8/08-1

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.