



Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE

Enzymatic Assay of **LYSOZYME**¹ (EC 3.2.1.17)

PRINCIPLE:

Micrococcus lysodeikticus Cells (Intact) $\xrightarrow{\text{Lysozyme}}$ Micrococcus lysodeikticus Cells (Lysed)

CONDITIONS: T = 25°C, pH = 6.24, $A_{450\text{nm}}$, Light path = 1 cm

METHOD: Turbidimetric Rate Determination

REAGENTS:

- A. 66 mM Potassium Phosphate Buffer, pH 6.24 at 25°C
(Prepare 100 ml in deionized water using Potassium Phosphate, Monobasic, Anhydrous, Sigma Prod. No. P-5379. Adjust to pH 6.24 at 25°C with 1 M KOH.)
- B. 0.015% (w/v) Micrococcus lysodeikticus Cell Suspension (Substrate)
(Prepare 25 ml in Reagent A using Micrococcus lysodeikticus, ATCC 4698 lyophilized cells, Sigma Prod. No. M-3770. The $A_{450\text{nm}}$ of this suspension should be between 0.6 and 0.7.)
- C. Lysozyme Enzyme Solution
(Immediately before use, prepare a solution containing 200 - 400 units/ml of lysozyme in cold Reagent A.)

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>Test</u>	<u>Blank</u>
Reagent B (Substrate)	2.50	2.50

Equilibrate to 25°C. Monitor the $A_{450\text{nm}}$ until constant, using a suitably thermostatted spectrophotometer. Then add:

Reagent C (Enzyme Solution)	0.10	-----
Reagent A (Buffer)	-----	0.10

Enzymatic Assay of LYSOZYME¹ (EC 3.2.1.17)

PROCEDURE: (continued)

Immediately mix by inversion and record the decrease in $A_{450\text{nm}}$ for approximately 5 minutes. Obtain the $\Delta A_{450\text{nm}}$ /minute using the maximum linear rate for both the Test and Blank.

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(\Delta A_{450\text{nm}}/\text{min Test} - \Delta A_{450\text{nm}}/\text{min Blank})(\text{df})}{(0.001)(0.1)}$$

df = Dilution factor

0.001 = Change in absorbance at $A_{450\text{nm}}$ as per the Unit Definition

0.1 = Volume (in milliliter) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will produce a $\Delta A_{450\text{nm}}$ of 0.001 per minute at pH 6.24 at 25°C using a suspension of *Micrococcus lysodeikticus* as substrate, in a 2.6 ml reaction mixture.

FINAL ASSAY CONCENTRATION:

In a 2.60 ml reaction mix, the final concentrations are 66 mM potassium phosphate, 0.014% (w/v) *Micrococcus lysodeikticus* cell suspension and 20 - 40 units lysozyme.

REFERENCE:

Shugar, D. (1952) *Biochimica et Biophysica Acta* **8**, 302-309

NOTES:

1. This assay procedure is not to be used to assay Lysozyme, Bovine Recombinant Expressed in *Pichia pastoris*, Sigma Prod. No. L-9772, Lysozyme, Human, Recombinant Expressed in *Pichia pastoris*, Sigma Prod. No. L-2026, and Lysozyme Insoluble Enzyme on Agarose, Sigma Prod. No. L-1129.

Enzymatic Assay of LYSOZYME¹
(EC 3.2.1.17)

NOTES: (continued)

2. This assay is based on the cited reference.
3. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.