



Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE

Enzymatic Assay of PEPSIN (EC 3.4.23.1)

PRINCIPLE:

Hemoglobin + H₂O $\xrightarrow{\text{Pepsin}}$ TCA-Soluble Peptides

CONDITIONS: T = 37°C, pH = 2.0, A_{280nm}, Light path = 1 cm

METHOD: Spectrophotometric Stop Rate Determination

REAGENTS:

- A. 10 mM Hydrochloric Acid Solution (Enzyme Diluent)
(Prepare 100 ml in deionized water using Hydrochloric Acid, Sigma Prod. No. H-7020.)
- B. 300 mM Hydrochloric Acid Solution
(Prepare 100 ml in deionized water using Hydrochloric Acid, Sigma Prod. No. H-7020.)
- C. 2.5% (w/v) Hemoglobin Solution
(Prepare 100 ml in deionized water using Hemoglobin, Bovine, Sigma Prod. No. H-2625. Mix vigorously and filter through a glass wool filter.)
- D. 2.0% (w/v) Hemoglobin Substrate Solution (Hb)
(Prepare by adding 20 ml of Reagent B to 80 ml of Reagent C.)
- E. 5% (w/v) Trichloroacetic Acid Solution (TCA)
(Prepare 100 ml in deionized water using Trichloroacetic Acid Solution, 6.1 N, approximately 100% (w/v), Sigma Stock. No. 490-10.)
- F. Pepsin Enzyme Solution
(Immediately before use, prepare a solution containing 0.01 - 0.05 mg/ml of Pepsin in cold Reagent A.)

**Enzymatic Assay of PEPSIN
(EC 3.4.23.1)**

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable containers:

	<u>Test</u>	<u>Blank</u>
Reagent D (Hb)	5.00	5.00

Equilibrate at 37°C. Then add:

Reagent F (Enzyme Solution)	1.00	-----
-----------------------------	------	-------

Mix by swirling and incubate at 37°C for exactly 10 minutes. Then add:

Reagent E (TCA)	10.00	10.00
Reagent F (Enzyme Solution)	-----	1.00

Mix by swirling and incubate at 37°C for 5 minutes. Filter the solutions through a Whatman #50 filter or a 0.8 µm syringe filter. Transfer the solutions to suitable quartz cuvettes and record the A_{280nm} for both the Test and Blank.

CALCULATION:

$$\text{Units/ml enzyme} = \frac{(A_{280nm} \text{ Test} - A_{280nm} \text{ Blank}) (df)}{(0.001) (10) (1)}$$

df = Dilution factor

0.001 = Change in Absorbance at 280 nm per unit of Pepsin (Unit Definition)

10 = Time of assay (in minutes) as per the Unit Definition

1 = Volume (in milliliter) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will produce a ΔA_{280nm} of 0.001 per minute at pH 2.0 at 37°C measured as TCA-soluble products using hemoglobin as substrate. (Final volume = 16 ml. Light path = 1 cm.)

**Enzymatic Assay of PEPSIN
(EC 3.4.23.1)**

FINAL ASSAY CONCENTRATION:

In a 6.00 ml reaction mix, the final concentrations are 52 mM hydrochloric acid, 1.7% (w/v) hemoglobin and 0.01 - 0.05 mg pepsin.

REFERENCE:

Anson, M.L. (1938) *Journal of General Physiology* **22**, 79-89

NOTE:

1. This assay is based on the cited reference.
2. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.