

## ProductInformation

### MICROWAVE TISSUE FIXATION QUALITY CONTROL CHART

#### **H2100 MICROWAVE PROCESSOR** **10% Neutral Buffered Formalin Procedure**

Date\_\_\_\_\_

Technician\_\_\_\_\_

Step	Reagent	Power	Time	Temperature	Record
2	10% Neutral Buffered Formalin	800 watts	1 minute	40 - 50 °C	
5	10% Neutral Buffered Formalin	100 watts	15 minutes	40 - 60 °C	
7	10% Neutral Buffered Formalin	100 watts	15 minutes	40 - 60 °C	
9	10% Neutral Buffered Formalin	100 watts	15 minutes	40 - 60 °C	
11	10% Neutral Buffered Formalin	100 watts	15 minutes	40 - 60 °C	
13	10% Neutral Buffered Formalin	100 watts	15 minutes	40 - 60 °C	
15	10% Neutral Buffered Formalin	100 watts	15 minutes	40 - 60 °C	

Critical Points: