

ProductInformation

MICROWAVE TISSUE PROCESSING QUALITY CONTROL CHART **H2100 MICROWAVE PROCESSOR**

Biopsy Procedure

Date _____

Technician _____

Step	Reagent	Power	Time	Temperature	Record
2	Reagent Alcohol	800 watts	1 minute	60 - 70 °C	
5	Reagent Alcohol	100 watts	5 minutes	63 - 70 °C	
6	Reagent Alcohol	100-150 watts	4 minutes	63 - 70 °C	
7	Fresh Reagent Alcohol	800 watts	1 minute	60 - 70 °C	
10	Reagent Alcohol	100 watts	5 minutes	63 - 70 °C	
11	Reagent Alcohol	100-150 watts	4 minutes	63 - 70 °C	
12	Isopropyl Alcohol	800 watts	1 minute	60 - 70 °C	
15	Isopropyl Alcohol	100 watts	5 minutes	74 - 80 °C	
16	Isopropyl Alcohol	100 -150 watts	4 minutes	74 - 80 °C	
17	Fresh Isopropyl Alcohol	800 watts	1 minute	60 - 70 °C	
20	Isopropyl Alcohol	100 watts	5 minutes	74 - 80 °C	
21	Isopropyl Alcohol	100 -150 watts	4 minutes	74 - 80 °C	
22	Paraffin	N/A	N/A	approx. 70 °C	
23	Paraffin	400 watts	10 minutes	68 - 72 °C	
24	Paraffin	500 watts	10 minutes	70 - 78 °C	
25	Paraffin	400 watts	10 minutes	80 - 88 °C	

Critical Points: