



**SIGMA-ALDRICH**

3050 Spruce Street  
Saint Louis, Missouri 63103 USA  
Telephone 800-325-5832 • (314) 771-5765  
Fax (314) 286-7828  
email: techserv@sial.com  
sigma-aldrich.com

## Product Information

### 5-BROMO-4-CHLORO-3-INDOLYL β-D-GALACTOPYRANOSIDE

Product Number **B4252, B9146, B6024**

Storage Temperature  $-20^{\circ}\text{C}$

Cas #: 7240-90-6

Synonyms: X-Gal

#### Product Description

5-Bromo-4-chloro-3-indolyl β-D-galactopyranoside, commonly known as X-Gal, is a histochemical substrate for β-galactosidase.<sup>1</sup> X-Gal is cleaved by β-galactosidase to yield an insoluble blue precipitate.<sup>1</sup> X-Gal is particularly useful in molecular biology applications to detect the activity of β-galactosidase which is frequently used as a reporter gene.<sup>2,3,4</sup> In cloning, X-Gal is used to detect insertion of foreign DNA into the lacZ region of plasmid DNA using α-complementation which is based on vectors such as the pUC and the M13mp series that carry a fragment of the β-galactosidase gene encoding an α-fragment of β-galactosidase.<sup>5</sup> Insertion of DNA into the lacZ region results in the loss of β-galactosidase activity. Lac<sup>+</sup> bacterial colonies resulting from α-complementation will appear blue whereas bacterial colonies containing plasmid with DNA inserted in the lacZ region, will be incapable of α-complementation and will appear white.<sup>5</sup>

Many other applications also use X-Gal as a substrate to detect β-galactosidase activity. These include β-galactosidase-antibody linked immunoassays and immunohistochemistry,<sup>6-9</sup> coliphage detection based on β-galactosidase induction,<sup>10</sup> and the detection of micrometastasis formation during tumor progression.<sup>4</sup>

X-gal is available in several forms (see also the related products section). Products B4252 and B9146 are in powder form and product B6024 is in tablet form (5 mg substrate per tablet). The Molecular Biology Reagent products, B9146 and B6024 are quality control tested for identification of lac<sup>+</sup> bacterial colonies.

Appearance:	White to white with a yellow cast powder or tablet
Molecular Formula:	$\text{C}_{14}\text{H}_{15}\text{BrClNO}_6$
Molecular Weight:	408.6
Purity:	≥98% by TLC

#### Precautions and Disclaimer

X-Gal is for laboratory use only; not for drug, household or other uses. Please refer to the Material Safety Data Sheet (MSDS).

#### Storage/Stability

Stored at  $-20^{\circ}\text{C}$  protected from light X-Gal powder can have a three year shelf life.<sup>11</sup>

#### Preparation Instructions

Prepare a 20 mg/ml stock solution of X-Gal in N,N-dimethylformamide (DMF) or dimethylsulfoxide (DMSO).<sup>12,13</sup> Sterilization is not required.<sup>3</sup> Store stock solution in glass container protected from light at  $-20^{\circ}\text{C}$ . Solutions may be stored at  $-20^{\circ}\text{C}$  for 6-12 months. If a solution turns pink, it should be discarded.<sup>11</sup>

#### Procedures

##### Blue/White Colony Screening

- X-Gal included in agar: Add 5 ml of X-Gal stock solution and 5 ml of 0.1 M isopropyl-β-D-thiogalactoside (IPTG, Product No. I6758) for each 1 liter of autoclaved media agar (e.g. LB agar, L2897) containing appropriate antibiotics just prior to pouring.<sup>14</sup> The media should be below  $55^{\circ}\text{C}$ . Plate cells on cooled agar and incubate overnight at  $37^{\circ}\text{C}$ .
- X-Gal applied to top of agar: To a premade LB agar plate (e.g. prepared using LB agar, L2897), add 40 μl of X-Gal stock solution (at room temperature) and 4 μl of a 200 mg/ml solution of IPTG.<sup>5</sup> Spread solution over the entire surface of the plate. Incubate at  $37^{\circ}\text{C}$  until the the fluid is no longer visible. This may take several hours. Plate cells and incubate overnight at  $37^{\circ}\text{C}$ . Using X-Gal only on the surface rather than throughout the agar plates may help minimize costs.<sup>5</sup>

##### Immunocytochemistry<sup>2,3,4,9</sup>

Prepare X-Gal Stain: 100 mM sodium phosphate, pH 7.3 (77 mM  $\text{Na}_2\text{HPO}_4$ , 23 mM  $\text{NaH}_2\text{PO}_4$ ), 1.3 mM  $\text{MgCl}_2$ , 3 mM potassium ferricyanide ( $\text{K}_3\text{Fe}[\text{CN}]_6$ ), 3 mM

potassium ferrocyanide ( $K_4Fe(CN)_6$ ), 1 mg/ml X-Gal. Filter through 0.45  $\mu$ m membrane prior to use. Overlay fixed cells with X-Gal stain. Place in a humidified incubator at 37°C and monitor for blue color development (from 30 minutes to overnight). As a matter of preference, the concentrations of potassium ferricyanide and potassium ferrocyanide may be as high as 35 mM. At higher concentrations the indole precipitation occurs more quickly and helps to reduce diffusion; however, these concentrations may cause a greenish background upon prolonged incubation in some tissues.<sup>3</sup> A recent publication suggests that using X-Gal solutions at pH greater than 7.5 can help to eliminate endogenous mammalian  $\beta$ -galactosidase activity.<sup>15</sup>

## References

- Horwitz, J. Substrates for Cytochemical Demonstration of Enzyme Activity. I. Some Substituted 3-Indolyl- $\beta$ -D-glycopyranosides. *J. Med. Chem.*, **7**, 574-575 (1964).
- MacGregor, G.R. et al. Use of *E. coli lacZ* ( $\beta$ -Galactosidase) as a Reporter Gene, in Methods in Molecular Biology, Volume 7: Gene Transfer and Expression Protocols, Murray, E.J. (ed.), The Humana Press Inc., NJ, 1991, Chapter 17, p.217-235.
- Ausubel, F.M. et al., Eds., Short Protocols in Molecular Biology, Fourth Edition, John Wiley & Sons, Inc., p. A1-45, 1999 (Product No. Z36,436-3).
- Lin W.C. et al., Bacterial *lacZ* gene as a highly sensitive marker to detect micrometastasis formation during tumor progression. *Cancer Res.*, **50**, 2808-2817 (1990).
- Sambrook, J., and Russell, D. W., Molecular Cloning: A Laboratory Manual, Third Edition, p. 1.123-1.125, 1.149-1.150 A 1.29, Cold Spring Harbor Laboratory (2001) (Product No. M8265).
- Holzmann B. and Johnson J.P., A beta-galactosidase linked immunoassay for the analysis of antigens on individual cells. *J. Immunol. Meth.*, **60**, 359-367 (1983).
- Gugliotta P. et al., Staining reaction for beta-galactosidase in immunocytochemistry and in situ hybridization. *Eur. J. Histochem.*, **36**, 143-148 (1992).
- Rosenberg W.S. et al., Authentic and artifactual detection of the *E. coli lacZ* gene product in the rat brain by histochemical methods. *Mol. Brain Res.*, **16**, 311-315 (1992).
- Lund-Hansen T. et al., A quantitative cytochemical assay of beta-galactosidase in single cultured human skin fibroblasts. *Histochemistry*, **81**, 321-330 (1984).
- Ijzerman M.M. and Hagedorn C., Improved method for coliphage detection based on beta-galactosidase induction. *J. Virol. Meth.*, **40**, 31-36 (1992).
- Sigma Chemical Co. data.
- Karlinsey, J. E., and Hughes, K.T. A Convenient and Safe Method for Storing X-Gal Solutions, *BioTechniques*, **15**(2),292 (1993).
- Edwards, M.J., and Taylor, M.F. Substitution of DMSO for DMF as a Solvent for X-Gal. *BioTechniques*, **14**(2), 234 (1993).
- Davis, L.G. et al. Basic Methods in Molecular Biology, Elsevier Science, NY, p. 335 (1986).
- Weiss D.J. et al., Histochemical discrimination of endogenous mammalian beta-galactosidase activity from that resulting from *lac-Z* gene expression. *Histochem. J.*, **31**(4), 231-236 (1999).

## Related Products

- GAL-S**,  $\beta$ -Galactosidase reporter gene staining kit, X-Gal based
- N1127**, o-Nitrophenyl  $\beta$ -D-galactopyranoside (ONPG), soluble substrate for  $\beta$ -galactosidase
- GAL-A**,  $\beta$ -Galactosidase reporter gene activity detection kit, ONPG based
- M1633**, 4-Methylumbelliferyl  $\beta$ -D-galactopyranoside (MUGal), fluorescent substrate for beta-galactosidase
- GAL-F**,  $\beta$ -Galactosidase fluorescence activity detection kit, MUGal based
- B3928**, Blue-White Select screening reagent, ready-to-use IPTG and X-Gal solution in DMSO

03/01

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.