

Product Information

Mer EXTRACELLULAR DOMAIN/Fc CHIMERA

Human, Recombinant
Expressed in Sf21 insect cells

Product Number **M 1314**

Product Description

Recombinant human Mer extracellular domain/Fc chimera consists of amino acid residues 1 - 499¹ that was fused by means of a polypeptide linker to the C-terminal Fc portion of human IgG1. The chimeric protein is expressed in baculovirus infected Sf21 insect cells. Recombinant Mer is a disulfide-linked homodimer. The amino terminus is Arg 26 based on N-terminal sequencing. The calculated molecular mass of the reduced monomer is approximately 78.9 kDa, but as a result of glycosylation, it migrates as an approx. 100-110 kDa protein on reducing SDS-PAGE.

Mer, along with Axl and Dtk, is a member of the receptor tyrosine kinase family.^{2,3} The Mer extracellular domain is composed of two Ig-like motifs and two fibronectin type III motifs.^{1,4} The known ligands are Protein S and Gas6 (growth-arrest specific protein).²⁻⁶ Protein S is an anti-coagulation factor and also plays a role in mitogenesis.³ The binding affinity for Gas6 is in the order of Axl>Dtk>Mer. Mer and its ligand Gas6 induce downstream signaling pathways that affect cell proliferation, migration, and prevent apoptosis. They may also be involved in the immune, reproductive, and vascular systems.³⁻⁷ Mer is expressed at high levels in epithelial and reproductive tissues as well as in monocytes. Over-expression is associated with lymphoid malignancies.⁷

Reagent

Recombinant human extracellular Mer/Fc chimera is supplied as approx. 100 µg of protein lyophilized from a sterile filtered phosphate-buffered saline (PBS) solution.

Preparation Instructions

Reconstitute the vial contents with sterile PBS containing at least 0.1% human or bovine serum albumin. Stock solution concentration should be no less than 50 µg/ml.

Storage/Stability

Lyophilized samples are stable for more than six months at -20 °C to -70 °C. Upon reconstitution, store at 2-4 °C for up to one month. Store in working aliquots at -20 °C for up to three months. Repeated freeze-thaw cycles should be avoided. Do not store in a frost-free freezer.

Product Profile

Human Mer/Fc chimera activity is measured by its ability to bind rhGas6 in a functional ELISA assay. Immobilized human Mer/Fc chimera (10 µg/ml, 100 µl/well) binds recombinant human Gas6 with a linear range of 100-5 ng/ml. Optimal dilutions should be determined by each laboratory for each application.

Purity: >90% by SDS-PAGE, visualized by silver stain.
Endotoxin level: < 0.1 ng/µg of protein as determined by the LAL (Limulus amoebocyte lysate) method.

References

1. Graham, D. K. et al., Cloning and mRNA expression analysis of a novel human proto-oncogene, c-met. *Cell Growth Differ.*, **5**, 647- 657 (1994).
2. Crosier, K.E. and Crosier, P.S., New insights into the control of cell growth; the role of the Axl family. *Pathology*, **29**, 131-135 (1997).
3. Lu, Q. and Lemke, G., Homeostatic regulation of the immune system by receptor tyrosine kinase of the Tyro 3 family., *Science*, **293**, 306-311 (2001).
4. Prieto, A.L., et al., Expression of the receptor protein-tyrosine kinases Tyro-3, Axl, and Mer in the developing rat central nervous system. *J. Comp. Neurol.*, **425**, 295-314 (2000).

5. Chen, J., et al., Identification of Gas6 as a ligand for Mer, a neural cell adhesion molecule related receptor tyrosine kinase implicated in cellular transformation., *Oncogene*, **14**, 2033-2039 (1997).
6. Nagata, K., et al., Identification of the product of growth arrest-specific gene 6 as a common ligand for Axl, Sky, and Mer receptor tyrosine kinases., *J. Biol. Chem.*, **271**, 30022-30027 (1996).
7. Scott, R.S., et al., Phagocytosis and clearance of apoptotic cells is mediated by Mer., *Nature*, **411**, 207-211 (2001).

LCM 10/01

Sigma brand products are sold through Sigma-Aldrich, Inc.
Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.