

Affinity Chromatography

	Product Code	Size
Activated/Functionalized Matrices		
Aminoethyl Agarose	A 5224	10 ml, 100 ml
Glyoxal Agarose	G 6167	10 ml, 100 ml
Activated CH-Sepharose 4B	A 9019	5 g, 15 g
Activated Thiol-Sepharose 4B	T 8512	1 g, 5 g
Adipic acid dihydrazide Agarose	A 0802	10 ml, 50 ml
ω -Aminohexyl Agarose	A 2419	50 ml
ω -Aminooctyl Agarose	A 5642	10 ml, 100 ml
Cyanogen bromide-activated-Agarose	C 9210	1 g, 5 g, 15 g
Epichlorohydrin Agarose	E 5142	1 g, 5 g
Epoxyactivated Agarose	E 6754	5 g, 15 g
N-Hydroxysuccinimidyl-Agarose	H 8280	1 ml, 5 ml, 15 ml
p-Nitrophenyl chloroformate-activated Agarose	N 7759	10 ml, 50 ml
Periodate-activated Agarose	P 9967	5 ml, 50 ml
Thiopropyl-activated Agarose	T 5024	5 ml
Vinylsulfone-activated Agarose	V 2755	2 g, 10 g
Amino Acid Resins		
L-Arginine Agarose	A 1018	5 ml, 25 ml
L-Lysine Agarose	L 6132	1 g, 5 g, 15 g
O-Phospho-L-Serine Agarose	P 3578	1 g
O-Phospho-L-Tyrosine Agarose	P 8438	1 g, 5 g
Poly-L-Lysine Agarose	P 6893	5 ml, 50 ml
L-Threonine Agarose	T 0387	5 ml
Avidin Biotin Matrices		
Avidin Agarose	A 9207	1 ml, 5 ml, 15 ml
Avidin (Monomeric) Agarose	A 2036	1 ml, 5 ml
Avidin acrylic beads	A 4808	50 units, 100 units
Biotin Agarose	B 0519	5 ml, 25 ml
2-Iminobiotin-Agarose	I 4507	1 ml, 5 ml
Streptavidin-Agarose	S 1638	1 ml, 5 ml
EZView Red Streptavidin Affinity Gel	E 5529	1 ml, 5 x 1 ml, 5 ml
SigmaScreen Streptavidin High Capacity Coated Plates	S 6940	1 each, 5 x 1 each
Carbohydrate Binding Resins		
Concanavalin A Agarose	C 7555	5 ml, 25 ml, 100 ml
Lectin-Agarose <i>Arachis hypogaea</i> (peanut)	L 2507	1 ml, 2 ml
Lectin-Agarose <i>Artocarpus integrifolia</i> (Jacalin)	L 5147	2 ml, 5 ml
Lectin-Agarose <i>Galanthus nivalis</i> (snowdrop)	L 8775	2 ml
Lectin-Agarose <i>Helix pomatia</i>	L 8639	1 ml, 5 ml
Lectin-Agarose <i>Lens culinai</i> s (lentil)	L 4018	1 ml, 5 ml
Lectin-Agarose <i>Triticum vulgari</i> s	L 1882	1 ml, 5 ml

CHROMATOGRAPHY

Affinity Chromatography continued

	Product Code	Size
Carbohydrate Resins		
N-Acetyl-D-galactosamine-Agarose	A 2787	5 ml, 25 ml
N-Acetyl-D-glucosamine-Agarose	A 2278	1 ml, 5 ml, 25 ml
p-Aminobenzyl 1-thio-β-D-galactopyranoside-Agarose	A 0414	5 ml, 10 ml, 25 ml
p-Aminophenyl β-D-thiogalactopyranoside-Agarose	A 8648	5 ml, 25 ml
α-Lactose-Agarose	L 7634	1 ml, 5 ml, 25 ml
Maltoheptaose-Agarose	M 9676	5 ml, 25 ml
Maltose-Agarose	M 8896	5 ml
Mannan-Agarose	M 9917	5 ml, 25 ml
D-Manose Agarose	M 6400	5 ml, 10 ml, 25 ml
Chelating Resins		
Chelex 100 sodium form	C 7901	25 g, 50 g, 100 g
Tris(carboxymethyl)ethylenediamine-Agarose	C 4280	1 g
Iminodiacetic acid Agarose	I 4758	5 ml, 25 ml, 50 ml
Dye Resins		
Blue dextran-Agarose	B 3760	5 ml, 25 ml
Cibacron Blue 3GA Agarose	C 1535	5 ml, 50 ml, 100 ml
Reactive Blue 4-Agarose	R 2507	5 ml, 25 ml
Reactive Green 19-Agarose	R 2882	25 ml, 100 ml
Reactive Red 120-Agarose	R 6143	10 ml, 50 ml
Reactive Yellow 3-Agarose	R 3757	10 ml, 25 ml, 100 ml
Hydrophobic Interactions		
Butyl-Agarose	B 8645	10 ml, 50 ml
Phenyl-Agarose	P 8901	50 ml, 100 ml
Octyl-Agarose	O 6127	10 ml, 50 ml
Immunoaffinity Resins		
Monoclonal Anti-Biotin-Agarose	A 1559	0.5 ml
Anti-GST-Agarose	A 8580	1 ml
Monoclonal Anti-Phosphoserine-Agarose	A 8076	0.5 ml, 1 ml
Monoclonal Anti-Phosphothreonine-Agarose	A 7951	0.5 ml, 1 ml
Monoclonal Anti-Phosphotyrosine-Agarose	A 4720	0.5 ml
Anti-BSA-Agarose	A 4338	1 ml
Anti-Mouse IgG Agarose	A 6531	2 ml, 5 ml, 25 ml
Protein A Agarose	P 2545	1 ml, 5 ml
EZView Red Protein A Affinity Gel	P 6486	1 ml, 5 x 1 ml
Protein G Agarose	P 7700	100 mg, 250 mg, 1 g
Protein L-Agarose	P 3351	5 ml
Specialty Resins		
Deoxyribonucleic Acid-Cellulose Single-stranded	D 8273	1 g, 5 g, 10 g
Gelatin-Agarose	G 5384	5 ml, 10 ml, 25 ml
Glutathione Agarose	G 4510	1 ml, 5 ml, 10 ml
Heparin Agarose	H 6508	5 ml, 25 ml, 100 ml
Methotrexate-Agarose	M 0269	10 ml, 25 ml
Pepstatin A-Agarose	P 2032	5 ml, 10 ml, 25 ml
Polymyxin B-Agarose	P 1411	5 ml, 10 ml
Trypsin Inhibitor Agarose	I 0637	5 ml, 10 ml, 25 ml
Ubiquitin-Agarose	U 5632	1 ml