

# Product Information

## Hanks' Balanced Salt Solution

HBSS Modified, with phenol red, without calcium, without magnesium

CATALOG NO. 55021

### Description

Hanks' Balanced Salt Solution (HBSS) is designed for use with cells maintained in non-CO<sub>2</sub> atmospheric conditions. For cell dissociation procedures, use HBSS Modified, which is formulated without calcium and magnesium salts.

### Formulation

Component (all components measured in mg/L)	
<b>INORGANIC SALTS</b>	
Potassium chloride	400.000
Potassium phosphate monobasic anhydrous	60.000
Sodium bicarbonate	350.000
Sodium chloride	8000.000
Sodium phosphate dibasic heptahydrate	90.000
<b>OTHER</b>	
Dextrose anhydrous	1000.000
Phenol red sodium salt	10.620

### Precautions

Use aseptic technique when handling or supplementing this buffer after filtration. This product is for further manufacturing use. THIS PRODUCT IS NOT INTENDED FOR HUMAN OR THERAPEUTIC USE.

### Storage

Store medium at 15 to 30 C. Do not use after the expiration date.

### Indications of Deterioration

Buffer should be clear of particulates and flocculent material. Do not use if liquid buffer is cloudy or contains precipitate. Other evidence of deterioration may include color change or degradation of physical or performance characteristics.

### Preparation Instructions

Supplements, such as antibiotics, can be added to the sterilized solution using aseptic technique. Storage conditions and shelf life of the supplemented product may be affected by the nature of the supplements.

### Characteristics

#### Appearance

Clear red solution

#### Endotoxin (LAL)

≤ 1.0 EU/mL

#### Osmolality (as supplied)

260 - 300 mOsm/kg H<sub>2</sub>O

#### pH (as supplied)

7.0 - 7.4

#### Sterility

No microbial growth detected

### References

- Hanks, J. H. and Wallace, R. E., *PSEBM* (1949) 71:196.

#### United States

SAFC Biosciences  
13804 W. 107th Street  
Lenexa, Kansas 66215  
USA  
Phone +1 913-469-5580  
Toll free-USA 1 800-255-6032  
Fax +1 913-469-5584

#### Europe

SAFC Biosciences  
Smeaton Road, West Portway  
Andover, Hampshire SP10 3LF  
UNITED KINGDOM  
Phone +44 (0)1264-333311  
Fax +44 (0)1264-332412

#### Asia Pacific

SAFC Biosciences  
18-20 Export Drive  
Brooklyn, Victoria 3025  
AUSTRALIA  
Phone +61 (0)3-9362-4500  
Toll free-AUS 1 800-200-404  
Fax +61 (0)3-9315-1656

**Warranty, Limitation of Remedies**

SAFC Biosciences warrants to the purchaser for a period of one year from date of delivery that this product conforms to its specifications. Other terms and conditions of this warranty are contained in SAFC Biosciences' written warranty, a copy of which is available upon request. ALL OTHER WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING THE IMPLIED WARRANTY OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE EXCLUDED. In no case will SAFC Biosciences be liable for any special, incidental, or consequential damages arising out of this product or the use of this product by the customer or any third party based upon breach of warranty, breach of contract, negligence, strict tort, or any other legal theory. SAFC Biosciences expressly disclaims any warranty against claims by any third party by way of infringement or the like. THIS PRODUCT IS INTENDED FOR PURPOSES DESCRIBED ONLY AND IS NOT INTENDED FOR ANY HUMAN OR THERAPEUTIC USE.

Additional Terms and Conditions are contained in the product Catalog, a copy of which is available upon request.

© 2005 SAFC Biosciences

Issued October 2005 XP55021  
0103 0905

---

**www.safcbiosciences.com**

**United States**

SAFC Biosciences  
13804 W. 107th Street  
Lenexa, Kansas 66215  
USA  
Phone +1 913-469-5580  
Toll free-USA 1 800-255-6032  
Fax +1 913-469-5584

**Europe**

SAFC Biosciences  
Smeaton Road, West Portway  
Andover, Hampshire SP10 3LF  
UNITED KINGDOM  
Phone +44 (0)1264-333311  
Fax +44 (0)1264-332412

**Asia Pacific**

SAFC Biosciences  
18-20 Export Drive  
Brooklyn, Victoria 3025  
AUSTRALIA  
Phone +61 (0)3-9362-4500  
Toll free-AUS 1 800-200-404  
Fax +61 (0)3-9315-1656