

# Product Information

sigma-aldrich.com

3050 Spruce Street, Saint Louis, MO 63103 USA  
Tel: (800) 521-8956 (314) 771-5765 Fax: (800) 325-5052 (314) 771-5757  
email: techservice@sial.com sigma-aldrich.com

## Deoxyribonuclease I from bovine pancreas

Catalog Number **D4263**

Storage Temperature  $-20\text{ }^{\circ}\text{C}$

CAS RN 9003-98-9

EC 3.1.21.1

Synonyms: DNase I; Deoxyribonuclease

5'-Oligonucleotidohydrolase

### Product Description

DNase I is found in most cells and tissues. In mammals the pancreas is one of the best sources for the enzyme. Pancreatic DNase I was the first DNase isolated.

DNase I is an endonuclease that acts on phosphodiester bonds adjacent to pyrimidines to produce polynucleotides with terminal 5'-phosphates. A tetranucleotide is the smallest average digestion product. In the presence of  $\text{Mg}^{2+}$  ions, DNase I attacks each strand of DNA independently and the cleavage sites are random. If  $\text{Mn}^{2+}$  ions are present, both DNA strands are cleaved at approximately the same site.<sup>1</sup> DNase I hydrolyzes single and double-stranded DNA and chromatin (reaction rate is restricted by DNA association with histones).

DNase I is used to remove DNA from protein and nucleic acid samples, and to nick DNA as a first step to incorporate labeled bases into DNA.

Bovine pancreatic DNase consists four chromatographically distinguishable components, A, B, C, and D.<sup>2</sup> The molar ratios of A:B:C in a pancreatic extract are 4:1:1. Only minor amounts of D are found. Forms A and B differ in carbohydrate content. Form C differs from forms A and B by having one less histidine and one more proline, and in the carbohydrate chain.<sup>4</sup>

Molecular mass: 30,072 Da (peptide, calculated), exists as a mixture of glycoproteins with two disulfide bridges.<sup>3</sup>

Carbohydrate Content:<sup>2</sup>

Form:	<u>A</u>	<u>B</u>	<u>C</u>
N-Acetylglucosamine	2	3	2
Mannose	6	5	5
Sialic Acid	—	1	—
Galactose	—	1	—

Isoelectric points:<sup>2</sup> A: 5.22; B: 4.96; C: 5.06; D: 4.78

Optimal pH: 7–8

Extinction Coefficient:  $E_{280}^{1\%} = 11.1$

Activators:

DNase I has an absolute requirement for divalent metal cations. The most commonly used is  $\text{Mg}^{2+}$ ;<sup>5</sup> however,  $\text{Mn}^{2+}$ ,  $\text{Ca}^{2+}$ ,  $\text{Co}^{2+}$ , and  $\text{Zn}^{2+}$  will activate DNase I.<sup>5,6</sup> A concentration of 5 mM  $\text{Ca}^{+2}$  will stabilize DNase I against proteolytic digestion; 0.1 mM is needed to reduce the rate of inactivation by one-half.<sup>7</sup>

Inhibitors:

2-Mercaptoethanol (the reduced enzyme is inactive, but can be reactivated in the presence of  $\text{Ca}^{2+}$  or  $\text{Mg}^{2+}$  ions),<sup>6</sup> chelators; sodium dodecyl sulfate (SDS),<sup>8</sup> and actin.<sup>9</sup> There is no general inhibitor specific for DNase I.<sup>5</sup> Citrate inhibits  $\text{Mg}^{2+}$ -activated DNase I, but not  $\text{Mn}^{2+}$ -activated DNase I.

This product is chromatographically purified from New Zealand source bovine pancreas. The purification procedure is not selective for any form (A, B, C, or D) of DNase I. It is supplied as a lyophilized powder, containing  $\text{CaCl}_2$ .

Vial content: ~2,000 Kunitz units/vial  
 $\geq 0.5$  mg protein (biuret)/vial

Unit definition: One Kunitz unit will produce a change in  $A_{260}$  of 0.001 per minute per ml at pH 5.0 at  $25\text{ }^{\circ}\text{C}$  using DNA, Type I or III, as the substrate. This enzyme assay reaction is performed in 83 mM acetate buffer, pH 5.0, at  $25\text{ }^{\circ}\text{C}$ , containing 4.2 mM  $\text{Mg}^{2+}$ , in a 3 ml reaction.

### Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

### Preparation Instructions

This enzyme is soluble in 0.15 M NaCl (5 mg/ml), yielding a clear solution.

### Storage/Stability

DNase I retains activity for at least three years when stored at -20 °C.

Solutions of DNase I (10 mg/ml) in 0.15 M NaCl may lose <10% of its activity stored for a week in aliquots at -20 °C. The same solutions stored in aliquots at 2-8 °C can lose ~20% activity.

DNase I remains active in solution between pH 5 and 7 up to 60 °C for at least five hours. A 1 mg/ml solution in acetate buffer (pH 5.0) or Tris buffer (pH 7.2) loses activity at the rate of 6%/hour. At 68 °C DNase I loses activity in <10 minutes.

### References

1. Sambrook, J., and Russell, D.W., Molecular Cloning: A Laboratory Manual, 2<sup>nd</sup> Ed., Cold Spring Harbor Laboratory Press, (Cold Spring Harbor, NY: 2001), Vol. 2, p. 5.83.
2. Kim, H.S., and Liao, T.-H., Isoelectric focusing of multiple forms of DNase in thin layers of polyacrylamide gel and detection of enzymatic activity with a zymogram method following separation. *Anal. Biochem.*, **119**, 96-101(1982).
3. Liao, T.-H., *et al.*, Bovine pancreatic deoxyribonuclease A. Isolation of cyanogen bromide peptides; complete covalent structure of the polypeptide chain. *J. Biol. Chem.*, **248**, 1489-1495 (1973).
4. Salnikow, J., *et al.*, Comparison of the multiple forms of bovine pancreatic deoxyribonuclease. *J. Biol. Chem.*, **245**, 5685-5690 (1970).
5. Weir, A. F., in *Enzymes of Molecular Biology*, Vol. 16 of *Methods in Molecular Biology*, Burrell, M.M., ed., Humana Press, (Totowa, NJ: 1993), Ch. 2, 2-16
6. Price, P.A., *et al.*, Effect of divalent cations on the reduction and re-formation of the disulfide bonds of deoxyribonuclease. *J. Biol. Chem.*, **244**, 929-932 (1969).
7. Price, P.A., *et al.*, Properties of chromatographically purified bovine pancreatic deoxyribonuclease. *J. Biol. Chem.*, **244**, 917-923 (1969).
8. Liao, T.-H., Reversible inactivation of pancreatic deoxyribonuclease A by sodium dodecyl sulfate. Removal of COOH-terminal residues from the denatured protein by carboxypeptidase A. *J. Biol. Chem.*, **250**, 3831-3836 (1975).
9. Lazarides, E., and Lindberg, U., Actin is the naturally occurring inhibitor of deoxyribonuclease I. *Proc. Natl. Acad. Sci. USA*, **71**, 4742-4746 (1974).
10. Kunitz, M., Crystalline desoxyribonuclease; isolation and general properties; spectrophotometric method for the measurement of desoxyribonuclease activity. *J. Gen. Physiol.*, **33**, 349-62 (1950).
11. Sambrook, J., and Russell, D.W., Molecular Cloning: A Laboratory Manual, 2<sup>nd</sup> Ed., Cold Spring Harbor Laboratory Press, (Cold Spring Harbor, NY: 2001), Vol. 2, p.13.28

VLR,JWM,RGB,MAM 01/08-1

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.