



3050 Spruce Street
Saint Louis, Missouri 63103 USA
Telephone 800-325-5832 • (314) 771-5765
Fax (314) 286-7828
email: techserv@sial.com
sigma-aldrich.com

Product Information

Monoclonal Anti-Histone Deacetylase 2 (HDAC2)

Clone HDAC2-62

Purified Mouse Immunoglobulin

Product Number **H 2663**

Product Description

Monoclonal Anti-Histone Deacetylase (HDAC2) (mouse IgG2b isotype) is derived from the HDAC2-62 hybridoma produced by the fusion of mouse myeloma cells (NS1) and splenocytes from BALB/c mice immunized with a synthetic peptide corresponding to the C-terminal region of human histone deacetylase 2 (amino acid residues 471-488 with N-terminal added cysteine) conjugated to maleimide-activated KLH. This sequence is highly conserved in mouse and chicken (2 and 1 amino acid substitution, respectively). The isotype is determined using Sigma ImmunoType™ Kit (Product Code ISO-1) and by a double diffusion immunoassay using Mouse Monoclonal Antibody Isotyping Reagents (Product Code ISO-2).

Monoclonal Anti-Histone Deacetylase 2 (HDAC2) recognizes recognizes human, bovine, dog, rat, mouse, and chicken HDAC2 (approx. 55 kDa). The antibody epitope resides within amino acids 471-488 of human HDAC2. The antibody can be used in various immunochemical techniques including ELISA, immunoblotting, immunoprecipitation, and immunohistochemistry

The basic repeating unit of chromatin is the nucleosome, which is composed of a protein octamer containing two each of the core histones H2A, H2B, H3, and H4, surrounded by approximately 146 base pairs of DNA. Reversible acetylation of highly conserved lysine residues in the N-terminal tail domains of core histones plays an important role in transcriptional regulation, cell cycle progression, and development events. Several histone acetyltransferases (HATs) catalyze this acetylation reaction (e.g. GCN5, PCAF, p300/CBP, TAFII250, P/CAF, SRC-1, BRCA-2). Acetylation of the core histones is generally considered to be associated with gene activation, probably through maintenance of the unfolded structure of transcribing nucleosomes.^{1, 2}

Histone acetylation is a dynamic process in which levels are determined by the net activities of HATs and the competing enzymes histone deacetylases (HDACs).³ Both activities are associated with the nuclear matrix. Eleven different mammalian HDACs have been described. HDACs 1-3 & 8 (Class I) are similar to yeast Rpd3 protein, while HDACs 4-7, 9 & 10 (Class II) are similar to yeast Hda1 protein.^{4, 5, 13} The activities of the histone deacetylases are often, but not always, associated with transcriptional repression and nucleosome condensation.^{6, 7} HDAC1, HDAC2 and several others are the catalytic subunits of different multiprotein regulatory complexes.⁸ Other components of such complexes may include: corepressors such as mSin3, N-CoR, SMRT, associated proteins such as SAP18, SAP30, RbAp46, RbAp48, and c-Ski oncogenic protein (involved in DNA methylation). Nucleosome remodeling and deacetylation (NRD) complexes containing HDAC1, HDAC2, Mi-2 (CH3, CH4) dermatomyositis specific autoantigen, and MAT2 (metastasis-associated protein) (related to MAT1) have been described. It is therefore assumed that ATP-dependent nucleosome remodeling activity and histone deacetylation may be interconnected or interdependent.^{9, 10} Recruitment of the multiprotein complexes to promoter sites occurs by many sequence specific DNA-binding proteins such as unliganded nuclear hormone receptors, DP1-E2F, YY1, and Rb family of transcription factors, transcriptional repressors, and tumor suppressors (e.g. BRCA1). Aberrant recruitment of HDACs by various oncoproteins may occur in certain neoplastic diseases.¹¹ It has been found that inhibition of HDAC2 activity by valproic acid induces proteosomal degradation of HDAC2.¹²

Reagent

Monoclonal Anti-Histone Deacetylase 2 (HDAC2) is supplied as a solution in 0.01 M phosphate buffered saline, pH 7.4, and 15 mM sodium azide.

Antibody concentration: Approx. 2 mg/ml

Precautions and Disclaimer

Due to the sodium azide content, a material safety data sheet (MSDS) for this product has been sent to the attention of the safety officer of your institution. Consult the MSDS for information regarding hazards and safe handling practices.

Storage/Stability

For continuous use, store at 2-8 °C for up to one month. For extended storage, freeze in working aliquots at -20 °C. Repeated freezing and thawing is not recommended. Storage in frost-free freezers is also not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation before use. Working dilutions should be discarded if not used within 12 hours.

Product Profile

By immunoblotting, a working antibody concentration of 0.25-0.5 µg/ml is recommended using total cell extracts from NIH-3T3 cells.

Note: In order to obtain the best results using various techniques and preparations, we recommend determining the optimal working dilution by titration.

References

1. Bauer, W.R., et al, J. Mol. Biol., **236**, 685-690 (1994).
2. Lee, D.Y., et al., Cell, **72**, 73-84 (1993).
3. Taunton, J., et al., Science, **272**, 408-411 (1996).
4. Grozinger, C.M., et al., Proc. Natl. Acad. Sci. USA, **96**, 4868-4873 (1999).
5. Fischle, W., et al., J. Biol. Chem., **274**, 11713-11720 (1999).
6. Wolffe, A.P., Science, **272**, 371-372 (1996).
7. Grunstein, M., Nature, **389**, 349-352 (1997).
8. Hassig, C.A., et al., Proc. Natl. Acad. Sci. USA, **95**, 3519-3524 (1998).
9. Tong, J.K., et al., Nature, **395**, 917-921 (1998).
10. Zhang, Y., et al., Cell, **95**, 279-289 (1998).
11. Lin, R.J., et al., Nature, **391**, 811-814 (1998).
12. Kramer, O.H., et al., EMBO, **22**, 3411-3420 (2003).
13. Gao, L., et al., J. Biol. Chem., **277**, 25748-25755 (2002).

KAA/EK 12/03

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.