

## Product Information

### Duolink® In Situ PLA® Probe Anti-Human PLUS

Product Number **DUO92020**

Storage Temperature 2–8 °C

#### Product Description

Duolink® In Situ PLA® Probe Anti-Human PLUS contains affinity purified donkey anti-human IgG (H+L), which reacts with whole molecule human IgG and also reacts with the light chains of other human immunoglobulins.

The PLA Probe Anti-Human Plus has minimal cross-reactivity with bovine, chicken, goat, guinea pig, Syrian hamster, horse, mouse, rabbit, rat, and sheep serum proteins

#### Components

Sufficient components are provided for the indicated number of reactions (30 or 100 RXN), based on 40 µL of the total reaction mixture covering 1 cm<sup>2</sup>.

5× PLA Probe Anti-Human PLUS – Donkey anti-human secondary antibody conjugated to oligonucleotide PLUS  
30 RXN – Catalog Number DUO92020  
100 RXN – Catalog Number DUO92020

1× Blocking Solution – Reagent for blocking of the sample  
30 RXN – Catalog Number DUO82007 4 mL  
100 RXN – Catalog Number DUO82007 8 mL

1× Antibody Diluent – For dilution of PLA probes and primary antibodies  
30 RXN – Catalog Number DUO82008 2.5 mL  
100 RXN – Catalog Number DUO82008 8 mL

#### Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

#### Preparation Instructions

The 1× Blocking Solution and the 1× Antibody Diluent are supplied ready to use.

The PLA Probe Anti-Human PLUS is supplied as a 5× concentrated stock. Dilute the PLA Probe 5-fold with 1× Antibody Diluent. Prepare the appropriate volume of diluted PLA Probe the day of the experiment, **do not store diluted PLA Probes**.

#### Storage/Stability

Store the PLA probe at 2–8 °C. **Do not freeze PLA probes**. Do not store diluted PLA Probe solutions.

#### Procedure

Experiments conducted using Duolink In Situ reagents can detect and visualize protein interactions, protein expression levels, and post translational modifications at the single molecule level in fixed cells and tissue samples. To perform a complete Duolink In Situ experiment, two primary antibodies (IHC or ICC/IF validated) that recognize two target epitopes are required. Additional reagents required include a pair of PLA probes (one PLUS and one MINUS) and detection reagents of choice. Recommended reagents include Wash Buffers and Mounting Medium.

The experimental procedures for Duolink In Situ fluorescence and brightfield applications can be found at [sigma.com/duolink](http://sigma.com/duolink).

This product is covered by several patents and patent applications including US 6,511,809, US 6,558,928, US 6,878,515, US 7,074,564, US 5,665,539, and related US and foreign patents, including Japanese Patent No. 5653964.

Duolink and PLA are registered trademarks of SigmaAldrich Co., LLC.

SG,HJ,MAM 12/18-1