


SWEET NEWS

Introducing Glycoconjugates
from GlycoNZ



The life science
business of Merck
KGaA, Darmstadt,
Germany operates as
MilliporeSigma in the
U.S. and Canada.

Sigma-Aldrich[®]
Lab & Production Materials

A Growing Portfolio for a Growing Field

Glycobiology has become increasingly important in academic, pharmaceutical, and biotech research for understanding the structure and activity of carbohydrates in relation to human health. As a leading supplier in the field, we offer an extensive range of products for glycobiology, including carbohydrates, lipids, glycoconjugates, and stable isotopes. And now, there's much more. We've partnered with GlycoNZ to expand our portfolio of glycoconjugates, giving you even greater possibilities for discovering drug targets for infectious diseases, inflammation, and cancer.

Brochure Content

BM-Series: Biotinylated Monomeric Probes	3
BP-Series: Biotinylated Polymeric Probes	8
FP-Series: Fluorescein-Labelled Polymeric Probes	13
PA-Series: Unlabeled Polyacrylamide Conjugates	18
Legend	22

Discover an unparalleled glycobiology portfolio for your breakthrough ideas.

SigmaAldrich.com/Glycobiology



GlycoNZ Glycoconjugates

Based in New Zealand, GlycoNZ is an established supplier of glycoconjugates for glycobiology research. Offering high quality and a very broad variety, their products are optimized for studying carbohydrate functions, carbohydrate-binding proteins in biological processes, and new carbohydrate-mediated interactions. The range includes more than 800 glycoconjugate forms in four series: biotinylated monomeric probes, biotinylated polymeric probes, fluorescein-labelled polymeric probes, and unlabeled polyacrylamide conjugates. All this is now easily available to you through MilliporeSigma – as always, with our renowned quick delivery and expert support.



New additions to our glycoconjugate portfolio include:

- Sialo- and sulfo-oligosaccharides
- Blood group and xenoantigens
- Cancer-associated antigens
- Glycoprotein O-chains
- Fragments of glycolipids, N-chains
- Ligands for galectins, selectins, siglecs, collectins

BM-Series: Biotinylated Monomeric Probes

These probes have an elongated spacer giving them the possibility to bind avidin or streptavidin. The biotin fragment is hydrophobic enough to permit the probes to be adsorbed on SepPack C18 cartridges from aqueous solutions, and to be eluted by methanol, similarly to glycosides bearing a "Lemieux-type" space. The spacer is the normal spacer of the ligand plus the own spacer of the biotin label $-\text{CO}(\text{CH}_2)_5\text{NH}-$.

Purity: 95-97%

Applications:

- Multi-arrays and micro-arrays
- Construction of glycol-surfaces, glycol-beads

Sug – spacer – biot



Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0000-BM	$\text{HOCH}_2(\text{HOCH})_4\text{CH}_2\text{NH}_2$ -biot	aminoglucitol	1
GNZ-0001-BM	GalNAc β 1-4GlcNAc β -sp3-biot	LacdiNAC	1
GNZ-0004-BM	GlcNAc β 1-3(GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2-biot	Tk	1
GNZ-0006-BM	GalNAc α 1-3(Fuca1-2)Gal β 1-4GlcNAc β -sp3-biot	A (type 2)	1
GNZ-0007-BM	Gal α 1-3(Fuca1-2)Gal β 1-4GlcNAc β -sp3-biot	B (type 2)	1
GNZ-0008-BM	Gal α 1-4Gal β 1-4GlcNAc β -sp3-biot	P ₁	1
GNZ-0009-BM	Gal α 1-3Gal β 1-4(Fuca1-3)GlcNAc β -sp3-biot		1
GNZ-0011-BM	GlcNAc β 1-2Gal β 1-3GalNAc α -sp3-biot	GlcNAc β 1-2`TF	1
GNZ-0012-BM	GlcA β -sp3-biot	β -glucuronate	1
GNZ-0013-BM	Glc β 1-4GalNAc α -sp3-biot		1
GNZ-0014-BM	Man β -sp4-biot	β -D-mannose	1
GNZ-0015-BM	Gal α 1-4GlcNAc β -sp3-biot	α LN	1
GNZ-0015a-BM	Gal α 1-4GlcNAc β -sp8-biot	α LN	1
GNZ-0016-BM	Neu5Ac β -sp9-biot	β -N-acetylneuraminic acid	1
GNZ-0017-BM	Neu5Ac α 2-3(6-O-Su-)Gal β 1-4(Fuca1-3)GlcNAc β -sp3-biot	SiaLe ^x -6(Gal)-O-sulfate	0.5
GNZ-0018-BM	Neu5Gc α -sp3-biot	α -N-glycolylneuraminic acid	1
GNZ-0019-BM	Glc α 1-4Glc β -sp3-biot	maltose	1
GNZ-0020-BM	Neu5Ac α 2-3Gal β 1-4(Fuca1-3)(6-O-Su-)GlcNAc β -sp3-biot	SiaLe ^x -6(GlcNAc)-O-sulfate	0.5
GNZ-0021-BM	Glc α -sp3-biot	α -D-glucose	1
GNZ-0022-BM	Glc β -sp3-biot	β -D-glucose	1
GNZ-0022b-BM	Glc β -sp4-biot		1
GNZ-0023-BM	Gal α -sp3-biot	α -D-galactose	1
GNZ-0024-BM	Gal β -sp3-biot	β -D-galactose	1
GNZ-0024a-BM	Gal β -sp4-biot		1
GNZ-0025a-BM	Man α -sp3-biot	α -mannose	1
GNZ-0026-BM	6-H ₂ PO ₃ -Man α -sp3-biot	α -D-mannose-6-phosphate	1
GNZ-0027-BM	L-Fuca-sp3-biot	α -L-fucose	1
GNZ-0028-BM	L-Rha α -sp3-biot	α -L-rhamnose	1
GNZ-0029-BM	GlcNAc β -sp3-biot	β -D-N-acetylglucosamine	1
GNZ-0029a-BM	GlcNAc β -sp2-biot		1
GNZ-0029d-BM	GlcNAc β -sp4-biot		1
GNZ-0033-BM	Gal α 1-4Gal β -sp3-biot		1

BM-Series: Biotinylated Monomeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0034-BM	3-O-Su-Gal β -sp3-biot	β -D-galactose-3-O-sulfate	1
GNZ-0035-BM	Neu5Aca-sp3-biot	α -N-acetylneuraminic acid	1
GNZ-0035a-BM	Neu5Aca-sp9-biot	α -N-acetylneuraminic acid	1
GNZ-0036-BM	Neu5Aca2-3Gal β 1-4GlcNAc β -sp3-biot	3`SLN	0.5
GNZ-0037-BM	Gala1-4Gal β 1-4Glc β -sp2-biot	P ^k , Gb3, GbOse ₃	1
GNZ-0038-BM	Gala1-3GalNAc β -sp3-biot	T _{oβ}	1
GNZ-0039-BM	Gal β 1-3Gal β -sp3-biot		1
GNZ-0040-BM	Gal β 1-3(Fuca1-4)GlcNAc β -sp3-biot	Le ^a	1
GNZ-0041-BM	Fuca1-2Gal β 1-3(Fuca1-4)GlcNAc β -sp3-biot	Le ^b	1
GNZ-0042-BM	Fuca1-2Gal β 1-3GlcNAc β -sp3-biot	Le ^d , H (type 1)	1
GNZ-0043-BM	Gal β 1-3GlcNAc β -sp3	Le ^c	1
GNZ-0044-BM	Gal β 1-4(Fuca1-3)GlcNAc β -sp3-biot	Le ^x	1
GNZ-0045-BM	Fuca1-2Gal β 1-4(Fuca1-3)GlcNAc β -sp3-biot	Le ^y	1
GNZ-0046a-BM	Gal β 1-4Glc β -sp2-biot	Lac	1
GNZ-0047-BM	Gal β 1-4GlcNAc β -sp3-biot	N-acetyllactosamine	1
GNZ-0047d-BM	Gal β 1-4GlcNAc β -sp2-biot	N-acetyllactosamine	1
GNZ-0048-BM	Gal β 1-3GalNAca-sp3-biot	TF, core 1	1
GNZ-0049-BM	Fuca1-3GlcNAc β -sp3-biot		1
GNZ-0050-BM	Fuca1-4GlcNAc β -sp3-biot	Le	1
GNZ-0051-BM	GalNAca1-3GalNAc β -sp3-biot	Fs	1
GNZ-0052-BM	GalNAca1-3GalNAca-sp3-biot	core 5	1
GNZ-0053-BM	Gala1-3GalNAca-sp3-biot	Taa, core 8	1
GNZ-0054-BM	Neu5Aca2-3Gal β 1-3GlcNAc β -sp3-biot	SiaLec	0.5
GNZ-0055-BM	Gala1-2Gal β -sp3-biot		1
GNZ-0056-BM	Gal β 1-3GalNAc β -sp3-biot	T _{oβ}	1
GNZ-0057-BM	GlcNAc β 1-4GlcNAc β -sp3-biot	chitobiose	1
GNZ-0057a-BM	GlcNAc β 1-4GlcNAc β -sp4-biot	chitobiose	1
GNZ-0058-BM	Neu5Aca2-6GalNAca-sp3-biot	SiaT _n	0.5
GNZ-0059-BM	Fuca1-2Gal β 1-3GalNAca-sp3-biot	H (type 3)	1
GNZ-0060-BM	Neu5Aca2-3Gal β 1-4Glc β -sp4-biot	3`SL	0.5
GNZ-0061-BM	Neu5Acα2-3Gal β 1-3(Fuca1-4)GlcNAc β -sp3-biot	SiaLe ^a	0.5
GNZ-0062-BM	Neu5Aca2-3Gal β 1-4(Fuca1-3)GlcNAc β -sp3-biot	SiaLe ^x	0.5
GNZ-0063a-BM	Neu5Aca2-6Gal β 1-4Glc β -sp2-biot	6`SL	0.5
GNZ-0064-BM	6-O-Su-GlcNAc β -sp3-biot	β -D-GlcNAc-6-O-sulfate	1
GNZ-0065-BM	3-O-Su-Gal β 1-3(Fuca1-4)GlcNAc β -sp3-biot	suLe ^a	0.5
GNZ-0066-BM	3-O-Su-Gal β 1-4(Fuca1-3)GlcNAc β -sp3-biot	suLe ^x	0.5
GNZ-0067a-BM	3-O-Su-Gal β 1-4GlcNAc β -sp2-biot		1
GNZ-0068-BM	3-O-Su-Gal β 1-3GlcNAc β -sp3-biot	Lec-3`-O-sulphate	1
GNZ-0070-BM	Gala1-3Gal β 1-4GlcNAc β -sp3-biot	Galili	1
GNZ-0071-BM	GlcNAc β 1-4GalNAca-sp3-biot		1
GNZ-0073-BM	Neu5Aca2-8Neu5Aca2-8Neu5Aca-sp3-biot	(Sia) ₃	1
GNZ-0075-BM	GlcNAc β 1-3Gal β 1-3GalNAca-sp3-biot	GlcNAc β 1-3`TF	1
GNZ-0076-BM	Gal β 1-2Gal β -sp3-biot		1
GNZ-0077a-BM	Gal β 1-4(6-O-Su)GlcNAc β -sp2-biot		1
GNZ-0078-BM	GlcNAc β 1-6(Gal β 1-3)GalNAca-sp3-biot	core 2	1
GNZ-0079-BM	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3-biot	(LN) ₃	1
GNZ-0080-BM	Fuca1-2Gal β 1-3GalNAc β -sp3-biot	H (type 4)	1
GNZ-0082-BM	Gal β 1-4GlcNAc β 1-3Gal β 1-4Glc β -sp4-biot	LNnT	1
GNZ-0083-BM	Neu5Aca2-3Gal β -sp3-biot	GM4	1
GNZ-0084-BM	Neu5Aca2-6Gal β -sp3-biot		0.5
GNZ-0085-BM	GalNAca1-3(Fuca1-2)Gal β -sp3-biot	A _{tri}	1

BM-Series: Biotinylated Monomeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0085a-BM	GalNAc1-3(Fucα1-2)Galβ-sp5-biot	A ^{tri}	1
GNZ-0086-BM	Gala1-3(Fuca1-2)Galβ-sp3-biot	B ^{tri}	1
GNZ-0086a-BM	Gala1-3(Fuca1-2)Galβ-sp5-biot	B ^{tri}	1
GNZ-0087-BM	GalNAc1-3Galβ-sp3-biot	A _{di}	1
GNZ-0088-BM	Gala1-3Galβ-sp3-biot	B _{di}	1
GNZ-0089-BM	Fuca1-2Galβ1-4GlcNAcβ-sp3-biot	H (type 2)	1
GNZ-0090a-BM	6-O-Su-Galβ1-4GlcNAcβ-sp2-biot	LacNAC-6-O-sulfate	1
GNZ-0091-BM	Fuca1-2Galβ-sp3-biot	H _{di}	1
GNZ-0092-BM	3-O-Su-Galβ1-3GalNAc-sp3-biot	TF-3`-O-sulphate	1
GNZ-0093a-BM	GalNAcβ1-4(6-O-Su)GlcNAcβ-sp3-biot		1
GNZ-0095-BM	GalNAcβ1-3GalNAcβ-sp3	para-Fs	1
GNZ-0096-BM	Neu5Aca2-3Galβ1-3GalNAc-sp3-biot	3`SiaTF	1
GNZ-0097-BM	GlcNAcβ1-3GalNAc-sp3-biot	core 3	1
GNZ-0098-BM	GlcNAcβ1-6GalNAc-sp3-biot	core 6	1
GNZ-0099-BM	GlcNAcβ1-3(GlcNAcβ1-6)GalNAc-sp3-biot	core 4	1
GNZ-0600-BM	Glcβ1-3GlcNAcβ-sp3-biot		1
GNZ-0602-BM	Glcβ1-3GalNAcβ-sp3-biot		1
GNZ-0605-BM	GlcNAcβ1-2Galβ-sp3-biot		1
GNZ-0607-BM	Fucβ1-2Galβ1-3GlcNAcβ-sp3-biot		1
GNZ-0608-BM	GlcNAcβ1-4Galβ-sp3-biot	GlcNAcβ4Galβ	1
GNZ-0609-BM	L-Glcβ-sp4-biot		1
GNZ-0709-BM	Neu5Gca2-3Galβ-sp3-biot	Neu5Gca3Gal	0.5
GNZ-0721-BM	GalNAc1-3(Fuca1-2)Galβ1-3GalNAcβ-sp3-biot	A (type 4)	1
GNZ-0724-BM	GlcNAc1-3GalNAcβ-sp3-biot		1
GNZ-0726-BM	L-Rhaβ-sp4-biot	β-L-rhamnose	1
GNZ-0728-BM	GlcNAc-sp3-biot	α-D-N-acetylglucosamine	1
GNZ-0730-BM	Neu5Gca2-3Galβ1-3(6-O-Su)GlcNAcβ-sp3-biot		1
GNZ-0731-BM	Neu5Gca2-3Galβ1-4(6-O-Su)GlcNAcβ-sp3-biot		1
GNZ-0736-BM	Xylβ-sp4-biot	β-D-xylopyranose	1
GNZ-0738-BM	L-Araα-sp4	α-L-arabinose	1
GNZ-0740-BM	Fucβ1-2Galβ1-4GlcNAcβ-sp3-biot		1
GNZ-0744-BM	Ribβ-sp4-biot	β-D-ribose	1
GNZ-0745-BM	Fucβ1-2Galβ1-4(Fuca1-3)GlcNAcβ-sp3-biot		1
GNZ-0747-BM	GalNAc1-3Galβ1-4GlcNAcβ-sp3-biot	GalNAc3`LN	1
GNZ-0748-BM	GalNAcβ1-3Galβ1-4GlcNAcβ-sp3-biot	GalNAcβ3`LN	1
GNZ-0755-BM	GalNAc1-3Galβ1-4(Fuca1-3)GlcNAcβ-sp3		1
GNZ-0757-BM	Neu5Aca2-6(Fuca1-2)Galβ1-4GlcNAcβ-sp3-biot	Sia6`H(type 2)	0.5
GNZ-0762-BM	6-O-Su-Galβ-sp3-biot	β-D-galactose-6-O-sulfate	1
GNZ-0763-BM	Neu5Aca2-3(6-O-Su)Galβ1-4(6-O-Su)GlcNAcβ-sp3-biot	3`SLN-6,6`-di-O-sulfate	0.5
GNZ-0769-BM	3-O-Su-GalNAc-sp3-biot	T _n -3-O-sulfate	1
GNZ-0770-BM	GalNGcβ-sp3-biot	β-D-N-glycolylgalactosamine	1
GNZ-0773-BM	Galβ1-3GalNGca-sp3-biot		1
GNZ-0778-BM	4-O-Su-GalNAc-sp3-biot	T _n -4-O-sulfate	1
GNZ-0785-BM	Neu5Aca2-3(6-O-Su)Galβ1-3GalNAc-sp3-biot	3`SiaTF-6`-O-sulfate	0.5
GNZ-0786-BM	Galβ1-3GlcNAcβ1-3GalNAc-sp3-biot	Le ^c T _n	1
GNZ-0789-BM	Galβ1-3(6-O-Su)GalNAc-sp3-biot	TF-6-O-sulfate	1
GNZ-0799-BM	Fucβ-sp4-biot	β-L-fucose	1
GNZ-0800-BM	GalNAc1-4Galβ-sp3-biot	GalNAc1-4Galβ	1
GNZ-0805-BM	GalNAcβ1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-biot		1
GNZ-0808-BM	GlcNAcβ1-4(GlcNAcβ1-6)GalNAc-sp3-biot		1
GNZ-0809-BM	(GlcNAcβ1) ₃ -3,4,6GalNAc-sp3-biot		1

BM-Series: Biotinylated Monomeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0810-BM	GalNAc β 1-3(Fuca1-2)Gal β -sp3-biot		1
GNZ-0813-BM	Gal β 1-3GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3-biot	Le ^c 3` LacNAc	1
GNZ-0814-BM	Gal β 1-3GlcNAc α 1-3Gal β 1-4GlcNAc β -sp3-biot	Le ^a 3` LacNAc	1
GNZ-0815-BM	Gal β 1-3GlcNAc β 1-3Gal β 1-3GlcNAc β -sp2-biot	Le ^c 3` Le ^c	1
GNZ-0815a-BM	Gal β 1-3GlcNAc β 1-3Gal β 1-3GlcNAc β -sp3-biot	Le ^c 3` Le ^c	1
GNZ-0816-BM	GalNAc α 1-3(Fuca1-2)Gal β 1-3GlcNAc β -sp3-biot	A (type 1)	1
GNZ-0821-BM	6-O-Su-Gal β 1-3GalNAc α -sp3-biot		1
GNZ-0822-BM	Gal β 1-3(6-O-Su)GlcNAc β -sp2-biot	Le ^c -6-O-sulphate	1
GNZ-0822a-BM	Gal β 1-3(6-O-Su)GlcNAc β -sp3-biot		1
GNZ-0823-BM	Neu5Ac α 2-3Gal β 1-4(2-O-Su-Fuca1-3)(6-O-Su)GlcNAc β -sp3-biot	SLe ^x -6(GlcNAc)-2(Fuc)-di-sulfate	0.5
GNZ-0828-BM	Fuca1-2(3-O-Su)Gal β -sp3-biot	H _{di} -3-O-sulphate	1
GNZ-0835a-BM	Neu5Ac α 2-3(GalNAc β 1-4)Gal β 1-4Glc β -sp4-biot	GM2	0.5
GNZ-0837-BM	4-O-Su-Gal β -sp3-biot	β -D-galactose-4-O-sulfate	1
GNZ-0840-BM	6-O-Su-Gal β 1-3GlcNAc β -sp2-biot	Le ^c -6`-O-sulphate	1
GNZ-0842-BM	Gal β 1-3GlcNAc β 1-6Gal β 1-4GlcNAc β -sp2-biot	Le ^c 6` LacNAc	1
GNZ-0847-BM	Gal α 1-3(Fuca1-2)Gal β 1-3GlcNAc β -sp3-biot	B (type 1)	1
GNZ-0848-BM	Gal α 1-3(Fuca1-2)Gal β 1-3GalNAc α -sp3	B (type 3)	1
GNZ-0849-BM	Gal α 1-3(Fuca1-2)Gal β 1-3GalNAc β -sp3	B (type 4)	1
GNZ-0852-BM	Gal α 1-3GlcNAc β -sp3		1
GNZ-0854d-BM	(GlcA β 1-3GlcNAc β 1-4) ₁₃ -sp6	hyaluronic acid	1
GNZ-0855-BM	GlcNAc β 1-4(6-O-Su)GlcNAc β -sp3	6-O-Su-chitobiose	1
GNZ-0857-BM	Gal α 1-3Gal β 1-4GlcNAc β 1-3Gal β -sp3	Galili(tetra)	1
GNZ-0859-BM	3-O-Su-Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3	(3` SuLN)3LN	1
GNZ-0860-BM	GalNAc α 1-3(Fuca1-2)Gal β 1-3GalNAc α -sp3	A (type 3)	1
GNZ-0864-BM	GlcNAc α 1-3Gal β 1-4GlcNAc β -sp3	GlcNAc α 3` LacNAc	1
GNZ-0864a-BM	GlcNAc α 1-3Gal β 1-4GlcNAc β -sp2		1
GNZ-0865a-BM	Gal β 1-3Gal β 1-4GlcNAc β -sp3	Gal β 3`LacNAc	1
GNZ-0866-BM	Gal β 1-4GlcNAc β 1-3(GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2		1
GNZ-0867-BM	Gal β 1-4GlcNAc β 1-3(Gal β 1-4GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2		1
GNZ-0870-BM	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp2	LacNAc3` LacNAc	1
GNZ-0870a-BM	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3		1
GNZ-0871-BM	Gal β 1-4GlcNAc β 1-6Gal β 1-4GlcNAc β -sp2	LacNAc6` LacNAc	1
GNZ-0872-BM	Neu5Gc β 2-6Gal β 1-4GlcNAc β -sp3	6` Sia(Gc) β LacNAc	0.5
GNZ-0874-BM	Gal β 1-4(Fuc β 1-3)GlcNAc β -sp3		1
GNZ-0880-BM	3,6-O-Su ₂ -Gal β 1-4(6-O-Su)GlcNAc β -sp2	LacNAc-3`,6,6`-tri-O-sulphate	1
GNZ-0881-BM	3-O-Su-Gal β 1-4(6-O-Su)GlcNAc β -sp3	LacNAc-3`,6-di-O-sulphate	1
GNZ-0882-BM	3,4-O-Su ₂ -Gal β 1-4GlcNAc β -sp3	LacNAc-3`,4`-di-O-sulphate	1
GNZ-0883-BM	6-O-Su-Gal β 1-4(6-O-Su)GlcNAc β -sp2	LacNAc-6,6`-di-O-sulphate	1
GNZ-0884-BM	Man α 1-3(Man α 1-6)Man α 1-6(Man α 1-3)Man β -sp4		1
GNZ-0885-BM	6-H ₂ PO ₃ -Glc β -sp4	β -D-glycose-6-O-phosphate	1
GNZ-0886-BM	3,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2		1
GNZ-0887a-BM	GlcNAc β 1-4Gal β 1-4GlcNAc β -sp3	GlcNAc4` LacNAc	1
GNZ-0901-BM	6-O-Su-Gal β 1-4(6-O-Su)Glc β -sp2	Lac-6,6`-di-O-sulphate	1
GNZ-0902-BM	Glc β 1-6Glc β -sp4	Gentiobiose	1
GNZ-0907-BM	Neu5Ac β 2-6Gal β 1-4GlcNAc β -sp3	6` Sia β LacNAc	0.5
GNZ-0908-BM	Neu5Ac α 2-6Gal β 1-4(6-O-Su)GlcNAc β -sp3	6` SLN-6-O-sulphate	0.5
GNZ-0909a-BM	4-O-Su-Gal β 1-4GlcNAc β -sp2		1
GNZ-0918a-BM	4,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2	LacNAc-4`,6`-di-O-sulphate	1
GNZ-0921-BM	4-O-Su-GlcNAc β -sp2	β -D-GlcNAc-4-O-sulfate	1
GNZ-0922-BM	GalNAc α 1-4GalNAc α -sp3		1
GNZ-0925-BM	Neu5Ac α 2-6Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3		1

BM-Series: Biotinylated Monomeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0931-BM	Glcα1-4Glcα1-4Glcα1-4Glcβ-sp4	maltotetraose	1
GNZ-0932-BM	Glcα1-4Glcα1-4Glcβ-sp4	maltotriose	1
GNZ-0934-BM	6-O-Su-GalNAcβ1-4(3-O-Ac)GlcNAcβ-sp3	3-O-Ac-LacdiNac-6`-sulphate	1
GNZ-0935-BM	4,6-O-Su ₂ -GalNAcβ1-4GlcNAcβ-sp3	LacdiNac-4`,6`-di-O-sulphate	1
GNZ-0936-BM	4-O-Su-GalNAcβ1-4GlcNAcβ-sp3		1
GNZ-0937-BM	6-O-Su-GalNAcβ1-4GlcNAcβ-sp3	6`-O-su-LacdiNac	1
GNZ-0941-BM	3-O-Su-GlcNAcβ-sp3	β-D-GlcNAc-3-O-sulfate	1
GNZ-0946-BM	Manα1-4Manβ-sp4		1
GNZ-0949-BM	Neu5Aca2-3Galβ1-3(6-O-Su)GlcNAcβ-sp3	3`SiaLec-6-O-sulphate	0.5
GNZ-0951-BM	Neu5Aca2-3Galβ1-4(6-O-Su)GlcNAcβ-sp3	3`SLN-6-O-sulphate	0.5
GNZ-0952-BM	3-O-Su-GalNAcβ-sp3	β-D-GalNAc-3-O-sulfate	1
GNZ-0953-BM	4-O-Su-GalNAcβ-sp3	β-D-GalNAc-4-O-sulfate	1
GNZ-0955-BM	Galβ1-4(Galβ1-3)GlcNAcβ-sp3		1
GNZ-0956-BM	Neu5Gca2-3Galβ1-4GlcNAcβ-sp3	3`Sia(Gc)LacNAc	0.5
GNZ-0957-BM	Neu5Gca2-6Galβ1-4GlcNAcβ-sp3	6`Sia(Gc)LacNAc	0.5
GNZ-0958-BM	GlcNAcβ1-3Galβ1-4GlcNAcβ-sp2	GlcNAcβ3`LacNAc	1
GNZ-0958a-BM	GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3	GlcNAcβ3`LacNAc	1
GNZ-0959-BM	Glcα1-6Glcα1-6Glcβ-sp4	Isomaltotriose	1
GNZ-0966-BM	Galα1-3(Fuca1-2)Galβ1-3(Fuca1-4)GlcNAcβ-sp3	BLE ^b	1
GNZ-0967-BM	GalNAca1-3(Fuca1-2)Galβ1-4(Fuca1-3)GlcNAcβ-sp3	ALe ^y	1
GNZ-0968-BM	Galα1-3(Fuca1-2)Galβ1-4(Fuca1-3)GlcNAcβ-sp3	BLE ^y	0.5
GNZ-0972-BM	GlcNAcβ1-4[3-O-CH(CH ₃)COOH]GlcNAcβ-sp4	GlcNAc-Mur	1
GNZ-0973-BM	GlcNAcβ1-4[3-O-CH(CH ₃)COOH]GlcNAca-sp4		1
GNZ-0976-BM	GlcAβ1-3Galβ-sp3	GlcA3Gal	1
GNZ-0977-BM	Neu5Aca2-6(Galα1-3)GalNAca-sp3	6SiaT _{aa}	0.5
GNZ-0978-BM	GlcAβ1-6Galβ-sp3	GlcAβ6Gal	1
GNZ-0980-BM	Galβ1-4GlcNAcβ1-6(Galβ1-3)GalNAca-sp3	LacNAc6TF	0.5
GNZ-0982-BM	GlcNAcβ1-4GlcNAβ1-4GlcNAcβ-sp4	chitotriose	1
GNZ-0984-BM	Neu5Aca2-6(Galβ1-3)GalNAca-sp3	6SiaTF	0.5
GNZ-0985-BM	Neu5Acβ2-6(Galβ1-3)GalNAca-sp3	6SiaβTF	0.5
GNZ-0986-BM	Neu5Acβ2-6GalNAca-sp3	SiaβT _n	0.5
GNZ-0991-BM	Galα1-4GalNAca-sp3		1
GNZ-0993-BM	Neu5Aca2-3GalNAca-sp3	3-SiaT _n	0.5
GNZ-0995-BM	Galβ1-4GlcNAβ1-3GalNAca-sp3	LacNAc3T _n	1
GNZ-0996-BM	Galβ1-4GlcNAβ1-6GalNAca-sp3	LacNAc6T _n	1
GNZ-0997-BM	Neu5Aca2-6Galβ1-4GlcNAcβ-sp3	6`SLN	1
GNZ-0998-BM	6-O-Su-GalNAca-sp3	α-D-GalNAc-6-O-sulfate	1

BP-Series: Biotinylated Polymeric Probes

This series includes HOCH₂CH₂NH₃⁺-salts for acidic sugars. The affinity of these probes is 10² to 10⁵ times higher than that of the corresponding free sugars. The spacer-arm is normally -(CH₂)₃-, while the spacer arm for biotin is -(CH₂)₆-. The flexible polymer chain behaves as an additional spacer. Used as a high molecular weight carrier, poly[N-(2-hydroxyethyl)acrylamide], abbreviated as PAA, has low non-specific sorption, and is stable to chemical and proteolytic action.


Molecular mass: approx. 30 kDa

Content: saccharide 20% mol., biotin 5% mol.

Purity: synthetic ω-aminoalkyl glycosides used for coupling with the polymer have a purity of >95% (HPLC and ¹H-NMR)

Applications:

- Construction of glycol-surfaces, glycol-beads, multi-arrays
- Revealing lectins in assays, flow cytometry, histochemistry



Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0000-BP	HOCH ₂ (HOCH) ₄ CH ₂ NH ₂ -PAA-biot	aminoglucitol	1
GNZ-0001-BP	GalNAcβ1-4GlcNAcβ-sp3-PAA-biot	LacdiNac	1
GNZ-0004-BP	GlcNAcβ1-3(GlcNAcβ1-6)Galβ1-4GlcNAcβ-sp2-PAA-biot	Tk	1
GNZ-0006-BP	GalNAcα1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA-biot	A (type 2)	1
GNZ-0007-BP	Galα1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA-biot	B (type 2)	1
GNZ-0008-BP	Galα1-4Galβ1-4GlcNAcβ-sp3-PAA-biot	P ₁	1
GNZ-0009-BP	Galα1-3Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA-biot		1
GNZ-0011-BP	GlcNAcβ1-2Galβ1-3GalNAcα-sp3-PAA-biot	GlcNAcβ1-2`TF	1
GNZ-0012-BP	GlcAβ-sp3-PAA-biot	β-glucuronate	1
GNZ-0013-BP	Glcβ1-4GalNAcα-sp3-PAA-biot		1
GNZ-0014-BP	Manβ-sp4-PAA-biot	β-D-mannose	1
GNZ-0015-BP	Galα1-4GlcNAcβ-sp3-PAA-biot	αLN	1
GNZ-0015a-BP	Galα1-4GlcNAcβ-sp8-PAA-biot	αLN	1
GNZ-0016-BP	Neu5Acβ-sp9-PAA-biot	β-N-acetylneuraminic acid	1
GNZ-0017-BP	Neu5Acα2-3(6-O-Su-)Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA-biot	SiaLex ^x -6(Gal)-O-sulfate	0.5
GNZ-0018-BP	Neu5Gca-sp3-PAA-biot	α-N-glycolylneuraminic acid	1
GNZ-0019-BP	Glcα1-4Glcβ-sp3-PAA-biot	maltose	1
GNZ-0020-BP	Neu5Acα2-3Galβ1-4(Fuca1-3)(6-O-Su-)GlcNAcβ-sp3-PAA-biot	SiaLex-6(GlcNAc)-O-sulfate	0.5
GNZ-0021-BP	Glcα-sp3-PAA-biot	α-D-glucose	1
GNZ-0022-BP	Glcβ-sp3-PAA-biot	β-D-glucose	1
GNZ-0022b-BP	Glcβ-sp4-PA-biot		1
GNZ-0023-BP	Galα-sp3-PAA-biot	α-D-galactose	1
GNZ-0024-BP	Galβ-sp3-PAA-biot	β-D-galactose	1
GNZ-0024a-BP	Galβ-sp4-PAA-biot		1
GNZ-0025a-BP	Mana-sp3-PAA-biot	α-mannose	1
GNZ-0026-BP	6-H ₂ PO ₃ -Mana-sp3-PAA-biot	α-D-mannose-6-phosphate	1
GNZ-0027-BP	L-Fuca-sp3-PAA-biot	α-L-fucose	1
GNZ-0028-BP	L-Rhaα-sp3-PAA-biot	α-L-rhamnose	1
GNZ-0029-BP	GlcNAcβ-sp3-PAA-biot	β-D-N-acetylglucosamine	1

BP-Series: Biotinylated Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0029a-BP	GlcNAc β -sp2-PAA-biot		1
GNZ-0029d-BP	GlcNAc β -sp4-PAA-biot		1
GNZ-0033-BP	Gala1-4Gal β -sp3-PAA-biot		1
GNZ-0034-BP	3-O-Su-Gal β -sp3-PAA-biot	β -D-galactose-3-O-sulfate	1
GNZ-0035-BP	Neu5Aca-sp3-PAA-biot	α -N-acetylneuraminic acid	1
GNZ-0035a-BP	Neu5Aca-sp9-PAA-biot	α -N-acetylneuraminic acid	1
GNZ-0036-BP	Neu5Aca2-3Gal β 1-4GlcNAc β -sp3-PAA-biot	3`SLN	0.5
GNZ-0037-BP	Gala1-4Gal β 1-4Glc β -sp2-PAA-biot	P ^k , Gb3, GbOse ₃	1
GNZ-0038-BP	Gala1-3GalNAc β -sp3-PAA-biot	T _{0β}	1
GNZ-0039-BP	Gal β 1-3Gal β -sp3-PAA-biot		1
GNZ-0040-BP	Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-biot	Le ^a	1
GNZ-0041-BP	Fuca1-2Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-biot	Le ^b	1
GNZ-0042-BP	Fuca1-2Gal β 1-3GlcNAc β -sp3-PAA-biot	Le ^d , H (type 1)	1
GNZ-0043-BP	Gal β 1-3GlcNAc β -sp3-PAA-biot	Le ^c	1
GNZ-0044-BP	Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-biot	Le ^x	1
GNZ-0045-BP	Fuca1-2Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-biot	Le ^v	1
GNZ-0046a-BP	Gal β 1-4Glc β -sp2-PAA-biot	Lac	1
GNZ-0047-BP	Gal β 1-4GlcNAc β -sp3-PAA-biot	N-acetyllactosamine	1
GNZ-0047d-BP	Gal β 1-4GlcNAc β -sp2-PAA-biot	N-acetyllactosamine	1
GNZ-0048-BP	Gal β 1-3GalNAca-sp3-PAA-biot	TF, core 1	1
GNZ-0049-BP	Fuca1-3GlcNAc β -sp3-PAA-biot		1
GNZ-0050-BP	Fuca1-4GlcNAc β -sp3-PAA-biot	Le	1
GNZ-0051-BP	GalNAca1-3GalNAc β -sp3-PAA-biot	Fs	1
GNZ-0052-BP	GalNAca1-3GalNAca-sp3-PAA-biot	core 5	1
GNZ-0053-BP	Gala1-3GalNAca-sp3-PAA-biot	T _{00r} , core 8	1
GNZ-0054-BP	Neu5Aca2-3Gal β 1-3GlcNAc β -sp3-PAA-biot	SiaLe ^c	0.5
GNZ-0055-BP	Gala1-2Gal β -sp3-PAA-biot		1
GNZ-0056-BP	Gal β 1-3GalNAc β -sp3-PAA-biot	T _{$\beta\beta$}	1
GNZ-0057-BP	GlcNAc β 1-4GlcNAc β -sp3-PAA-biot	chitobiose	1
GNZ-0057a-BP	GlcNAc β 1-4GlcNAc β -sp4-PAA-biot	chitobiose	1
GNZ-0058-BP	Neu5Aca2-6GalNAca-sp3-PAA-biot	SiaT _n	0.5
GNZ-0059-BP	Fuca1-2Gal β 1-3GalNAca-sp3-PAA-biot	H (type 3)	1
GNZ-0060-BP	Neu5Aca2-3Gal β 1-4Glc β -sp4-PAA-biot	3`SL	0.5
GNZ-0061-BP	Neu5Aca α 2-3Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-biot	SiaLe ^a	0.5
GNZ-0062-BP	Neu5Aca2-3Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-biot	SiaLe ^x	0.5
GNZ-0063a-BP	Neu5Aca2-6Gal β 1-4Glc β -sp2-PAA-biot	6`SL	0.5
GNZ-0064-BP	6-O-Su-GlcNAc β -sp3-PAA-biot	β -D-GlcNAc-6-O-sulfate	1
GNZ-0065-BP	3-O-Su-Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-biot	suLe ^a	0.5
GNZ-0066-BP	3-O-Su-Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-biot	suLe ^x	0.5
GNZ-0067a-BP	3-O-Su-Gal β 1-4GlcNAc β -sp2-PAA-biot		1
GNZ-0068-BP	3-O-Su-Gal β 1-3GlcNAc β -sp3-PAA-biot	Lec-3`-O-sulphate	1
GNZ-0070-BP	Gala1-3Gal β 1-4GlcNAc β -sp3-PAA-biot	Galili	1
GNZ-0071-BP	GlcNAc β 1-4GalNAca-sp3-PAA-biot		1
GNZ-0073-BP	Neu5Aca2-8Neu5Aca2-8Neu5Aca-sp3-PAA-biot	(Sia) ₃	1
GNZ-0075-BP	GlcNAc β 1-3Gal β 1-3GalNAca-sp3-PAA-biot	GlcNAc β 1-3`TF	1
GNZ-0076-BP	Gal β 1-2Gal β -sp3-PAA-biot		1
GNZ-0077a-BP	Gal β 1-4(6-O-Su)GlcNAc β -sp2-PAA-biot		1
GNZ-0078-BP	GlcNAc β 1-6(Gal β 1-3)GalNAca-sp3-PAA-biot	core 2	1
GNZ-0079-BP	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3-PAA-biot	(LN) ₃	1
GNZ-0080-BP	Fuca1-2Gal β 1-3GalNAc β -sp3-PAA-biot	H (type 4)	1
GNZ-0082-BP	Gal β 1-4GlcNAc β 1-3Gal β 1-4Glc β -sp4-PAA-biot	LNnT	1

BP-Series: Biotinylated Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0083-BP	Neu5Aca2-3Galβ-sp3-PAA-biot	GM4	1
GNZ-0084-BP	Neu5Aca2-6Galβ-sp3-PAA-biot		0.5
GNZ-0085-BP	GalNAca1-3(Fuca1-2)Galβ-sp3-PAA-biot	A _{tri}	1
GNZ-0085a-BP	GalNAca1-3(Fucα1-2)Galβ-sp5-PAA-biot	A _{tri}	1
GNZ-0086-BP	Galα1-3(Fuca1-2)Galβ-sp3-PAA-biot	B _{tri}	1
GNZ-0086a-BP	Galα1-3(Fuca1-2)Galβ-sp5-PAA-biot	B _{tri}	1
GNZ-0087-BP	GalNAca1-3Galβ-sp3-PAA-biot	A _{di}	1
GNZ-0088-BP	Galα1-3Galβ-sp3-PAA-biot	B _{di}	1
GNZ-0089-BP	Fuca1-2Galβ1-4GlcNAcβ-sp3-PAA-biot	H (type 2)	1
GNZ-0090a-BP	6-O-Su-Galβ1-4GlcNAcβ-sp2-PAA-biot	LacNAc-6-O-sulfate	1
GNZ-0091-BP	Fuca1-2Galβ-sp3-PAA-biot	H _{di}	1
GNZ-0092-BP	3-O-Su-Galβ1-3GalNAca-sp3-PAA-biot	TF-3`-O-sulphate	1
GNZ-0093a-BP	GalNAcβ1-4(6-O-Su)GlcNAcβ-sp3-PAA-biot		1
GNZ-0095-BP	GalNAcβ1-3GalNAcβ-sp3-PAA-biot	para-Fs	1
GNZ-0096-BP	Neu5Aca2-3Galβ1-3GalNAca-sp3-PAA-biot	3`SiaTF	1
GNZ-0097-BP	GlcNAcβ1-3GalNAca-sp3-PAA-biot	core 3	1
GNZ-0098-BP	GlcNAcβ1-6GalNAca-sp3-PAA-biot	core 6	1
GNZ-0099-BP	GlcNAcβ1-3(GlcNAcβ1-6)GalNAca-sp3-PAA-biot	core 4	1
GNZ-0600-BP	Glcβ1-3GlcNAcβ-sp3-PAA-biot		1
GNZ-0602-BP	Glcβ1-3GalNAcβ-sp3-PAA-biot		1
GNZ-0605-BP	GlcNAcβ1-2Galβ-sp3-PAA-biot		1
GNZ-0607-BP	Fucβ1-2Galβ1-3GlcNAcβ-sp3-PAA-biot		1
GNZ-0608-BP	GlcNAcβ1-4Galβ-sp3-PAA-biot	GlcNAcβ4Galβ	1
GNZ-0609-BP	L-Glcβ-sp4-PAA-biot		1
GNZ-0709-BP	Neu5Gca2-3Galβ-sp3-PAA-biot	Neu5Gca3Gal	0.5
GNZ-0721-BP	GalNAca1-3(Fuca1-2)Galβ1-3GalNAcβ-sp3-PAA-biot	A (type 4)	1
GNZ-0724-BP	GlcNAca1-3GalNAcβ-sp3-PAA-biot		1
GNZ-0726-BP	L-Rhaβ-sp4-PAA-biot	β-L-rhamnose	1
GNZ-0728-BP	GlcNAca-sp3-PAA-biot	α-D-N-acetylglucosamine	1
GNZ-0730-BP	Neu5Gca2-3Galβ1-3(6-O-Su)GlcNAcβ-sp3-PAA-biot		1
GNZ-0731-BP	Neu5Gca2-3Galβ1-4(6-O-Su)GlcNAcβ-sp3-PAA-biot		1
GNZ-0736-BP	Xylβ-sp4-PAA-biot	β-D-xylopyranose	1
GNZ-0738-BP	L-Araα-sp4-PAA-biot	α-L-arabinose	1
GNZ-0740-BP	Fucβ1-2Galβ1-4GlcNAcβ-sp3-PAA-biot		1
GNZ-0744-BP	Ribβ-sp4-PAA-biot	β-D-ribose	1
GNZ-0745-BP	Fucβ1-2Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA-biot		1
GNZ-0747-BP	GalNAca1-3Galβ1-4GlcNAcβ-sp3-PAA-biot	GalNAca3`LN	1
GNZ-0748-BP	GalNAcβ1-3Galβ1-4GlcNAcβ-sp3-PAA-biot	GalNAcβ3`LN	1
GNZ-0755-BP	GalNAca1-3Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA-biot		1
GNZ-0757-BP	Neu5Aca2-6(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA-biot	Sia6`H(type 2)	0.5
GNZ-0762-BP	6-O-Su-Galβ-sp3-PAA-biot	β-D-galactose-6-O-sulfate	1
GNZ-0763-BP	Neu5Aca2-3(6-O-Su)Galβ1-4(6-O-Su)GlcNAcβ-sp3-PAA-biot	3`SLN-6,6`-di-O-sulfate	0.5
GNZ-0769-BP	3-O-Su-GalNAca-sp3-PAA-biot	T _n -3-O-sulfate	1
GNZ-0770-BP	GalNGcβ-sp3-PAA-biot	β-D-N-glycolylgalactosamine	1
GNZ-0773-BP	Galβ1-3GalNGca-sp3-PAA-biot		1
GNZ-0778-BP	4-O-Su-GalNAca-sp3-PAA-biot	T _n -4-O-sulfate	1
GNZ-0785-BP	Neu5Aca2-3(6-O-Su)Galβ1-3GalNAca-sp3-PAA-biot	3`SiaTF-6`-O-sulfate	0.5
GNZ-0786-BP	Galβ1-3GlcNAcβ1-3GalNAca-sp3-PAA-biot	Le ^c 3T _n	1
GNZ-0789-BP	Galβ1-3(6-O-Su)GalNAca-sp3-PAA-biot	TF-6-O-sulfate	1
GNZ-0799-BP	Fucβ-sp4-PAA-biot	β-L-fucose	1
GNZ-0800-BP	GalNAca1-4Galβ-sp3-PAA-biot	GalNAca1-4Galβ	1

BP-Series: Biotinylated Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0805-BP	GalNAc β 1-3(Fuca1-2)Gal β 1-4GlcNAc β -sp3-PAA-biot		1
GNZ-0808-BP	GlcNAc β 1-4(GlcNAc β 1-6)GalNAca-sp3-PAA-biot		1
GNZ-0809-BP	(GlcNAc β 1) ₃ -3,4,6GalNAca-sp3-PAA-biot		1
GNZ-0810-BP	GalNAc β 1-3(Fuca1-2)Gal β -sp3		1
GNZ-0813-BP	Gal β 1-3GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3-PAA-biot	Le ^e 3`LacNAc	1
GNZ-0814-BP	Gal β 1-3GlcNAca1-3Gal β 1-4GlcNAc β -sp3-PAA-biot	Le ^e 3`LacNAc	1
GNZ-0815-BP	Gal β 1-3GlcNAc β 1-3Gal β 1-3GlcNAc β -sp2-PAA-biot	Le ^e 3`Lec	1
GNZ-0815a-BP	Gal β 1-3GlcNAc β 1-3Gal β 1-3GlcNAc β -sp3-PAA-biot	Le ^e 3`Lec	1
GNZ-0816-BP	GalNAca1-3(Fuca1-2)Gal β 1-3GlcNAc β -sp3-PAA-biot	A (type 1)	1
GNZ-0821-BP	6-O-Su-Gal β 1-3GalNAca-sp3-PAA-biot		1
GNZ-0822-BP	Gal β 1-3(6-O-Su)GlcNAc β -sp2-PAA-biot	Le ^e -6-O-sulphate	1
GNZ-0822a-BP	Gal β 1-3(6-O-Su)GlcNAc β -sp3-PAA-biot		1
GNZ-0823-BP	Neu5Aca2-3Gal β 1-4(2-O-Su-Fuca1-3)(6-O-Su)GlcNAc β -sp3-PAA-biot	SLe ^x -6 ^(GlcNAc) -2 ^(Fuc) -di-sulfate	0.5
GNZ-0828-BP	Fuca1-2(3-O-Su)Gal β -sp3-PAA-biot	H _{di} -3-O-sulphate	1
GNZ-0835a-BP	Neu5Aca2-3(GalNAc β 1-4)Gal β 1-4Glc β -sp4-PAA-biot	GM2	0.5
GNZ-0837-BP	4-O-Su-Gal β -sp3-PAA-biot	β -D-galactose-4-O-sulfate	1
GNZ-0840-BP	6-O-Su-Gal β 1-3GlcNAc β -sp2-PAA-biot	Le ^e -6`-O-sulphate	1
GNZ-0842-BP	Gal β 1-3GlcNAc β 1-6Gal β 1-4GlcNAc β -sp2-PAA-biot	Le ^e 6`LacNAc	1
GNZ-0847-BP	Gal α 1-3(Fuca1-2)Gal β 1-3GlcNAc β -sp3-PAA-biot	B (type 1)	1
GNZ-0848-BP	Gal α 1-3(Fuca1-2)Gal β 1-3GalNAca-sp3	B (type 3)	1
GNZ-0849-BP	Gal α 1-3(Fuca1-2)Gal β 1-3GalNAc β -sp3	B (type 4)	1
GNZ-0852-BP	Gal α 1-3GlcNAc β -sp3		1
GNZ-0854d-BP	(GlcA β 1-3GlcNAc β 1-4)13-sp6	hyaluronic acid	1
GNZ-0855-BP	GlcNAc β 1-4(6-O-Su)GlcNA β -sp3	6-O-Su-chitobiose	1
GNZ-0857-BP	Gal α 1-3Gal β 1-4GlcNAc β 1-3Gal β -sp3	Galili(tetra)	1
GNZ-0859-BP	3-O-Su-Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3	(3`SuLN)3LN	1
GNZ-0860-BP	GalNAca1-3(Fuca1-2)Gal β 1-3GalNAca-sp3	A (type 3)	1
GNZ-0864-BP	GlcNAca1-3Gal β 1-4GlcNAc β -sp3	GlcNAca3`LacNAc	1
GNZ-0864a-BP	GlcNAca1-3Gal β 1-4GlcNAc β -sp2		1
GNZ-0865a-BP	Gal β 1-3Gal β 1-4GlcNAc β -sp3	Gal β 3`LacNAc	1
GNZ-0866-BP	Gal β 1-4GlcNAc β 1-3(GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2		1
GNZ-0867-BP	Gal β 1-4GlcNAc β 1-3(Gal β 1-4GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2		1
GNZ-0870-BP	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp2	LacNAc3`LacNAc	1
GNZ-0870a-BP	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3		1
GNZ-0871-BP	Gal β 1-4GlcNAc β 1-6Gal β 1-4GlcNAc β -sp2	LacNAc6`LacNAc	1
GNZ-0872-BP	Neu5Gc β 2-6Gal β 1-4GlcNAc β -sp3	6`Sia(Gc) β LacNAc	0.5
GNZ-0874-BP	Gal β 1-4(Fuc β 1-3)GlcNAc β -sp3		1
GNZ-0880-BP	3,6-O-Su ₂ -Gal β 1-4(6-O-Su)GlcNAc β -sp2	LacNAc-3`,6,6`-tri-O-sulphate	1
GNZ-0881-BP	3-O-Su-Gal β 1-4(6-O-Su)GlcNAc β -sp3	LacNAc-3`,6-di-O-sulphate	1
GNZ-0882-BP	3,4-O-Su ₂ -Gal β 1-4GlcNAc β -sp3	LacNAc-3`,4`-di-O-sulphate	1
GNZ-0883-BP	6-O-Su-Gal β 1-4(6-O-Su)GlcNAc β -sp2	LacNAc-6,6`-di-O-sulphate	1
GNZ-0884-BP	Man α 1-3(Man α 1-6)Man α 1-6(Man α 1-3)Man β -sp4		1
GNZ-0885-BP	6-H ₂ PO ₃ -Glc β -sp4	β -D-glycose-6-O-phosphate	1
GNZ-0886-BP	3,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2		1
GNZ-0887a-BP	GlcNAc β 1-4Gal β 1-4GlcNAc β -sp3	GlcNAc4`LacNAc	1
GNZ-0901-BP	6-O-Su-Gal β 1-4(6-O-Su)Glc β -sp2	Lac-6,6`-di-O-sulphate	1
GNZ-0902-BP	Glc β 1-6Glc β -sp4	Gentiobiose	1
GNZ-0907-BP	Neu5Ac β 2-6Gal β 1-4GlcNAc β -sp3	6`Sia β LacNAc	0.5
GNZ-0908-BP	Neu5Aca2-6Gal β 1-4(6-O-Su)GlcNAc β -sp3	6`SLN-6-O-sulphate	0.5
GNZ-0909a-BP	4-O-Su-Gal β 1-4GlcNAc β -sp2		1
GNZ-0918a-BP	4,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2	LacNAc-4`,6`-di-O-sulphate	1

BP-Series: Biotinylated Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0921-BP	4-O-Su-GlcNAc β -sp2	β -D-GlcNAc-4-O-sulfate	1
GNZ-0922-BP	GalNAca1-4GalNAca-sp3		1
GNZ-0925-BP	Neu5Aca2-6Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3		1
GNZ-0931-BP	Glc α 1-4Glc α 1-4Glc α 1-4Glc β -sp4	maltotetraose	1
GNZ-0932-BP	Glc α 1-4Glc α 1-4Glc β -sp4	maltotriose	1
GNZ-0934-BP	6-O-Su-GalNAc β 1-4(3-O-Ac)GlcNAc β -sp3	3-O-Ac-LacdiNAc-6`-sulphate	1
GNZ-0935-BP	4,6-O-Su ₂ -GalNAc β 1-4GlcNAc β -sp3	LacdiNAc-4`,6`-di-O-sulphate	1
GNZ-0936-BP	4-O-Su-GalNAc β 1-4GlcNAc β -sp3		1
GNZ-0937-BP	6-O-Su-GalNAc β 1-4GlcNAc β -sp3	6`-O-su-LacdiNAc	1
GNZ-0941-BP	3-O-Su-GlcNAc β -sp3	β -D-GlcNAc-3-O-sulfate	1
GNZ-0946-BP	Man α 1-4Man β -sp4		1
GNZ-0949-BP	Neu5Aca2-3Gal β 1-3(6-O-Su)GlcNAc β -sp3	3`SiaLe ^c -6-O-sulphate	0.5
GNZ-0951-BP	Neu5Aca2-3Gal β 1-4(6-O-Su)GlcNAc β -sp3	3`SLN-6-O-sulphate	0.5
GNZ-0952-BP	3-O-Su-GalNAc β -sp3	β -D-GalNAc-3-O-sulfate	1
GNZ-0953-BP	4-O-Su-GalNAc β -sp3	β -D-GalNAc-4-O-sulfate	1
GNZ-0955-BP	Gal β 1-4(Gal β 1-3)GlcNAc β -sp3		1
GNZ-0956-BP	Neu5Gca2-3Gal β 1-4GlcNAc β -sp3	3`Sia(Gc)LacNAc	0.5
GNZ-0957-BP	Neu5Gca2-6Gal β 1-4GlcNAc β -sp3	6`Sia(Gc)LacNAc	0.5
GNZ-0958-BP	GlcNAc β 1-3Gal β 1-4GlcNAc β -sp2	GlcNAc β 3`LacNAc	1
GNZ-0958a-BP	GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3	GlcNAc β 3`LacNAc	1
GNZ-0959-BP	Glc α 1-6Glc α 1-6Glc β -sp4	Isomaltotriose	1
GNZ-0966-BP	Gal α 1-3(Fuca1-2)Gal β 1-3(Fuca1-4)GlcNAc β -sp3	BLe ^b	1
GNZ-0967-BP	GalNAca1-3(Fuca1-2)Gal β 1-4(Fuca1-3)GlcNAc β -sp3	ALe ^y	1
GNZ-0968-BP	Gal α 1-3(Fuca1-2)Gal β 1-4(Fuca1-3)GlcNAc β -sp3	BLe ^y	0.5
GNZ-0972-BP	GlcNAc β 1-4[3-O-CH(CH ₃)COOH]GlcNAc β -sp4	GlcNAc-Mur	1
GNZ-0973-BP	GlcNAc β 1-4[3-O-CH(CH ₃)COOH]GlcNAca-sp4		1
GNZ-0976-BP	GlcA β 1-3Gal β -sp3	GlcA3Gal	1
GNZ-0977-BP	Neu5Aca2-6(Gal α 1-3)GalNAca-sp3	6SiaT _{aa}	0.5
GNZ-0978-BP	GlcA β 1-6Gal β -sp3	GlcA β 6Gal	1
GNZ-0980-BP	Gal β 1-4GlcNAc β 1-6(Gal β 1-3)GalNAca-sp3	LacNAc6TF	0.5
GNZ-0982-BP	GlcNAc β 1-4GlcNA β 1-4GlcNAc β -sp4	chitotriose	1
GNZ-0984-BP	Neu5Aca2-6(Gal β 1-3)GalNAca-sp3	6SiaTF	0.5
GNZ-0985-BP	Neu5Ac β 2-6(Gal β 1-3)GalNAca-sp3	6Sia β TF	0.5
GNZ-0986-BP	Neu5Ac β 2-6GalNAca-sp3	Sia β T _n	0.5
GNZ-0991-BP	Gal α 1-4GalNAca-sp3		1
GNZ-0993-BP	Neu5Aca2-3GalNAca-sp3	3-SiaT _n	0.5
GNZ-0995-BP	Gal β 1-4GlcNA β 1-3GalNAca-sp3	LacNAc3T _n	1
GNZ-0996-BP	Gal β 1-4GlcNA β 1-6GalNAca-sp3	LacNAc6T _n	1
GNZ-0997-BP	Neu5Aca2-6Gal β 1-4GlcNAc β -sp3	6`SLN	1
GNZ-0998-BP	6-O-Su-GalNAca-sp3	α -D-GalNAc-6-O-sulfate	1

FP-Series: Fluorescein-Labelled Polymeric Probes

These probes are designed to reveal lectins, including selectins, directly on cell membranes, organelles, and in cytoplasm. The low fluorescein content ensures that probe solubility in water is not effected, but still allows reliable probe detection. The affinity of the probes is 10^2 to 10^5 times higher than that of corresponding free sugars.

PAA is poly[N-(2-hydroxyethyl)acrylamide], a flexible polymer chain which serves as an additional spacer. Used as a molecular weight carrier, PAA demonstrates an absence of non-specific interaction with cells, and is stable to chemical and proteolytic action.


Molecular mass: approx. 30 kDa

Content: carbohydrate 20% mol.

Purity: synthetic ω -aminoalkyl glycosides used for coupling with the polymer have a purity of >95% (HPLC and $^1\text{H-NMR}$)

Applications:

- Flow cytometry
- Fluorescence microscopy



Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0000-FP	HOCH ₂ (HOCH) ₄ CH ₂ NH ₂ -PAA-fluo	aminoglucitol	0.4
GNZ-0001-FP	GalNAc β 1-4GlcNAc β -sp3-PAA-fluo	LacdiNac	0.4
GNZ-0004-FP	GlcNAc β 1-3(GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2-PAA-fluo	Tk	0.4
GNZ-0006-FP	GalNAca1-3(Fuca1-2)Gal β 1-4GlcNAc β -sp3-PAA-fluo	A (type 2)	0.4
GNZ-0007-FP	Gal α 1-3(Fuca1-2)Gal β 1-4GlcNAc β -sp3-PAA-fluo	B (type 2)	0.4
GNZ-0008-FP	Gal α 1-4Gal β 1-4GlcNAc β -sp3-PAA-fluo	P ₁	0.4
GNZ-0009-FP	Gal α 1-3Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-fluo		0.4
GNZ-0011-FP	GlcNAc β 1-2Gal β 1-3GalNAca-sp3-PAA-fluo	GlcNAc β 1-2`TF	0.4
GNZ-0012-FP	GlcA β -sp3-PAA-fluo	β -glucuronate	0.4
GNZ-0013-FP	Glc β 1-4GalNAca-sp3-PAA-fluo		0.4
GNZ-0014-FP	Man β -sp4-PAA-fluo	β -D-mannose	0.4
GNZ-0015-FP	Gal α 1-4GlcNAc β -sp3-PAA-fluo	α LN	0.4
GNZ-0015a-FP	Gal α 1-4GlcNAc β -sp8-PAA-fluo	α LN	0.4
GNZ-0016-FP	Neu5Ac β -sp9-PAA-fluo	β -N-acetylneuraminic acid	0.4
GNZ-0017-FP	Neu5Aca2-3(6-O-Su-)Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-fluo	SiaLe ^x -6 ^(Gal) -O-sulfate	0.2
GNZ-0018-FP	Neu5Gca-sp3-PAA-fluo	α -N-glycolylneuraminic acid	0.4
GNZ-0019-FP	Glc α 1-4Glc β -sp3-PAA-fluo	maltose	0.4
GNZ-0020-FP	Neu5Aca2-3Gal β 1-4(Fuca1-3)(6-O-Su-)GlcNAc β -sp3-PAA-fluo	SiaLe ^x -6 ^(GlcNAc) -O-sulfate	0.2
GNZ-0021-FP	Glc α -sp3-PAA-fluo	α -D-glucose	0.4
GNZ-0022-FP	Glc β -sp3-PAA-fluo	β -D-glucose	0.4
GNZ-0022b-FP	Glc β -sp4-PAA-fluo		0.4
GNZ-0023-FP	Gal α -sp3-PAA-fluo	α -D-galactose	0.4
GNZ-0024-FP	Gal β -sp3-PAA-fluo	β -D-galactose	0.4
GNZ-0024a-FP	Gal β -sp4-PAA-fluo		0.4
GNZ-0025a-FP	Mana-sp3-PAA-fluo	α -mannose	0.4
GNZ-0026-FP	6-H ₂ PO ₃ -Mana-sp3-PAA-fluo	α -D-mannose-6-phosphate	0.4
GNZ-0027-FP	L-Fuca-sp3-PAA-fluo	α -L-fucose	0.4

FP-Series: Fluorescein-Labelled Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0028-FP	L-Rhaa-sp3-PAA-fluo	α -L-rhamnose	0.4
GNZ-0029-FP	GlcNAc β -sp3-PAA-fluo	β -D-N-acetylglucosamine	0.4
GNZ-0029a-FP	GlcNAc β -sp2-PAA-fluo		0.4
GNZ-0029d-FP	GlcNAc β -sp4-PAA-fluo		0.4
GNZ-0033-FP	Gala1-4Gal β -sp3-PAA-fluo		0.4
GNZ-0034-FP	3-O-Su-Gal β -sp3-PAA-fluo	β -D-galactose-3-O-sulfate	0.4
GNZ-0035-FP	Neu5Aca-sp3-PAA-fluo	α -N-acetylneuraminic acid	0.4
GNZ-0035a-FP	Neu5Aca-sp9-PAA-fluo	α -N-acetylneuraminic acid	0.4
GNZ-0036-FP	Neu5Aca2-3Gal β 1-4GlcNAc β -sp3-PAA-fluo	3`SLN	0.2
GNZ-0037-FP	Gala1-4Gal β 1-4Glc β -sp2-PAA-fluo	P ^k , Gb3, GbOse3	0.2
GNZ-0038-FP	Gala1-3GalNAc β -sp3-PAA-fluo	T _{0B}	0.4
GNZ-0039-FP	Gal β 1-3Gal β -sp3-PAA-fluo		0.4
GNZ-0040-FP	Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-fluo	Le ^a	0.4
GNZ-0041-FP	Fuca1-2Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-fluo	Le ^b	0.4
GNZ-0042-FP	Fuca1-2Gal β 1-3GlcNAc β -sp3-PAA-fluo	Le ^d , H (type 1)	0.4
GNZ-0043-FP	Gal β 1-3GlcNAc β -sp3-PAA-fluo	Le ^e	0.4
GNZ-0044-FP	Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-fluo	Le ^x	0.4
GNZ-0045-FP	Fuca1-2Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-fluo	Le ^y	0.4
GNZ-0046a-FP	Gal β 1-4Glc β -sp2-PAA-fluo	Lac	0.4
GNZ-0047-FP	Gal β 1-4GlcNAc β -sp3-PAA-fluo	N-acetyllactosamine	0.4
GNZ-0047d-FP	Gal β 1-4GlcNAc β -sp2-PAA-fluo	N-acetyllactosamine	0.4
GNZ-0048-FP	Gal β 1-3GalNAca-sp3-PAA-fluo	TF, core 1	0.4
GNZ-0049-FP	Fuca1-3GlcNAc β -sp3-PAA-fluo		0.4
GNZ-0050-FP	Fuca1-4GlcNAc β -sp3-PAA-fluo	Le	0.4
GNZ-0051-FP	GalNAca1-3GalNAc β -sp3-PAA-fluo	Fs	0.4
GNZ-0052-FP	GalNAca1-3GalNAca-sp3-PAA-fluo	core 5	0.4
GNZ-0053-FP	Gala1-3GalNAca-sp3-PAA-fluo	T _{00r} , core 8	0.4
GNZ-0054-FP	Neu5Aca2-3Gal β 1-3GlcNAc β -sp3-PAA-fluo	SiaLe ^c	0.2
GNZ-0055-FP	Gala1-2Gal β -sp3-PAA-fluo		0.4
GNZ-0056-FP	Gal β 1-3GalNAc β -sp3-PAA-fluo	T _{0B}	0.4
GNZ-0057-FP	GlcNAc β 1-4GlcNAc β -sp3-PAA-fluo	chitobiose	0.4
GNZ-0057a-FP	GlcNAc β 1-4GlcNAc β -sp4-PAA-fluo	chitobiose	0.4
GNZ-0058-FP	Neu5Aca2-6GalNAca-sp3-PAA-fluo	SiaT _n	0.2
GNZ-0059-FP	Fuca1-2Gal β 1-3GalNAca-sp3-PAA-fluo	H (type 3)	0.4
GNZ-0060-FP	Neu5Aca2-3Gal β 1-4Glc β -sp4-PAA-fluo	3`SL	0.2
GNZ-0061-FP	Neu5Ac&aptha;2-3Gal β 1-3(Fuca1-4)GlcNAc β -sp3	SiaLe ^a	0.2
GNZ-0062-FP	Neu5Aca2-3Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-fluo	SiaLe ^x	0.2
GNZ-0063a-FP	Neu5Aca2-6Gal β 1-4Glc β -sp2-PAA-fluo	6`SL	0.2
GNZ-0064-FP	6-O-Su-GlcNAc β -sp3-PAA-fluo	β -D-GlcNAc-6-O-sulfate	0.4
GNZ-0065-FP	3-O-Su-Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA-fluo	suLe ^a	0.2
GNZ-0066-FP	3-O-Su-Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA-fluo	suLe ^x	0.2
GNZ-0067a-FP	3-O-Su-Gal β 1-4GlcNAc β -sp2-PAA-fluo		0.4
GNZ-0068-FP	3-O-Su-Gal β 1-3GlcNAc β -sp3-PAA-fluo	Lec-3`-O-sulphate	0.4
GNZ-0070-FP	Gala1-3Gal β 1-4GlcNAc β -sp3-PAA-fluo	Galili	0.4
GNZ-0071-FP	GlcNAc β 1-4GalNAca-sp3-PAA-fluo		0.4
GNZ-0073-FP	Neu5Aca2-8Neu5Aca2-8Neu5Aca-sp3-PAA-fluo	(Sia) ₃	0.4
GNZ-0075-FP	GlcNAc β 1-3Gal β 1-3GalNAca-sp3-PAA-fluo	GlcNAc β 1-3`TF	0.4
GNZ-0076-FP	Gal β 1-2Gal β -sp3-PAA-fluo		0.4
GNZ-0077a-FP	Gal β 1-4(6-O-Su)GlcNAc β -sp2-PAA-fluo		0.4
GNZ-0078-FP	GlcNAc β 1-6(Gal β 1-3)GalNAca-sp3-PAA-fluo	core 2	0.4

FP-Series: Fluorescein-Labelled Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0079-FP	Galβ1-4GlcNAcβ1-3Galβ1-4GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3-PAA-fluo	(LN) ₃	0.4
GNZ-0080-FP	Fuca1-2Galβ1-3GalNAcβ-sp3-PAA-fluo	H (type 4)	0.4
GNZ-0082-FP	Galβ1-4GlcNAcβ1-3Galβ1-4Glcβ-sp4-PAA-fluo	LNnT	0.4
GNZ-0083-FP	Neu5Aca2-3Galβ-sp3-PAA-fluo	GM4	0.4
GNZ-0084-FP	Neu5Aca2-6Galβ-sp3-PAA-fluo		0.2
GNZ-0085-FP	GalNAca1-3(Fuca1-2)Galβ-sp3-PAA-fluo	A _{tri}	0.4
GNZ-0085a-FP	GalNAca1-3(Fucα1-2)Galβ-sp5-PAA-fluo	A _{tri}	0.4
GNZ-0086-FP	Galα1-3(Fuca1-2)Galβ-sp3-PAA-fluo	B _{tri}	0.4
GNZ-0086a-FP	Galα1-3(Fuca1-2)Galβ-sp5-PAA-fluo	B _{tri}	0.4
GNZ-0087-FP	GalNAca1-3Galβ-sp3-PAA-fluo	A _{di}	0.4
GNZ-0088-FP	Galα1-3Galβ-sp3-PAA-fluo	B _{di}	0.4
GNZ-0089-FP	Fuca1-2Galβ1-4GlcNAcβ-sp3-PAA-fluo	H (type 2)	0.4
GNZ-0090a-FP	6-O-Su-Galβ1-4GlcNAcβ-sp2-PAA-fluo	LacNAc-6-O-sulfate	0.4
GNZ-0091-FP	Fuca1-2Galβ-sp3-PAA-fluo	H _{di}	0.4
GNZ-0092-FP	3-O-Su-Galβ1-3GalNAca-sp3-PAA-fluo	TF-3`-O-sulphate	0.4
GNZ-0093a-FP	GalNAcβ1-4(6-O-Su)GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0095-FP	GalNAcβ1-3GalNAcβ-sp3-PAA-fluo	para-Fs	0.4
GNZ-0096-FP	Neu5Aca2-3Galβ1-3GalNAca-sp3-PAA-fluo	3` SiaTF	0.4
GNZ-0097-FP	GlcNAcβ1-3GalNAca-sp3-PAA-fluo	core 3	0.4
GNZ-0098-FP	GlcNAcβ1-6GalNAca-sp3-PAA-fluo	core 6	0.4
GNZ-0099-FP	GlcNAcβ1-3(GlcNAcβ1-6)GalNAca-sp3-PAA-fluo	core 4	0.4
GNZ-0600-FP	Glcβ1-3GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0602-FP	Glcβ1-3GalNAcβ-sp3-PAA-fluo		0.4
GNZ-0605-FP	GlcNAcβ1-2Galβ-sp3-PAA-fluo		0.4
GNZ-0607-FP	Fucβ1-2Galβ1-3GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0608-FP	GlcNAcβ1-4Galβ-sp3-PAA-fluo	GlcNAcβ4Galβ	0.4
GNZ-0609-FP	L-Glcβ-sp4-PAA-fluo		0.4
GNZ-0709-FP	Neu5Gca2-3Galβ-sp3-PAA-fluo	Neu5Gca3Gal	0.2
GNZ-0721-FP	GalNAca1-3(Fuca1-2)Galβ1-3GalNAcβ-sp3-PAA-fluo	A (type 4)	0.4
GNZ-0724-FP	GlcNAca1-3GalNAcβ-sp3-PAA-fluo		0.4
GNZ-0726-FP	L-Rhaβ-sp4-PAA-fluo	β-L-rhamnose	0.4
GNZ-0728-FP	GlcNAca-sp3-PAA-fluo	α-D-N-acetylglucosamine	0.4
GNZ-0730-FP	Neu5Gca2-3Galβ1-3(6-O-Su)GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0731-FP	Neu5Gca2-3Galβ1-4(6-O-Su)GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0736-FP	Xylβ-sp4-PAA-fluo	β-D-xylopyranose	0.4
GNZ-0738-FP	L-Araα-sp4-PAA-fluo	α-L-arabinose	0.4
GNZ-0740-FP	Fucβ1-2Galβ1-4GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0744-FP	Ribβ-sp4-PAA-fluo	β-D-ribose	0.4
GNZ-0745-FP	Fucβ1-2Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0747-FP	GalNAca1-3Galβ1-4GlcNAcβ-sp3-PAA-fluo	GalNAca3` LN	0.4
GNZ-0748-FP	GalNAcβ1-3Galβ1-4GlcNAcβ-sp3-PAA-fluo	GalNAcβ3` LN	0.4
GNZ-0755-FP	GalNAca1-3Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0757-FP	Neu5Aca2-6(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA-fluo	Sia6` H(type 2)	0.2
GNZ-0762-FP	6-O-Su-Galβ-sp3-PAA-fluo	β-D-galactose-6-O-sulfate	0.4
GNZ-0763-FP	Neu5Aca2-3(6-O-Su)Galβ1-4(6-O-Su)GlcNAcβ-sp3-PAA-fluo	3` SLN-6,6`-di-O-sulfate	0.2
GNZ-0769-FP	3-O-Su-GalNAca-sp3-PAA-fluo	T _n -3-O-sulfate	0.4
GNZ-0770-FP	GalNGcβ-sp3-PAA-fluo	β-D-N-glycolylgalactosamine	0.4
GNZ-0773-FP	Galβ1-3GalNGca-sp3-PAA-fluo		0.4
GNZ-0778-FP	4-O-Su-GalNAca-sp3-PAA-fluo	T _n -4-O-sulfate	0.4
GNZ-0785-FP	Neu5Aca2-3(6-O-Su)Galβ1-3GalNAca-sp3-PAA-fluo	3` SiaTF-6`-O-sulfate	0.2
GNZ-0786-FP	Galβ1-3GlcNAcβ1-3GalNAca-sp3-PAA-fluo	Le ^e 3T _n	0.4

FP-Series: Fluorescein-Labelled Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0789-FP	Galβ1-3(6-O-Su)GalNAca-sp3-PAA-fluo	TF-6-O-sulfate	0.4
GNZ-0799-FP	Fucβ-sp4-PAA-fluo	β-L-fucose	0.4
GNZ-0800-FP	GalNAca1-4Galβ-sp3-PAA-fluo	GalNAca1-4Galβ	0.4
GNZ-0805-FP	GalNAcβ1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0808-FP	GlcNAcβ1-4(GlcNAcβ1-6)GalNAca-sp3-PAA-fluo		0.4
GNZ-0809-FP	(GlcNAcβ1) ₃ -3,4,6GalNAca-sp3-PAA-fluo		0.4
GNZ-0810-FP	GalNAcβ1-3(Fuca1-2)Galβ-sp3-PAA-fluo		0.4
GNZ-0813-FP	Galβ1-3GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3-PAA-fluo	Le ^c 3`LacNAc	0.4
GNZ-0814-FP	Galβ1-3GlcNAca1-3Galβ1-4GlcNAcβ-sp3-PAA-fluo	Le ^a 3`LacNAc	0.4
GNZ-0815-FP	Galβ1-3GlcNAcβ1-3Galβ1-3GlcNAcβ-sp2-PAA-fluo	Le ^c 3`Lec	0.4
GNZ-0815a-FP	Galβ1-3GlcNAcβ1-3Galβ1-3GlcNAcβ-sp3-PAA-fluo	Le ^c 3`Lec	0.4
GNZ-0816-FP	GalNAca1-3(Fuca1-2)Galβ1-3GlcNAcβ-sp3-PAA-fluo	A (type 1)	0.4
GNZ-0821-FP	6-O-Su-Galβ1-3GalNAca-sp3-PAA-fluo		0.4
GNZ-0822-FP	Galβ1-3(6-O-Su)GlcNAcβ-sp2-PAA-fluo	Le ^c -6-O-sulphate	0.4
GNZ-0822a-FP	Galβ1-3(6-O-Su)GlcNAcβ-sp3-PAA-fluo		0.4
GNZ-0823-FP	Neu5Aca2-3Galβ1-4(2-O-Su-Fuca1-3)(6-O-Su)GlcNAcβ-sp3-PAA-fluo	SLe ^x -6(GlcNAc)-2(Fuc)-di-sulfate	0.2
GNZ-0828-FP	Fuca1-2(3-O-Su)Galβ-sp3-PAA-fluo	H _{di} -3-O-sulphate	0.4
GNZ-0835a-FP	Neu5Aca2-3(GalNAcβ1-4)Galβ1-4Glcβ-sp4-PAA-fluo	GM2	0.2
GNZ-0837-FP	4-O-Su-Galβ-sp3-PAA-fluo	β-D-galactose-4-O-sulfate	0.4
GNZ-0840-FP	6-O-Su-Galβ1-3GlcNAcβ-sp2-PAA-fluo	Le ^c -6`-O-sulphate	0.4
GNZ-0842-FP	Galβ1-3GlcNAcβ1-6Galβ1-4GlcNAcβ-sp2-PAA-fluo	Le ^c 6`LacNAc	0.4
GNZ-0847-FP	Galα1-3(Fuca1-2)Galβ1-3GlcNAcβ-sp3-PAA-fluo	B (type 1)	0.4
GNZ-0848-FP	Galα1-3(Fuca1-2)Galβ1-3GalNAca-sp3	B (type 3)	0.4
GNZ-0849-FP	Galα1-3(Fuca1-2)Galβ1-3GalNAcβ-sp3	B (type 4)	0.4
GNZ-0852-FP	Galα1-3GlcNAcβ-sp3		0.4
GNZ-0854d-FP	(GlcAβ1-3GlcNAcβ1-4) ₁₃ -sp6	hyaluronic acid	0.4
GNZ-0855-FP	GlcNAcβ1-4(6-O-Su)GlcNAβ-sp3	6-O-Su-chitobiose	0.4
GNZ-0857-FP	Galα1-3Galβ1-4GlcNAcβ1-3Galβ-sp3	Galili(tetra)	0.4
GNZ-0859-FP	3-O-Su-Galβ1-4GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3	(3`SuLN)3LN	0.4
GNZ-0860-FP	GalNAca1-3(Fuca1-2)Galβ1-3GalNAca-sp3	A (type 3)	0.4
GNZ-0864-FP	GlcNAca1-3Galβ1-4GlcNAcβ-sp3	GlcNAca3`LacNAc	0.4
GNZ-0864a-FP	GlcNAca1-3Galβ1-4GlcNAcβ-sp2		0.4
GNZ-0865a-FP	Galβ1-3Galβ1-4GlcNAcβ-sp3	Galβ3`LacNAc	0.4
GNZ-0866-FP	Galβ1-4GlcNAcβ1-3(GlcNAcβ1-6)Galβ1-4GlcNAcβ-sp2		0.4
GNZ-0867-FP	Galβ1-4GlcNAcβ1-3(Galβ1-4GlcNAcβ1-6)Galβ1-4GlcNAcβ-sp2		0.4
GNZ-0870-FP	Galβ1-4GlcNAcβ1-3Galβ1-4GlcNAcβ-sp2	LacNAc3`LacNAc	0.4
GNZ-0870a-FP	Galβ1-4GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3		0.4
GNZ-0871-FP	Galβ1-4GlcNAcβ1-6Galβ1-4GlcNAcβ-sp2	LacNAc6`LacNAc	0.4
GNZ-0872-FP	Neu5Gcβ2-6Galβ1-4GlcNAcβ-sp3	6`Sia(Gc)βLacNac	0.2
GNZ-0874-FP	Galβ1-4(Fucβ1-3)GlcNAcβ-sp3		0.4
GNZ-0880-FP	3,6-O-Su ₂ -Galβ1-4(6-O-Su)GlcNAcβ-sp2	LacNAc-3`,6,6`-tri-O-sulphate	0.4
GNZ-0881-FP	3-O-Su-Galβ1-4(6-O-Su)GlcNAcβ-sp3	LacNAc-3`,6-di-O-sulphate	0.4
GNZ-0882-FP	3,4-O-Su ₂ -Galβ1-4GlcNAcβ-sp3	LacNAc-3`,4`-di-O-sulphate	0.4
GNZ-0883-FP	6-O-Su-Galβ1-4(6-O-Su)GlcNAcβ-sp2	LacNAc-6,6`-di-O-sulphate	0.4
GNZ-0884-FP	Mana1-3(Mana1-6)Mana1-6(Mana1-3)Manβ-sp4		0.4
GNZ-0885-FP	6-H ₂ PO ₃ -Glcβ-sp4	β-D-glycose-6-O-phosphate	0.4
GNZ-0886-FP	3,6-O-Su ₂ -Galβ1-4GlcNAcβ-sp2		0.4
GNZ-0887a-FP	GlcNAcβ1-4Galβ1-4GlcNAcβ-sp3	GlcNAc4`LacNAc	0.4
GNZ-0901-FP	6-O-Su-Galβ1-4(6-O-Su)Glcβ-sp2	Lac-6,6`-di-O-sulphate	0.4
GNZ-0902-FP	Glcβ1-6Glcβ-sp4	Gentiobiose	0.4

FP-Series: Fluorescein-Labelled Polymeric Probes

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0907-FP	Neu5Ac β 2-6Gal β 1-4GlcNAc β -sp3	6` Sia β LacNAc	0.2
GNZ-0908-FP	Neu5Ac α 2-6Gal β 1-4(6-O-Su)GlcNAc β -sp3	6` SLN-6-O-sulphate	0.2
GNZ-0909a-FP	4-O-Su-Gal β 1-4GlcNAc β -sp2		0.4
GNZ-0918a-FP	4,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2	LacNAc-4`,6`-di-O-sulphate	0.4
GNZ-0921-FP	4-O-Su-GlcNAc β -sp2	β -D-GlcNAc-4-O-sulfate	0.4
GNZ-0922-FP	GalNAc α 1-4GalNAc α -sp3		0.4
GNZ-0925-FP	Neu5Ac α 2-6Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3		0.4
GNZ-0931-FP	Glc α 1-4Glc α 1-4Glc α 1-4Glc β -sp4	maltotetraose	0.4
GNZ-0932-FP	Glc α 1-4Glc α 1-4Glc β -sp4	maltotriose	0.4
GNZ-0934-FP	6-O-Su-GalNAc β 1-4(3-O-Ac)GlcNAc β -sp3	3-O-Ac-LacdiNAc-6`-sulphate	0.4
GNZ-0935-FP	4,6-O-Su ₂ -GalNAc β 1-4GlcNAc β -sp3	LacdiNAc-4`,6`-di-O-sulphate	0.4
GNZ-0936-FP	4-O-Su-GalNAc β 1-4GlcNAc β -sp3		0.4
GNZ-0937-FP	6-O-Su-GalNAc β 1-4GlcNAc β -sp3	6`-O-su-LacdiNAc	0.4
GNZ-0941-FP	3-O-Su-GlcNAc β -sp3	β -D-GlcNAc-3-O-sulfate	0.4
GNZ-0946-FP	Man α 1-4Man β -sp4		0.4
GNZ-0949-FP	Neu5Ac α 2-3Gal β 1-3(6-O-Su)GlcNAc β -sp3	3` SiaLe ^c -6-O-sulphate	0.2
GNZ-0951-FP	Neu5Ac α 2-3Gal β 1-4(6-O-Su)GlcNAc β -sp3	3` SLN-6-O-sulphate	0.2
GNZ-0952-FP	3-O-Su-GalNAc β -sp3	β -D-GalNAc-3-O-sulfate	0.4
GNZ-0953-FP	4-O-Su-GalNAc β -sp3	β -D-GalNAc-4-O-sulfate	0.4
GNZ-0955-FP	Gal β 1-4(Gal β 1-3)GlcNAc β -sp3		0.4
GNZ-0956-FP	Neu5Gc α 2-3Gal β 1-4GlcNAc β -sp3	3` Sia(Gc)LacNAc	0.2
GNZ-0957-FP	Neu5Gc α 2-6Gal β 1-4GlcNAc β -sp3	6` Sia(Gc)LacNAc	0.2
GNZ-0958-FP	GlcNAc β 1-3Gal β 1-4GlcNAc β -sp2	GlcNAc β 3` LacNAc	0.4
GNZ-0958a-FP	GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3	GlcNAc β 3` LacNAc	0.4
GNZ-0959-FP	Glc α 1-6Glc α 1-6Glc β -sp4	Isomaltotriose	0.4
GNZ-0966-FP	Gal α 1-3(Fuca1-2)Gal β 1-3(Fuca1-4)GlcNAc β -sp3	BLE ^b	0.4
GNZ-0967-FP	GalNAc α 1-3(Fuca1-2)Gal β 1-4(Fuca1-3)GlcNAc β -sp3	ALe ^v	0.4
GNZ-0968-FP	Gal α 1-3(Fuca1-2)Gal β 1-4(Fuca1-3)GlcNAc β -sp3	BLE ^v	0.2
GNZ-0972-FP	GlcNAc β 1-4[3-O-CH(CH ₃)COOH]GlcNAc β -sp4	GlcNAc-Mur	0.4
GNZ-0973-FP	GlcNAc β 1-4[3-O-CH(CH ₃)COOH]GlcNAc α -sp4		0.4
GNZ-0976-FP	GlcA β 1-3Gal β -sp3	GlcA3Gal	0.4
GNZ-0977-FP	Neu5Ac α 2-6(Gal α 1-3)GalNAc α -sp3	6SiaT _{aa}	0.2
GNZ-0978-FP	GlcA β 1-6Gal β -sp3	GlcA β 6Gal	0.4
GNZ-0980-FP	Gal β 1-4GlcNAc β 1-6(Gal β 1-3)GalNAc α -sp3	LacNAc6TF	0.2
GNZ-0982-FP	GlcNAc β 1-4GlcNA β 1-4GlcNAc β -sp4	chitotriose	0.4
GNZ-0984-FP	Neu5Ac α 2-6(Gal β 1-3)GalNAc α -sp3	6SiaTF	0.2
GNZ-0985-FP	Neu5Ac β 2-6(Gal β 1-3)GalNAc α -sp3	6Sia β TF	0.2
GNZ-0986-FP	Neu5Ac β 2-6GalNAc α -sp3	Sia β T _n	0.2
GNZ-0991-FP	Gal α 1-4GalNAc α -sp3		0.4
GNZ-0993-FP	Neu5Ac α 2-3GalNAc α -sp3	3-SiaT _n	0.2
GNZ-0995-FP	Gal β 1-4GlcNA β 1-3GalNAc α -sp3	LacNAc3T _n	0.4
GNZ-0996-FP	Gal β 1-4GlcNA β 1-6GalNAc α -sp3	LacNAc6T _n	0.4
GNZ-0997-FP	Neu5Ac α 2-6Gal β 1-4GlcNAc β -sp3	6` SLN	0.4
GNZ-0998-FP	6-O-Su-GalNAc α -sp3	α -D-GalNAc-6-O-sulfate	0.4

PA-Series: Unlabeled Polyacrylamide Conjugates

This series consists of HOCH₂CH₂NH₃⁺-salts for carboxylates and sulfates. PAA is poly[N-(2-hydroxyethyl)acrylamide], a flexible polymer chain which serves as an additional spacer. The spacer-arm for oligosaccharides is normally -(CH₂)₃-.


Molecular mass: approx. 30 kDa

Content: carbohydrate 20% mol.

Purity: synthetic ω-aminoalkyl glycosides used for coupling with the polymer have a purity of >95% (HPLC and 1H-NMR)

Applications:

- Coating reagent for ELISA and other assays
- Polyvalent inhibitor



Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0000-PA	HOCH ₂ (HOCH) ₄ CH ₂ NH ₂ -PAA	aminoglucitol	1
GNZ-0001-PA	GalNAcβ1-4GlcNAcβ-sp3-PAA	LacdiNAc	1
GNZ-0004-PA	GlcNAcβ1-3(GlcNAcβ1-6)Galβ1-4GlcNAcβ-sp2-PAA	Tk	1
GNZ-0006-PA	GalNAca1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA	A (type 2)	1
GNZ-0007-PA	Galα1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA	B (type 2)	1
GNZ-0008-PA	Galα1-4Galβ1-4GlcNAcβ-sp3-PAA	P ₁	1
GNZ-0009-PA	Galα1-3Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA		1
GNZ-0011-PA	GlcNAcβ1-2Galβ1-3GalNAca-sp3-PAA	GlcNAcβ1-2`TF	1
GNZ-0012-PA	GlcAβ-sp3-PAA	β-glucuronate	1
GNZ-0013-PA	Glcβ1-4GalNAca-sp3-PAA		1
GNZ-0014-PA	Manβ-sp4-PAA	β-D-mannose	1
GNZ-0015-PA	Galα1-4GlcNAcβ-sp3-PAA	αLN	1
GNZ-0015a-PA	Galα1-4GlcNAcβ-sp8-PAA	αLN	1
GNZ-0016-PA	Neu5Acβ-sp9-PAA	β-N-acetylneuraminic acid	1
GNZ-0017-PA	Neu5Aca2-3(6-O-Su-)Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA	SiaLe ^x -6 ^(Gal) -O-sulfate	0.5
GNZ-0018-PA	Neu5Gca-sp3-PAA	α-N-glycolylneuraminic acid	1
GNZ-0019-PA	Glcα1-4Glcβ-sp3-PAA	maltose	1
GNZ-0020-PA	Neu5Aca2-3Galβ1-4(Fuca1-3)(6-O-Su-)GlcNAcβ-sp3-PAA	SiaLe ^x -6 ^(GlcNAc) -O-sulfate	0.5
GNZ-0021-PA	Glcα-sp3-PAA	α-D-glucose	1
GNZ-0022-PA	Glcβ-sp3-PAA	β-D-glucose	1
GNZ-0022b-PA	Glcβ-sp4-PAA		1
GNZ-0023-PA	Galα-sp3-PAA	α-D-galactose	1
GNZ-0024-PA	Galβ-sp3-PAA	β-D-galactose	1
GNZ-0024a-PA	Galβ-sp4-PAA		1
GNZ-0025a-PA	Manα-sp3-PAA	α-mannose	1
GNZ-0026-PA	6-H ₂ PO ₃ -Manα-sp3-PAA	α-D-mannose-6-phosphate	1
GNZ-0027-PA	L-Fuca-sp3-PAA	α-L-fucose	1
GNZ-0028-PA	L-Rhaα-sp3-PAA	α-L-rhamnose	1
GNZ-0029-PA	GlcNAcβ-sp3-PAA	β-D-N-acetylglucosamine	1
GNZ-0029a-PA	GlcNAcβ-sp2-PAA		1

PA-Series: Unlabeled Polyacrylamide Conjugates

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0029d-PA	GlcNAc β -sp4-PAA		1
GNZ-0033-PA	Gal α 1-4Gal β -sp3-PAA		1
GNZ-0034-PA	3-O-Su-Gal β -sp3-PAA	β -D-galactose-3-O-sulfate	1
GNZ-0035-PA	Neu5Aca-sp3-PAA	α -N-acetylneuraminic acid	1
GNZ-0035a-PA	Neu5Aca-sp9-PAA	α -N-acetylneuraminic acid	1
GNZ-0036-PA	Neu5Aca2-3Gal β 1-4GlcNAc β -sp3-PAA	3`SLN	0.5
GNZ-0037-PA	Gal α 1-4Gal β 1-4Glc β -sp2-PAA	P ^k , Gb3, GbOse3	1
GNZ-0038-PA	Gal α 1-3GalNAc β -sp3-PAA	T _{0β}	1
GNZ-0039-PA	Gal β 1-3Gal β -sp3-PAA		1
GNZ-0040-PA	Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA	Le ^a	1
GNZ-0041-PA	Fuca1-2Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA	Le ^b	1
GNZ-0042-PA	Fuca1-2Gal β 1-3GlcNAc β -sp3-PAA	Le ^d , H (type 1)	1
GNZ-0043-PA	Gal β 1-3GlcNAc β -sp3-PAA	Le ^c	1
GNZ-0044-PA	Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA	Le ^x	1
GNZ-0045-PA	Fuca1-2Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA	Le ^y	1
GNZ-0046a-PA	Gal β 1-4Glc β -sp2-PAA	Lac	1
GNZ-0047-PA	Gal β 1-4GlcNAc β -sp3-PAA	N-acetyllactosamine	1
GNZ-0047d-PA	Gal β 1-4GlcNAc β -sp2-PAA	N-acetyllactosamine	1
GNZ-0048-PA	Gal β 1-3GalNAca-sp3-PAA	TF, core 1	1
GNZ-0049-PA	Fuca1-3GlcNAc β -sp3-PAA		1
GNZ-0050-PA	Fuca1-4GlcNAc β -sp3-PAA	Le	1
GNZ-0051-PA	GalNAca1-3GalNAc β -sp3-PAA	Fs	1
GNZ-0052-PA	GalNAca1-3GalNAca-sp3-PAA	core 5	1
GNZ-0053-PA	Gal α 1-3GalNAca-sp3-PAA	T _{0α} , core 8	1
GNZ-0054-PA	Neu5Aca2-3Gal β 1-3GlcNAc β -sp3-PAA	SiaLe ^c	0.5
GNZ-0055-PA	Gal α 1-2Gal β -sp3-PAA		1
GNZ-0056-PA	Gal β 1-3GalNAc β -sp3-PAA	T _{$\beta\beta$}	1
GNZ-0057-PA	GlcNAc β 1-4GlcNAc β -sp3-PAA	chitobiose	1
GNZ-0057a-PA	GlcNAc β 1-4GlcNAc β -sp4-PAA	chitobiose	1
GNZ-0058-PA	Neu5Aca2-6GalNAca-sp3-PAA	SiaT _n	0.5
GNZ-0059-PA	Fuca1-2Gal β 1-3GalNAca-sp3-PAA	H (type 3)	1
GNZ-0060-PA	Neu5Aca2-3Gal β 1-4Glc β -sp4-PAA	3`SL	0.5
GNZ-0061-PA	Neu5Acα2-3Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA	SiaLe ^a	0.5
GNZ-0062-PA	Neu5Aca2-3Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA	SiaLe ^x	0.5
GNZ-0063a-PA	Neu5Aca2-6Gal β 1-4Glc β -sp2-PAA	6`SL	0.5
GNZ-0064-PA	6-O-Su-GlcNAc β -sp3-PAA	β -D-GlcNAc-6-O-sulfate	1
GNZ-0065-PA	3-O-Su-Gal β 1-3(Fuca1-4)GlcNAc β -sp3-PAA	suLe ^a	0.5
GNZ-0066-PA	3-O-Su-Gal β 1-4(Fuca1-3)GlcNAc β -sp3-PAA	suLe ^x	0.5
GNZ-0067a-PA	3-O-Su-Gal β 1-4GlcNAc β -sp2-PAA		1
GNZ-0068-PA	3-O-Su-Gal β 1-3GlcNAc β -sp3-PAA	Lec-3`-O-sulphate	1
GNZ-0070-PA	Gal α 1-3Gal β 1-4GlcNAc β -sp3-PAA	Galili	1
GNZ-0071-PA	GlcNAc β 1-4GalNAca-sp3-PAA		1
GNZ-0073-PA	Neu5Aca2-8Neu5Aca2-8Neu5Aca-sp3-PAA	(Sia) ₃	1
GNZ-0075-PA	GlcNAc β 1-3Gal β 1-3GalNAca-sp3-PAA	GlcNAc β 1-3`TF	1
GNZ-0076-PA	Gal β 1-2Gal β -sp3-PAA		1
GNZ-0077a-PA	Gal β 1-4(6-O-Su)GlcNAc β -sp2-PAA		1
GNZ-0078-PA	GlcNAc β 1-6(Gal β 1-3)GalNAca-sp3-PAA	core 2	1
GNZ-0079-PA	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3-PAA	(LN) ₃	1
GNZ-0080-PA	Fuca1-2Gal β 1-3GalNAc β -sp3-PAA	H (type 4)	1
GNZ-0082-PA	Gal β 1-4GlcNAc β 1-3Gal β 1-4Glc β -sp4-PAA	LNnT	1
GNZ-0083-PA	Neu5Aca2-3Gal β -sp3-PAA	GM4	1

PA-Series: Unlabeled Polyacrylamide Conjugates

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0084-PA	Neu5Aca2-6Galβ-sp3-PAA		0.5
GNZ-0085-PA	GalNAca1-3(Fuca1-2)Galβ-sp3-PAA	A _{tri}	1
GNZ-0085a-PA	GalNAca1-3(Fucα1-2)Galβ-sp5-PAA	A _{tri}	1
GNZ-0086-PA	Galα1-3(Fuca1-2)Galβ-sp3-PAA	B _{tri}	1
GNZ-0086a-PA	Galα1-3(Fuca1-2)Galβ-sp5-PAA	B _{tri}	1
GNZ-0087-PA	GalNAca1-3Galβ-sp3-PAA	A _{di}	1
GNZ-0088-PA	Galα1-3Galβ-sp3-PAA	B _{di}	1
GNZ-0089-PA	Fuca1-2Galβ1-4GlcNAcβ-sp3-PAA	H (type 2)	1
GNZ-0090a-PA	6-O-Su-Galβ1-4GlcNAcβ-sp2-PAA	LacNAc-6-O-sulfate	1
GNZ-0091-PA	Fuca1-2Galβ-sp3-PAA	H _{di}	1
GNZ-0092-PA	3-O-Su-Galβ1-3GalNAca-sp3-PAA	TF-3`-O-sulphate	1
GNZ-0093a-PA	GalNAcβ1-4(6-O-Su)GlcNAcβ-sp3-PAA		1
GNZ-0095-PA	GalNAcβ1-3GalNAcβ-sp3-PAA	para-Fs	1
GNZ-0096-PA	Neu5Aca2-3Galβ1-3GalNAca-sp3-PAA	3` SiaTF	1
GNZ-0097-PA	GlcNAcβ1-3GalNAca-sp3-PAA	core 3	1
GNZ-0098-PA	GlcNAcβ1-6GalNAca-sp3-PAA	core 6	1
GNZ-0099-PA	GlcNAcβ1-3(GlcNAcβ1-6)GalNAca-sp3-PAA	core 4	1
GNZ-0600-PA	Glcβ1-3GlcNAcβ-sp3-PAA		1
GNZ-0602-PA	Glcβ1-3GalNAcβ-sp3-PAA		1
GNZ-0605-PA	GlcNAcβ1-2Galβ-sp3-PAA		1
GNZ-0607-PA	Fucβ1-2Galβ1-3GlcNAcβ-sp3-PAA		1
GNZ-0608-PA	GlcNAcβ1-4Galβ-sp3-PAA	GlcNAcβ4Galβ	1
GNZ-0609-PA	L-Glcβ-sp4-PAA		1
GNZ-0709-PA	Neu5Gca2-3Galβ-sp3-PAA	Neu5Gca3Gal	0.5
GNZ-0721-PA	GalNAca1-3(Fuca1-2)Galβ1-3GalNAcβ-sp3-PAA	A (type 4)	1
GNZ-0724-PA	GlcNAca1-3GalNAcβ-sp3-PAA		1
GNZ-0726-PA	L-Rhaβ-sp4-PAA	β-L-rhamnose	1
GNZ-0728-PA	GlcNAca-sp3-PAA	α-D-N-acetylglucosamine	1
GNZ-0730-PA	Neu5Gca2-3Galβ1-3(6-O-Su)GlcNAcβ-sp3-PAA		1
GNZ-0731-PA	Neu5Gca2-3Galβ1-4(6-O-Su)GlcNAcβ-sp3-PAA		1
GNZ-0736-PA	Xylβ-sp4-PAA	β-D-xylopyranose	1
GNZ-0738-PA	L-Araα-sp4-PAA	α-L-arabinose	1
GNZ-0740-PA	Fucβ1-2Galβ1-4GlcNAcβ-sp3-PAA		1
GNZ-0744-PA	Ribβ-sp4-PAA	β-D-ribose	1
GNZ-0745-PA	Fucβ1-2Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA		1
GNZ-0747-PA	GalNAca1-3Galβ1-4GlcNAcβ-sp3-PAA	GalNAca3` LN	1
GNZ-0748-PA	GalNAcβ1-3Galβ1-4GlcNAcβ-sp3-PAA	GalNAcβ3` LN	1
GNZ-0755-PA	GalNAca1-3Galβ1-4(Fuca1-3)GlcNAcβ-sp3-PAA		1
GNZ-0757-PA	Neu5Aca2-6(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA	Sia6` H(type 2)	0.5
GNZ-0762-PA	6-O-Su-Galβ-sp3-PAA	β-D-galactose-6-O-sulfate	1
GNZ-0763-PA	Neu5Aca2-3(6-O-Su)Galβ1-4(6-O-Su)GlcNAcβ-sp3-PAA	3` SLN-6,6` -di-O-sulfate	0.5
GNZ-0769-PA	3-O-Su-GalNAca-sp3-PAA	T _n -3-O-sulfate	1
GNZ-0770-PA	GalNGcβ-sp3-PAA	β-D-N-glycolylgalactosamine	1
GNZ-0773-PA	Galβ1-3GalNGca-sp3-PAA		1
GNZ-0778-PA	4-O-Su-GalNAca-sp3-PAA	T _n -4-O-sulfate	1
GNZ-0785-PA	Neu5Aca2-3(6-O-Su)Galβ1-3GalNAca-sp3-PAA	3` SiaTF-6` -O-sulfate	0.5
GNZ-0786-PA	Galβ1-3GlcNAcβ1-3GalNAca-sp3-PAA	Le ^c T _n	1
GNZ-0789-PA	Galβ1-3(6-O-Su)GalNAca-sp3-PAA	TF-6-O-sulfate	1
GNZ-0799-PA	Fucβ-sp4-PAA	β-L-fucose	1
GNZ-0800-PA	GalNAca1-4Galβ-sp3-PAA	GalNAca1-4Galβ	1
GNZ-0805-PA	GalNAcβ1-3(Fuca1-2)Galβ1-4GlcNAcβ-sp3-PAA		1

PA-Series: Unlabeled Polyacrylamide Conjugates


Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0808-PA	GlcNAc β 1-4(GlcNAc β 1-6)GalNAca-sp3-PAA		1
GNZ-0809-PA	(GlcNAc β 1) ₃ -3,4,6GalNAca-sp3-PAA		1
GNZ-0810-PA	GalNAc β 1-3(Fuca1-2)Gal β -sp3-PAA		1
GNZ-0813-PA	Gal β 1-3GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3-PAA	Le ^c 3` LacNAc	1
GNZ-0814-PA	Gal β 1-3GlcNAca1-3Gal β 1-4GlcNAc β -sp3-PAA	Le ^c 3` LacNAc	1
GNZ-0815-PA	Gal β 1-3GlcNAc β 1-3Gal β 1-3GlcNAc β -sp2-PAA	Le ^c 3` Le ^c	1
GNZ-0815a-PA	Gal β 1-3GlcNAc β 1-3Gal β 1-3GlcNAc β -sp3-PAA	Le ^c 3` Le ^c	1
GNZ-0816-PA	GalNAca1-3(Fuca1-2)Gal β 1-3GlcNAc β -sp3-PAA	A (type 1)	1
GNZ-0821-PA	6-O-Su-Gal β 1-3GalNAca-sp3-PAA		1
GNZ-0822-PA	Gal β 1-3(6-O-Su)GlcNAc β -sp2-PAA	Le ^c -6-O-sulphate	1
GNZ-0822a-PA	Gal β 1-3(6-O-Su)GlcNAc β -sp3-PAA		1
GNZ-0823-PA	Neu5Aca2-3Gal β 1-4(2-O-Su-Fuca1-3)(6-O-Su)GlcNAc β -sp3-PAA	SLe ^x -6(GlcNAc)-2(Fuc)-di-sulfate	0.5
GNZ-0828-PA	Fuca1-2(3-O-Su)Gal β -sp3-PAA	H _{di} -3-O-sulphate	1
GNZ-0835a-PA	Neu5Aca2-3(GalNAc β 1-4)Gal β 1-4Glc β -sp4-PAA	GM2	0.5
GNZ-0837-PA	4-O-Su-Gal β -sp3-PAA	β -D-galactose-4-O-sulfate	1
GNZ-0840-PA	6-O-Su-Gal β 1-3GlcNAc β -sp2-PAA	Le ^c -6`-O-sulphate	1
GNZ-0842-PA	Gal β 1-3GlcNAc β 1-6Gal β 1-4GlcNAc β -sp2-PAA	Le ^c 6` LacNAc	1
GNZ-0847-PA	Gal α 1-3(Fuca1-2)Gal β 1-3GlcNAc β -sp3-PAA	B (type 1)	1
GNZ-0848-PA	Gal α 1-3(Fuca1-2)Gal β 1-3GalNAca-sp3	B (type 3)	1
GNZ-0849-PA	Gal α 1-3(Fuca1-2)Gal β 1-3GalNAc β -sp3	B (type 4)	1
GNZ-0852-PA	Gal α 1-3GlcNAc β -sp3		1
GNZ-0854d-PA	(GlcA β 1-3GlcNAc β 1-4)13-sp6	hyaluronic acid	1
GNZ-0855-PA	GlcNAc β 1-4(6-O-Su)GlcNA β -sp3	6-O-Su-chitobiose	1
GNZ-0857-PA	Gal α 1-3Gal β 1-4GlcNAc β 1-3Gal β -sp3	Galili(tetra)	1
GNZ-0859-PA	3-O-Su-Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3	(3` SuLN)3LN	1
GNZ-0860-PA	GalNAca1-3(Fuca1-2)Gal β 1-3GalNAca-sp3	A (type 3)	1
GNZ-0864-PA	GlcNAca1-3Gal β 1-4GlcNAc β -sp3	GlcNAca3` LacNAc	1
GNZ-0864a-PA	GlcNAca1-3Gal β 1-4GlcNAc β -sp2		1
GNZ-0865a-PA	Gal β 1-3Gal β 1-4GlcNAc β -sp3	Gal β 3`LacNAc	1
GNZ-0866-PA	Gal β 1-4GlcNAc β 1-3(GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2		1
GNZ-0867-PA	Gal β 1-4GlcNAc β 1-3(Gal β 1-4GlcNAc β 1-6)Gal β 1-4GlcNAc β -sp2		1
GNZ-0870-PA	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp2	LacNAc3` LacNAc	1
GNZ-0870a-PA	Gal β 1-4GlcNAc β 1-3Gal β 1-4GlcNAc β -sp3		1
GNZ-0871-PA	Gal β 1-4GlcNAc β 1-6Gal β 1-4GlcNAc β -sp2	LacNAc6` LacNAc	1
GNZ-0872-PA	Neu5Gc β 2-6Gal β 1-4GlcNAc β -sp3	6` Sia(Gc) β LacNac	0.5
GNZ-0874-PA	Gal β 1-4(Fuc β 1-3)GlcNAc β -sp3		1
GNZ-0880-PA	3,6-O-Su ₂ -Gal β 1-4(6-O-Su)GlcNAc β -sp2	LacNAc-3`,6,6`-tri-O-sulphate	1
GNZ-0881-PA	3-O-Su-Gal β 1-4(6-O-Su)GlcNAc β -sp3	LacNAc-3`,6-di-O-sulphate	1
GNZ-0882-PA	3,4-O-Su ₂ -Gal β 1-4GlcNAc β -sp3	LacNAc-3`,4`-di-O-sulphate	1
GNZ-0883-PA	6-O-Su-Gal β 1-4(6-O-Su)GlcNAc β -sp2	LacNAc-6,6`-di-O-sulphate	1
GNZ-0884-PA	Mana1-3(Mana1-6)Mana1-6(Mana1-3)Man β -sp4		1
GNZ-0885-PA	6-H ₂ PO ₃ -Glc β -sp4	β -D-glycose-6-O-phosphate	1
GNZ-0886-PA	3,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2		1
GNZ-0887a-PA	GlcNAc β 1-4Gal β 1-4GlcNAc β -sp3	GlcNAc4` LacNAc	1
GNZ-0901-PA	6-O-Su-Gal β 1-4(6-O-Su)Glc β -sp2	Lac-6,6`-di-O-sulphate	1
GNZ-0902-PA	Glc β 1-6Glc β -sp4	Gentiobiose	1
GNZ-0907-PA	Neu5Ac β 2-6Gal β 1-4GlcNAc β -sp3	6` Sia β LacNAc	0.5
GNZ-0908-PA	Neu5Aca2-6Gal β 1-4(6-O-Su)GlcNAc β -sp3	6` SLN-6-O-sulphate	0.5
GNZ-0909a-PA	4-O-Su-Gal β 1-4GlcNAc β -sp2		1
GNZ-0918a-PA	4,6-O-Su ₂ -Gal β 1-4GlcNAc β -sp2	LacNAc-4`,6`-di-O-sulphate	1
GNZ-0921-PA	4-O-Su-GlcNAc β -sp2	β -D-GlcNAc-4-O-sulfate	1

PA-Series: Unlabeled Polyacrylamide Conjugates

Catalog#	Oligosaccharide	Trivial	Pack (mg)
GNZ-0922-PA	GalNAca1-4GalNAca-sp3		1
GNZ-0925-PA	Neu5Aca2-6Galβ1-4GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3		1
GNZ-0931-PA	Glca1-4Glca1-4Glca1-4Glcβ-sp4	maltotetraose	1
GNZ-0932-PA	Glca1-4Glca1-4Glcβ-sp4	maltotriose	1
GNZ-0934-PA	6-O-Su-GalNAcβ1-4(3-O-Ac)GlcNAcβ-sp3	3-O-Ac-LacdiNAc-6`-sulphate	1
GNZ-0935-PA	4,6-O-Su ₂ -GalNAcβ1-4GlcNAcβ-sp3	LacdiNAc-4`,6`-di-O-sulphate	1
GNZ-0936-PA	4-O-Su-GalNAcβ1-4GlcNAcβ-sp3		1
GNZ-0937-PA	6-O-Su-GalNAcβ1-4GlcNAcβ-sp3	6`-O-su-LacdiNAc	1
GNZ-0941-PA	3-O-Su-GlcNAcβ-sp3	β-D-GlcNAc-3-O-sulfate	1
GNZ-0946-PA	Mana1-4Manβ-sp4		1
GNZ-0949-PA	Neu5Aca2-3Galβ1-3(6-O-Su)GlcNAcβ-sp3	3`SiaLe ^c -6-O-sulphate	0.5
GNZ-0951-PA	Neu5Aca2-3Galβ1-4(6-O-Su)GlcNAcβ-sp3	3`SLN-6-O-sulphate	0.5
GNZ-0952-PA	3-O-Su-GalNAcβ-sp3	β-D-GalNAc-3-O-sulfate	1
GNZ-0953-PA	4-O-Su-GalNAcβ-sp3	β-D-GalNAc-4-O-sulfate	1
GNZ-0955-PA	Galβ1-4(Galβ1-3)GlcNAcβ-sp3		1
GNZ-0956-PA	Neu5Gca2-3Galβ1-4GlcNAcβ-sp3	3`Sia(Gc)LacNAc	0.5
GNZ-0957-PA	Neu5Gca2-6Galβ1-4GlcNAcβ-sp3	6`Sia(Gc)LacNAc	0.5
GNZ-0958-PA	GlcNAcβ1-3Galβ1-4GlcNAcβ-sp2	GlcNAcβ3`LacNAc	1
GNZ-0958a-PA	GlcNAcβ1-3Galβ1-4GlcNAcβ-sp3	GlcNAcβ3`LacNAc	1
GNZ-0959-PA	Glca1-6Glca1-6Glcβ-sp4	Isomaltotriose	1
GNZ-0966-PA	Galα1-3(Fuca1-2)Galβ1-3(Fuca1-4)GlcNAcβ-sp3	BLE ^b	1
GNZ-0967-PA	GalNAca1-3(Fuca1-2)Galβ1-4(Fuca1-3)GlcNAcβ-sp3	ALe ^γ	1
GNZ-0968-PA	Galα1-3(Fuca1-2)Galβ1-4(Fuca1-3)GlcNAcβ-sp3	BLE ^γ	0.5
GNZ-0972-PA	GlcNAcβ1-4[3-O-CH(CH ₃)COOH]GlcNAcβ-sp4	GlcNAc-Mur	1
GNZ-0973-PA	GlcNAcβ1-4[3-O-CH(CH ₃)COOH]GlcNAca-sp4		1
GNZ-0976-PA	GlcAβ1-3Galβ-sp3	GlcA3Gal	1
GNZ-0977-PA	Neu5Aca2-6(Galα1-3)GalNAca-sp3	6SiaT _{oo}	0.5
GNZ-0978-PA	GlcAβ1-6Galβ-sp3	GlcAβ6Gal	1
GNZ-0980-PA	Galβ1-4GlcNAcβ1-6(Galβ1-3)GalNAca-sp3	LacNAc6TF	0.5
GNZ-0982-PA	GlcNAcβ1-4GlcNAβ1-4GlcNAcβ-sp4	chitotriose	1
GNZ-0984-PA	Neu5Aca2-6(Galβ1-3)GalNAca-sp3	6SiaTF	0.5
GNZ-0985-PA	Neu5Acβ2-6(Galβ1-3)GalNAca-sp3	6SiaβTF	0.5
GNZ-0986-PA	Neu5Acβ2-6GalNAca-sp3	SiaβT _n	0.5
GNZ-0991-PA	Galα1-4GalNAca-sp3		1
GNZ-0993-PA	Neu5Aca2-3GalNAca-sp3	3-SiaT _n	0.5
GNZ-0995-PA	Galβ1-4GlcNAβ1-3GalNAca-sp3	LacNAc3T _n	1
GNZ-0996-PA	Galβ1-4GlcNAβ1-6GalNAca-sp3	LacNAc6T _n	1
GNZ-0997-PA	Neu5Aca2-6Galβ1-4GlcNAcβ-sp3	6`SLN	1
GNZ-0998-PA	6-O-Su-GalNAca-sp3	α-D-GalNAc-6-O-sulfate	1

Legend

sp1	= ol	= aminoalditol	Ala	= alanine	Fm	= formyl
sp2	= C2	= OCH2CH2NH2	Arg	= arginine	Gc	= glycolyl
sp3	= C3	= OCH2CH2CH2NH2	Asn	= asparagine	GN	= GlcNAcβ
sp4	= Gly	= NHCOCH2NH2	Ile	= iso-leucine	Lac	= lactose
sp5	= long	= -O(CH2)3NHCO(CH2)5NH2	Nle	= norleucine	LN	= N-acetyllactosamine
sp6	= -NH(p-C6H4)CH2CH2NH2	(as-aminoalditol)	Ser	= serine	M	= Man
sp7	= -O(CH2)2NHCO(OCH2CH2)6NH2		Trp	= tryptophan	Tn	= GalNAca
sp8	= PEG6	= -(OCH2CH2)6NH2	Phe	= phenylalanine	P	= phosphate
sp9	= BnGly	= -OCH2C6H4-p-NHCOCH2NH2	Val	= Valine	Su	= sulfate
sp10	= PEG2	= -(OCH2CH2)2NH2	Cit	= Citrulline		
sp0	= OCH2CH2CH2SCH2CH2NH2					



Sigma-Aldrich®

Lab & Production Materials

MilliporeSigma
400 Summit Drive
Burlington, MA 01803

SigmaAldrich.com

To place an order or receive technical assistance:

Order/Customer Service: **SigmaAldrich.com/order**
Technical Service: **SigmaAldrich.com/techservice**
Safety-related Information: **SigmaAldrich.com/safetycenter**

© 2021 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved. MilliporeSigma, the vibrant M and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.

MS_CA6885EN
33549
01/2021