

**Enzymatic Assay of PYRUVATE KINASE<sup>1</sup>  
from Rabbit Muscle, Dog Muscle, and Chicken Muscle  
(EC 2.7.1.40)**

**PRINCIPLE:**

Phospho(enol)pyruvate + ADP  $\xrightarrow[\text{Mg}^{2+}, \text{K}^+]{\text{Pyruvate Kinase}}$  Pyruvate + ATP

Pyruvate +  $\beta$ -NADH  $\xrightarrow{\text{L-Lactic Dehydrogenase}}$  L-Lactate +  $\beta$ -NAD

Abbreviations used:

ADP = Adenosine 5'-Diphosphate

ATP = Adenosine 5'-Triphosphate

$\beta$ -NADH =  $\beta$ -Nicotinamide Adenine Dinucleotide, Reduced Form

$\beta$ -NAD =  $\beta$ -Nicotinamide Adenine Dinucleotide, Oxidized Form

**CONDITIONS:** T = 37°C, pH = 7.6, A<sub>340nm</sub>, Light path = 1 cm

**METHOD:** Continuous Spectrophotometric Rate Determination

**REAGENTS:**

- A. 100 mM Potassium Phosphate Buffer, pH 7.6 at 37°C.  
(Prepare 100 ml in deionized water using Potassium Phosphate, Monobasic, Anhydrous, Sigma Prod. No. P-5379. Adjust to pH 7.6 at 37°C with 1 M KOH.)
- B. 8.0 mM Phospho(enol)pyruvate Solution (PEP)  
(Prepare 1 ml in deionized water using Phospho(enol)pyruvate, Monopotassium Salt, Sigma Prod. No. P-7127. **PREPARE FRESH.**)
- C. 3.0 mM  $\beta$ -Nicotinamide Adenine Dinucleotide, Reduced Form Solution ( $\beta$ -NADH)  
(Prepare 2 ml in deionized water using  $\beta$ -Nicotinamide Adenine Dinucleotide, Reduced Form, Disodium Salt, Sigma Prod. No. N-8129. **PREPARE FRESH.**)
- D. 100 mM Magnesium Sulfate Solution (MgSO<sub>4</sub>)  
(Prepare 1 ml in deionized water using Magnesium Sulfate, Heptahydrate, Sigma Prod. No. M-1880.)

**Enzymatic Assay of PYRUVATE KINASE<sup>1</sup>  
from Rabbit Muscle, Dog Muscle, and Chicken Muscle  
(EC 2.7.1.40)**

**REAGENTS:** (continued)

- E. 40 mM Adenosine Diphosphate Solution (ADP)  
(Prepare 1 ml in deionized water using Adenosine 5'-Diphosphate, Sodium Salt, Sigma Prod. No. A-2754.)
- F. L-Lactic Dehydrogenase Solution (LDH)  
(Immediately before use, prepare a solution containing 500 units/ml in cold Reagent A using L-Lactic Dehydrogenase, Sigma Prod. No. L-2500.)
- G. Pyruvate Kinase Enzyme Solution  
(Immediately before use, prepare a solution containing 0.3 - 0.6 unit/ml of Pyruvate Kinase in cold Reagent A.)

**PROCEDURE:**

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>Test</u>	<u>Blank</u>
Deionized Water	1.40	1.40
Reagent A (Buffer)	0.80	0.90
Reagent B (PEP)	0.16	0.16
Reagent C ( $\beta$ -NADH)	0.20	0.20
Reagent D ( $MgSO_4$ )	0.20	0.20
Reagent E (ADP)	0.10	
Reagent F (LDH)	0.04	0.10
		0.04

Mix by inversion and equilibrate to 37°C. Monitor the  $A_{340nm}$  until constant, using a suitably thermostatted spectrophotometer. Then add:

Reagent G (Enzyme Solution)	0.10	-----
-----------------------------	------	-------

Immediately mix by inversion and record the decrease in  $A_{340nm}$  for approximately 5 minutes. Obtain the  $r A_{340nm}/minute$  using the maximum linear rate for both the Test and Blank.

**Enzymatic Assay of PYRUVATE KINASE<sup>1</sup>**  
**from Rabbit Muscle, Dog Muscle, and Chicken Muscle**  
**(EC 2.7.1.40)**

**CALCULATIONS:**

$$\text{Units/ml enzyme} = \frac{(\text{r } A_{340\text{nm}}/\text{min Test} - \text{r } A_{340\text{nm}}/\text{min Blank})(3)(\text{df})}{(6.22)(0.1)}$$

3 = Total volume (in milliliters) of assay

df = Dilution factor

6.22 = Millimolar extinction coefficient of  $\beta$ -NADH at 340

nm 0.1 = Volume (in milliliter) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/mg enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/mg enzyme}}$$

**UNIT DEFINITION:**

One unit will convert 1.0  $\mu$ mole of phospho(enol)pyruvate to pyruvate per minute at pH 7.6 at 37°C.

**FINAL ASSAY CONCENTRATION:**

In a 3.00 ml reaction mix, the final concentrations are 31 mM potassium phosphate, 0.43 mM phospho(enol)pyruvate, 0.20 mM  $\beta$ -nicotinamide adenine dinucleotide, reduced form, 6.7 mM magnesium sulfate, 1.3 mM adenosine 5'-diphosphate, 20 units lactic dehydrogenase and 0.03 - 0.06 unit pyruvate kinase.

**REFERENCE:**

Bergmeyer, H.U., Gawehn, K., and Grassl, M. (1974) in *Methods of Enzymatic Analysis* (Bergmeyer, H.U. ed.) Second Edition, Volume I, 509-510, Academic Press, Inc., New York, NY

**NOTES:**

1. This assay is not to be used to assay Pyruvate Kinase from Rabbit Liver, Sigma Prod. No. P-7286, Pyruvate Kinase, from *Bacillus stearothermophilus*, Sigma Prod. No. P-1903, Pyruvate Kinase, from Porcine Heart, Sigma Prod. No. P-2040, and Pyruvate Kinase, Insoluble Enzyme, Sigma Prod. No. P-4010.

**Enzymatic Assay of PYRUVATE KINASE<sup>1</sup>  
from Rabbit Muscle, Dog Muscle, and Chicken Muscle  
(EC 2.7.1.40)**

**NOTES:** (continued)

2. Unit Definition for L-Lactic Dehydrogenase: One unit will reduce 1.0  $\mu$ mole of pyruvate to L-lactate per minute at pH 7.5 at 37°C.
3. This assay is based on the cited reference.
4. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

**This procedure is for informational purposes. For a current copy of Sigma's quality control procedure contact our Technical Service Department.**