


## 80661 Atto 655 maleimide

### Application


Atto 655 belongs to a new generation of fluorescent labels. The dye is designed for application in the area of life science, e.g. labeling of DNA, RNA or proteins. Characteristic features of the label are strong absorption, good fluorescence quantum yield, excellent thermal and photo-stability, outstanding ozone resistance, very good water solubility, and very little triplet formation. Atto 655 is a zwitterionic dye with a net electrical charge of zero. The fluorescence is efficiently quenched by electron donors like guanine, tryptophan, etc.

### Product Description

MW	812 g/mol
$\lambda_{\text{abs}}$	663 nm
$\epsilon_{\text{max}}$	$1.25 \times 10^5 \text{ M}^{-1} \text{ cm}^{-1}$
$\lambda_{\text{fl}}$	680 nm
$\eta_{\text{fl}}$	30 %
$\tau_{\text{fl}}$	1.8 ns
CF <sub>260</sub>	0.24
CF <sub>280</sub>	0.08



### Optical data of the carboxy derivative (in aqueous solution)



## General procedure for labelling proteins with maleimides

- 1)** Dissolve the protein at 50–100  $\mu\text{M}$  in a suitable buffer at pH 7.0–7.5 at room temperature. Common buffers include 10–100 mM phosphate, Tris, HEPES. Under those conditions, the protein thiol groups are sufficiently nucleophilic so that they react almost exclusively with the reagent. Other protein amines mostly remain protonated and relatively unreactive.
- 2)** Reduce disulfide bonds in the protein. A 10-fold molar excess of a reducing agent such as DTT (43817) or TCEP (93284) is usually sufficient. If DTT is used, then dialysis is required to remove the excess DTT prior to introducing the reactive dye. This is not necessary for TCEP.
- 3)** As thiols can be oxidized to disulfides, it may be advisable to carry out thiol modifications in an oxygen-free environment. This is particularly important if the protein has been treated with a reagent such as dithiothreitol prior to thiol modification. In this case, all buffers should be deoxygenated and the reactions carried out under an inert atmosphere to prevent reformation of disulfides.
- 4)** Prepare a 10–20 mM stock solution of the reactive dye in a suitable solvent immediately prior to use (DMSO is the most common choice). Protect all stock solutions from light as much as possible by wrapping containers in aluminum foil.
- 5)** Add sufficient protein-modification reagent from a stock solution to achieve a 10–20 molar excess compared to protein. Add the reagent dropwise to the protein solution as it is stirring.
- 6)** Let the reaction proceed for 2 hours at room temperature or overnight at 4°C. In both cases reaction should take place in the dark.
- 7)** Upon completion of the reaction with the protein, an excess soluble low molecular weight thiol (e.g. glutathione, mercaptoethanol) can be added to consume excess thiol-reactive reagent, thus ensuring that no reactive species are present during the purification step.
- 8)** Separate the conjugate on a gel filtration column, such as a Sephadex G-25 column or equivalent matrix, or by extensive dialysis at 4°C in an appropriate buffer.

Sephadex is a registered trademark of GE Healthcare

**Storage:** store at  $\leq -20^\circ\text{C}$ . Protect from long-term exposure to moisture and light.

## Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

The vibrant M and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates.

Detailed information on trademarks is available via publicly accessible resources.

© 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the US and Canada.

