



SIGMA QUALITY CONTROL TEST PROCEDURE

Product Information

Enzymatic Assay of L-ASPARTASE (EC 4.3.1.1)

PRINCIPLE:



CONDITIONS: T = 30°C, pH 8.5, A_{240nm}, Light path = 1 cm

METHOD: Continuous Spectrophotometric Rate Determination

REAGENTS:

- A. 150 mM Tris HCl Buffer, pH 8.5 at 30°C
(Prepare 100 ml in deionized water using Trizma Base, Sigma Prod. No. T-1503. Adjust to pH 8.5 at 30°C with 1 M HCl.)
- B. 60 mM Magnesium Sulfate Solution (MgSO₄)
(Prepare 1 ml in deionized water using Magnesium Sulfate, Heptahydrate, Sigma Prod. No. M-1880.)
- C. 3.0 mM Ethylenediaminetetraacetic Acid Solution (EDTA)
(Prepare 1 ml in Reagent A using Ethylenediaminetetraacetic Acid, Disodium Salt, Dihydrate, Sigma Stock No. ED2SS.)
- D. 500 mM L-Aspartate Solution (L-Asp)
(Prepare 10 ml in deionized water using L-Aspartic Acid, Monopotassium, Sigma Prod. No. A-6558.)
- E. 5 mM Potassium Phosphate buffer, pH 7.0 at 25°C (Enz Dil)
(Prepare 25 ml in deionized water using Potassium Phosphate, Monobasic, Anhydrous, Sigma Prod. No. P-5379. Adjust to pH 7.0 at 25°C with 1 M KOH.)
- F. L-Aspartase Enzyme Solution
(Immediately before use, prepare a solution containing 2 units/ml of L-Aspartase in ice cold Reagent E. Place on ice.)

**Enzymatic Assay of L-ASPARTASE
(EC 4.3.1.1)**

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable cuvettes:

	<u>Test</u>	<u>Blank</u>
Reagent A (Buffer)	1.00	1.00
Reagent B (MgSO ₄)	0.10	0.10
Reagent C (EDTA)	0.10	0.10
Reagent D (L-Asp)	0.30	0.30
Deionized Water	1.40	1.40

Mix by inversion and equilibrate to 30°C. Then add:

Reagent F (Enzyme Solution)	0.10	-----
Reagent E (Enz Dil)	-----	0.10

Immediately mix by inversion and record the increase in A_{240nm} for approximately 5 minutes. Obtain the ΔA_{240nm}/minute using the maximum linear rate for both the Test and Blank.

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(\Delta A_{240\text{nm}}/\text{min Test} - \Delta A_{240\text{nm}}/\text{min Blank})(3)(\text{df})}{(2.53)(0.1)}$$

3 = Total volume (in milliliters) of assay

df = Dilution factor

2.53 = Millimolar extinction coefficient of potassium fumarate at 240 nm

0.1 = Volume (in milliliter) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will convert 1.0 μmole of L-aspartate to fumarate per minute at pH 8.5 at 30°C.

**Enzymatic Assay of L-ASPARTASE
(EC 4.3.1.1)**

FINAL ASSAY CONCENTRATIONS:

In a 3.00 ml reaction mix, the final concentrations are 55 mM Tris, 2 mM magnesium sulfate, 0.1 mM ethylenediamine- tetraacetic acid, 50 mM L-aspartate, 0.2 mM potassium phosphate, and 0.2 unit L-aspartase.

REFERENCE:

Williams, V.R. and Lartigue, D.J. (1969) *Methods in Enzymology*, XIII, 354-361

NOTES:

1. This assay is based on the cited reference.
2. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.