

Product Information

Fibroblast Growth Factor-4

Human, Recombinant
Expressed in *E. coli*

Product Number **F8424**

Product Description

Fibroblast Growth Factor-4 (FGF-4), of the fibroblast growth factor family, is encoded by the K-fgf/hst oncogene. FGF-4 is also known as hst-1 (from human stomach tumor), and K-FGF (from Kaposi's sarcoma). The K-fgf/hst oncogene was originally identified by transfection into NIH3T3 cells with DNA from stomach and colon cancer,^{1,2,3} Kaposi's sarcoma,^{4,5} and hepatocellular carcinoma.⁶ The activation of the K-fgf oncogene results from unregulated expression of a normal gene product.⁷ Unlike the two prototypes of the FGF family, FGF basic (FGF-2) and FGF acidic (FGF-1), FGF-4 is glycosylated and secreted by cells into culture medium.⁵

Fibroblast cell lines expressing FGF-4 acquire a transformed phenotype *in vitro* and are highly tumorigenic *in vivo*.⁸ FGF-4 is a potent mitogen for fibroblasts in culture and has features of a transforming growth factor.⁸ In addition, FGF-4 is mitogenic for endothelial cells and will cause morphological transformation of NIH3T3 cells.^{4,5,7} FGF-4 shares 42% sequence identity with FGF-basic (FGF-2),⁹ and both FGF-basic and FGF-4 bind to the same receptors.^{10,11} Recombinant FGF-4 is a 19 kDa protein containing 182 amino acid residues.

Reagent

Lyophilized from a 0.2 µm-filtered buffered solution containing bovine serum albumin as a carrier protein.

Storage/Stability

The lyophilized product is stable for a few weeks at room temperature, but is best stored at -20 °C. After reconstitution, store in working aliquots at -20 °C. Repeated freeze/thaw cycles will result in some loss of activity.

Reconstitution and Use

Reconstitute in water to a concentration of 0.1-1.0 mg/ml. This solution can then be diluted into other aqueous buffers and stored at 2-8 °C for up to

one week. For extended use, the reconstituted product should be stored in working aliquots at -20 °C. Repeated freezing and thawing is not recommended.

Product Profile

The biological activity of recombinant human FGF-4 is measured by the dose-dependent stimulation of thymidine uptake using BaF3 cells expressing FGF receptors.

The ED₅₀ is defined as the effective concentration of growth factor that elicits a 50% increase in cell growth in a cell based bioassay.

Purity: ≥ 95% by SDS-PAGE and HPLC

Endotoxin: <0.1 ng/µg

References

1. Sakamoto, H., et al., Proc. Natl. Acad. Sci. USA, **83**, 3997 (1986).
2. Koda, T., et al., Jpn. J. Cancer Res., **78**, 325 (1987).
3. Taria, M., et al., Proc. Natl. Acad. Sci. USA, **84**, 2980 (1987).
4. Delli-Bovi, P., et al., Proc. Natl. Acad. Sci. USA, **84**, 5660 (1987).
5. Delli-Bovi, P., et al., Cell, **50**, 729 (1987).
6. Nakagama, H., et al., Jpn. J. Cancer Res., **78**, 651 (1987).
7. Delli-Bovi, P., et al., Mol. Cell. Biol., **8**, 2933 (1988).
8. Talarico, D., et al., Mol. Cell. Biol., **11**, 1138 (1991).
9. Bernharroch, D., et al., Isr. J. Med. Sci., **26**, 212 (1990).
10. Moscatelli, H., et al., J. Cell Biol., **109**, 2519 (1989).
11. Mansukhani, A., et al., Proc. Natl. Acad. Sci. USA, **87**, 4378 (1990).

KAA 12/03

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.