

## Product Information

## Medium 199

**M4530, M2520, M0393, M0650, M7528,  
M2154, M3769, M5017, M7653, M9163**

Many early tissue culture media were predominantly formulated from animal products and/or tissue extracts. In 1950, Morgan and his coworkers reported their efforts to produce a totally defined nutritional source for cell cultures. Their experiments, conducted with various combinations of vitamins, amino acids, and other factors revealed that growth of explanted tissue could be measured in what has become known as Medium 199.

However, it was found that long-term cultivation of cells required addition of a serum supplement to the culture medium. When properly supplemented, Medium 199 has broad species applicability, particularly for cultivation of non-transformed cells. It is widely used in virology, vaccine production, and in vitro cultivation of primary explants of mouse pancreatic epithelial and rat lens tissues.

	<b>M0393</b>	<b>M0650</b>	<b>M2154</b>	<b>M2520</b>	<b>M3769</b>
	[powder]	[10×]	[1×]	[powder]	[powder]
<b>COMPONENT</b>	g/L	g/L	g/L	g/L	g/L
Inorganic Salts					
CaCl <sub>2</sub> (anhydrous)	0.1396	—	—	0.2	0.2
CaCl <sub>2</sub> •2H <sub>2</sub> O	—	2.659	0.265	—	—
Fe(NO <sub>3</sub> ) <sub>3</sub> • 9H <sub>2</sub> O	0.00072	0.0072	0.00072	0.00072	0.00072
MgSO <sub>4</sub> (anhydrous)	0.09767	0.9767	0.09767	0.09767	0.0967
KCl	0.4	4.0	0.4	0.4	0.4
KH <sub>2</sub> PO <sub>4</sub>	0.06	—	—	—	—
Na • Acetate (anhydrous)	0.05	0.5	0.05	0.05	0.05
NaHCO <sub>3</sub>	—	—	2.2	—	—
NaCl	8.0	68.0	6.8	6.0	6.8
Na <sub>2</sub> HPO <sub>4</sub> (anhydrous)	0.04788	—	—	—	—
NaH <sub>2</sub> PO <sub>4</sub> (anhydrous)	—	1.22	0.122	0.122	0.122
Amino Acids					
L-Alanine	0.025	0.25	0.025	0.025	0.025
L-Arginine • HCl	0.07	0.7	0.07	0.07	0.07
L-Aspartic Acid	0.03	0.3	0.03	0.03	0.03
L-Cystine • 2HCl	0.026	0.260	0.026	0.026	0.026
L-Cysteine • HCl• H <sub>2</sub> O	0.00011	0.0011	0.00011	0.00011	0.00011
L-Glutamic Acid	0.0668	0.668	0.0668	0.0668	0.0668
L-Glutamine	0.1	—	—	0.1	—
Glycine	0.05	0.5	0.05	0.05	0.05
L-Histidine • HCl • H <sub>2</sub> O	0.02188	0.2188	0.02188	0.02188	0.02188
Hydroxy-L-Proline	0.01	0.1	0.01	0.01	0.01
L-Isoleucine	0.02	0.2	0.02	0.02	0.02
L-Leucine	0.06	0.6	0.06	0.06	0.06
L-Lysine • HCl	0.07	0.7	0.07	0.07	0.07
L-Methionine	0.015	0.15	0.015	0.015	0.015
L-Phenylalanine	0.025	0.25	0.025	0.025	0.025

L-Proline	0.04	0.4	0.04	0.04	0.04
L-Serine	0.025	0.25	0.025	0.025	0.025
L-Threonine	0.03	0.3	0.03	0.03	0.03
L-Tryptophan	0.01	0.1	0.01	0.01	0.01
L-Tyrosine • 2Na • 2H <sub>2</sub> O	0.05766	0.5766	0.05766	0.05766	0.05766
L-Valine	0.025	0.25	0.025	0.025	0.025
Vitamins					
Ascorbic Acid • Na	0.0000566	0.0005625	0.0000566	0.0000566	0.0000566
Biotin	0.00001	0.0001	0.00001	0.00001	0.00001
Calciferol	0.0001	0.001	0.0001	0.0001	0.0001
Choline Chloride	0.0005	0.005	0.0005	0.0005	0.0005
Folic Acid	0.00001	0.0001	0.00001	0.00001	0.00001
Menadione (sodium bisulfite)	—	0.00016	0.000016	0.000016	—
Menadione	0.000010	—	—	—	0.000010
myo-Inositol	0.00005	0.0005	0.00005	0.00005	0.00005
Niacinamide	0.000025	0.00025	0.000025	0.000025	0.000025
Nicotinic Acid	0.000025	0.00025	0.000025	0.000025	0.000025
p-Amino Benzoic Acid	0.00005	0.0005	0.00005	0.00005	0.00005
D-Pantothenic Acid • ½Ca	0.00001	0.0001	0.00001	0.00001	0.00001
Pyridoxal • HCl	0.000025	0.00025	0.000025	0.000025	0.000025
Pyridoxine • HCl	0.000025	0.00025	0.000025	0.000025	0.000025
Retinol Acetate	0.00014	0.0014	0.00014	0.00014	0.00014
Riboflavin	0.00001	0.0001	0.00001	0.00001	0.00001
DL- $\alpha$ -Tocopherol Phosphate • 2Na	0.00001	0.0001	0.00001	0.00001	0.00001
Thiamine • HCl	0.00001	0.0001	0.00001	0.00001	0.00001
Other					
Adenine Hemisulfate	0.01	0.1	0.01	0.01	0.01
Adenosine Triphosphate • 2Na • 3H <sub>2</sub> O	0.001	0.01	0.001	0.001	0.001
Adenosine Monophosphate • Na	0.0002385	0.002385	0.0002385	0.0002385	0.0002385
Cholesterol	0.0002	0.002	0.0002	0.0002	0.0002
Deoxyribose	0.0005	0.005	0.0005	0.0005	0.0005
Glucose	1.0	10.0	1.0	1.0	1.0
Glutathione (reduced)	0.00005	0.0005	0.00005	0.00005	0.00005
Guanine	0.00024	—	—	0.00024	0.00024
Guanine • HCl	—	0.003	0.0003	—	—
HEPES	—	—	—	5.958	—
Hypoxanthine Sodium salt	0.000348	—	—	—	0.000348
Hypoxanthine	—	0.003	0.0003	0.0003	—
Phenol Red • Na	0.0213	0.213	0.0213	0.0213	—
TWEEN® 80	0.02	0.2	0.02	0.02	0.02
Ribose	0.0005	0.005	0.0005	0.0005	0.0005
Thymine	0.0003	0.003	0.0003	0.0003	0.0003
Uracil	0.0003	0.003	0.0003	0.0003	0.0003
Xanthine • Na	0.000344	0.00344	0.000344	0.000344	0.000344
ADD					
L-Glutamine	—	0.1 at 1x	0.1	—	0.1
Sodium Bicarbonate	0.35	2.2 at 1x	—	2.2	2.2

	<b>M4530</b>	<b>M5017</b>	<b>M7528</b>	<b>M7653</b>	<b>M9163</b>
	[1×]	[powder]	[1×]	[1×]	[10×]
<b>COMPONENT</b>	g/L	g/L	g/L	g/L	g/L
Inorganic Salts					
CaCl <sub>2</sub> (anhydrous)	—	0.2	—	—	—
CaCl <sub>2</sub> •2H <sub>2</sub> O	0.265	—	0.265	0.185	1.85
Fe(NO <sub>3</sub> ) <sub>3</sub> • 9H <sub>2</sub> O	0.00072	0.00072	0.00072	0.00072	0.0072
MgSO <sub>4</sub> (anhydrous)	0.09767	0.09767	0.09767	0.09767	0.9767
KCl	0.4	0.4	0.4	0.4	4.0
KH <sub>2</sub> PO <sub>4</sub>	—	—	—	0.06	0.6
Na • Acetate (anhydrous)	0.05	0.05	0.05	0.05	0.5
NaHCO <sub>3</sub>	2.2	—	2.2	0.35	—
NaCl	6.8	6.8	6.0	8.0	80.0
Na <sub>2</sub> HPO <sub>4</sub> (anhydrous)	—	—	—	0.04788	0.4788
NaH <sub>2</sub> PO <sub>4</sub> (anhydrous)	0.122	0.122	0.122	—	—
Amino Acids					
L-Alanine	0.025	0.025	0.025	0.025	0.25
L-Arginine • HCl	0.07	0.07	0.07	0.07	0.7
L-Aspartic Acid	0.03	0.03	0.03	0.03	0.3
L-Cystine • 2HCl	0.026	0.026	0.026	0.026	0.260
L-Cysteine • HCl• H <sub>2</sub> O	0.00011	0.00011	0.00011	0.00011	0.0011
L-Glutamic Acid	0.0668	0.0668	0.0668	0.0668	0.668
L-Glutamine	0.1	0.1	—	—	—
Glycine	0.05	0.05	0.05	0.05	0.5
L-Histidine • HCl • H <sub>2</sub> O	0.02188	0.02188	0.02188	0.02188	0.2188
Hydroxy-L-Proline	0.01	0.01	0.01	0.01	0.1
L-Isoleucine	0.02	0.02	0.02	0.02	0.2
L-Leucine	0.06	0.06	0.06	0.06	0.6
L-Lysine • HCl	0.07	0.07	0.07	0.07	0.7
L-Methionine	0.015	0.015	0.015	0.015	0.15
L-Phenylalanine	0.025	0.025	0.025	0.025	0.25
L-Proline	0.04	0.04	0.04	0.04	0.4
L-Serine	0.025	0.025	0.025	0.025	0.25
L-Threonine	0.03	0.03	0.03	0.03	0.3
L-Tryptophan	0.01	0.01	0.01	0.01	0.1
L-Tyrosine • 2Na • 2H <sub>2</sub> O	0.05766	0.05766	0.05766	0.05766	0.5766
L-Valine	0.025	0.025	0.025	0.025	0.25

<b>Vitamins</b>					
Ascorbic Acid • Na	0.0000566	0.0000566	0.0000566	0.0000566	0.000566
Biotin	0.00001	0.00001	0.00001	0.00001	0.0001
Calciferol	0.0001	0.0001	0.0001	0.0001	0.001
Choline Chloride	0.0005	0.0005	0.0005	0.0005	0.005
Folic Acid	0.00001	0.00001	0.00001	0.00001	0.0001
Menadione (sodium bisulfite)	0.000016	--	0.000016	0.000016	0.00016
Menadione	—	0.000010	—	—	—
myo-Inositol	0.00005	0.00005	0.00005	0.00005	0.0005
Niacinamide	0.000025	0.000025	0.000025	0.000025	0.00025
Nicotinic Acid	0.000025	0.000025	0.000025	0.000025	0.00025
p-Amino Benzoic Acid	0.00005	0.00005	0.00005	0.00005	0.0005
D-Pantothenic Acid • ½Ca	0.00001	0.00001	0.00001	0.00001	0.0001
Pyridoxal • HCl	0.000025	0.000025	0.000025	0.000025	0.00025
Pyridoxine • HCl	0.000025	0.000025	0.000025	0.000025	0.00025
Retinol Acetate	0.00014	0.00014	0.00014	0.00014	0.0014
Riboflavin	0.00001	0.00001	0.00001	0.00001	0.0001
DL-α-Tocopherol Phosphate • 2Na	0.00001	0.00001	0.00001	0.00001	0.0001
Thiamine • HCl	0.00001	0.00001	0.00001	0.00001	0.0001
<b>Other</b>					
Adenine Hemisulfate	0.01	0.01	0.01	0.01	0.1
Adenosine Triphosphate • 2Na • 3H <sub>2</sub> O	0.001	0.001	0.001	0.001	0.01
Adenosine Monophosphate • Na	0.0002385	0.0002385	0.0002385	0.0002385	0.002385
Cholesterol	0.0002	0.0002	0.0002	0.0002	0.002
Deoxyribose	0.0005	0.0005	0.0005	0.0005	0.005
Glucose	1.0	1.0	1.0	1.0	10.0
Glutathione (reduced)	0.00005	0.00005	0.00005	0.00005	0.0005
Guanine	—	0.00024	0.00024	—	—
Guanine • HCl	0.0003	—	—	0.0003	0.003
HEPES	—	—	5.958	—	—
Hypoxanthine Sodium salt	—	0.000348	—	—	—
Hypoxanthine	0.0003	—	0.0003	0.0003	0.003
Phenol Red • Na	0.0213	0.0213	0.0213	0.0213	0.0213
TWEEN® 80	0.02	0.02	0.02	0.02	0.2
Ribose	0.0005	0.0005	0.0005	0.0005	0.005
Thymine	0.0003	0.0003	0.0003	0.0003	0.003
Uracil	0.0003	0.0003	0.0003	0.0003	0.003
Xanthine • Na	0.000344	0.000344	0.000344	0.000344	0.00344
ADD					
L-Glutamine	—	—	0.1	0.1	0.1 at 1×
Sodium Bicarbonate	—	2.2	—	—	0.35 at 1×

## Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

## References

1. Morgan, J.F., Morton, H.J., and Parker, R.C., The Nutrition of Animal Cells in Tissue Culture. I. Initial Studies on a Synthetic Medium. Proc. Soc. Exp. Biol. Med., **73**, 1-8 (1950).
2. Morgan, J.F., Campbell, E., and Morton, H.J. The Nutrition of Animal Tissues Cultivated In Vitro. I.A Survey of Natural Materials are Supplements to Synthetic Medium. J.N.C.I., 16:2 557-567 (1955).

## Notice

We provide information and advice to our customers on application technologies and regulatory matters to the best of our knowledge and ability, but without obligation or liability. Existing laws and regulations are to be observed in all cases by our customers. This also applies in respect to any rights of third parties. Our information and advice do not relieve our customers of their own responsibility for checking the suitability of our products for the envisaged purpose.

The information in this document is subject to change without notice and should not be construed as a commitment by the manufacturing or selling entity, or an affiliate. We assume no responsibility for any errors that may appear in this document.

### Technical Assistance

Visit the tech service page at [SigmaAldrich.com/techservice](https://SigmaAldrich.com/techservice).

### Standard Warranty

The applicable warranty for the products listed in this publication may be found at [SigmaAldrich.com/terms](https://SigmaAldrich.com/terms).

### Contact Information

For the location of the office nearest you, go to [SigmaAldrich.com/offices](https://SigmaAldrich.com/offices).

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the U.S. and Canada.

MilliporeSigma, and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates. All other trademarks are the property of their respective owners. Detailed information on trademarks is available via publicly accessible resources.  
© 2021 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.

The logo for MilliporeSigma, featuring the word "MILLIPORE" in a bold, red, sans-serif font above the word "SIGMA" in a similar bold, red, sans-serif font.