

## Product Information

### Anti-Phox2a

Developed in Rabbit, Affinity isolated antibody

Product Number **P 0246**

#### Product Description

Anti-Phox2a is developed in rabbit using a synthetic peptide, FPEPSGLHEKRKQRRIR corresponding to human Phox2a (amino acids 78-94) conjugated to BSA as immunogen. The antibody is affinity-purified using the immunizing peptide immobilized on resin.

Anti-Phox2a specifically recognizes Phox2a (29.6 kDa) by immunoblotting and immunohistochemistry. The antibody recognizes human and rodent Phox2a. Other species reactivity has not been confirmed.

Phox2a (paired-like homeobox 2a, aristaless homeobox homolog, Arix) is a transcription factor expressed in noradrenergic cell types of the sympathetic nervous system.

#### Reagent

Anti-Phox2a is provided as affinity isolated antibody in a 50% ammonium sulfate suspension in phosphate buffered saline, containing no additional preservatives.

#### Preparation Instructions

##### Method 1 for immunostaining and immunoblotting (Western blot)

1. Carefully resuspend antibody pellet to uniformity.
2. Remove a fixed amount of suspension and dissolve 1:10 in PBS or TBS to yield a 100 µg/ml solution.

##### Method 2 for immunoprecipitation, supershift, immunostaining and immunoblotting (Western blot)

1. Pellet antibodies at 10,000 – 15,000 x g for 10 minutes at 2 to 8 °C using a microcentrifuge.
2. Carefully remove as much supernatant as possible. It is not necessary to remove all the ammonium sulfate solution; a small residual amount will not effect the antibody preparation. Dissolve the pellet (antibody) in small volume

(100 µL) of PBS (or TBS) at final concentration of 1 mg/ml (100 µg/100 µl). Do not allow the pellet to dry out. This can cause loss of activity. Gently allow pellet to dissolve at least 1 hour before use. Do not vortex. Mix by finger-tapping or gentle stirring.

#### Notes:

- Reconstituted antibody may be stored at 2 to 8 °C for up to one month. Addition of a preservative (15 mM sodium azide) may be necessary.
- For extended storage, add an equal volume of high purity glycerol, to a final concentration of 50% and BSA to a final concentration of 1% and store at –20 °C.
- During shipment, small volumes will occasionally become entrapped in the seal of the product vial. We recommend briefly centrifuging the vial in a tabletop centrifuge to dislodge any liquid in the container's cap.

#### Storage/Stability

Store ammonium sulfate suspension at 2 to 8 °C for up to one month.

For extended storage, freeze in working aliquots.

Reconstituted and diluted antiserum should be stored in aliquots at –20 °C.

#### Product Profile

Recommended dilutions are 1:200 to 1:1,000 for immunoblotting and immunohistochemistry.

Note: In order to obtain best results and assay sensitivity in different techniques and preparations we recommend determining optimal working dilutions by titration test.

lpg 11/03

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications. Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply. Please see reverse side of the invoice or packing slip.