




Product Information

SIGMA QUALITY CONTROL TEST PROCEDURE

Enzymatic Assay of PHOSPHATASE, ACID (EC 3.1.3.2)

PRINCIPLE:



Abbreviation:

P_i = Inorganic phosphate

CONDITIONS: T = 37°C, pH = 4.8, A_{410nm}, Light path = 1 cm

METHOD: Spectrophotometric Stop Rate Determination

REAGENTS:

- A. 90 mM Citrate Buffer, pH 4.8 at 37°C
(Prepare 100 ml in deionized water using Citric Acid, Trisodium, Dihydrate, Sigma Prod. No. C-7254, or Citrate Buffer Solution, Sigma Stock No. 104-4. Adjust to pH 4.8 at 37°C with 1 M NaOH or 1 M HCl.)
- B. 15.2 mM p-Nitrophenyl Phosphate (PNPP)
(Prepare 5 ml in deionized water using Sigma 104 Phosphatase Substrate, Sigma Stock No. 104-0.)
- C. 100 mM Sodium Hydroxide Solution (NaOH)
(Prepare 50 ml in deionized water using Sodium Hydroxide, Anhydrous, Sigma Prod. No. S-5881.)
- D. Acid Phosphatase Enzyme Solution
(Immediately before use, prepare a solution containing 0.15 - 0.25 unit/ml of Phosphatase, Acid in cold deionized water.)

PROCEDURE:

Pipette (in milliliters) the following reagents into suitable containers:

	<u>Test</u>	<u>Blank</u>
Reagent A (Buffer)	0.50	0.50
Reagent B (PNPP)	0.50	0.50

**Enzymatic Assay of PHOSPHATASE, ACID
(EC 3.1.3.2)**

PROCEDURE: (continued)

Mix by inversion and equilibrate to 37°C. Then add:

	<u>Test</u>	<u>Blank</u>
Reagent D (Enzyme Solution)	0.10	-----

Immediately mix by inversion and incubate at 37°C for exactly 10 minutes. Then add:

Reagent C (NaOH)	4.00	4.00
Reagent D (Enzyme Solution)	-----	0.10

Mix by inversion and record the $A_{410\text{nm}}$ for both the Test and Blank in a suitable spectrophotometer.

CALCULATIONS:

$$\text{Units/ml enzyme} = \frac{(A_{410\text{nm}} \text{ Test} - A_{410\text{nm}} \text{ Blank})(5.1)(\text{df})}{(10)(18.3)(0.1)}$$

5.1 = Total volume (in milliliters) of solution

df = Dilution factor

10 = Time of assay (in minutes) as per the Unit Definition

18.3 = Millimolar extinction coefficient of p-Nitrophenol at 410 nm

0.1 = Volume (in milliliter) of enzyme used

$$\text{Units/mg solid} = \frac{\text{units/ml enzyme}}{\text{mg solid/ml enzyme}}$$

$$\text{Units/mg protein} = \frac{\text{units/ml enzyme}}{\text{mg protein/ml enzyme}}$$

UNIT DEFINITION:

One unit will hydrolyze 1.0 μmole of p-nitrophenyl phosphate per minute at pH 4.8 at 37°C.

FINAL ASSAY CONCENTRATION:

In a 1.10 ml reaction mix, the final concentrations are 41 mM citric acid, 6.9 mM p-nitrophenyl phosphate and 0.015 - 0.025 unit phosphatase, acid.

**Enzymatic Assay of PHOSPHATASE, ACID
(EC 3.1.3.2)**

REFERENCE:

Bergmeyer, H.U., Gawehn, K., and Grassl, M. (1974) in *Methods of Enzymatic Analysis* (Bergmeyer H.U.) Volume I, 2nd ed., 495-496, Academic Press, Inc., New York, NY

NOTES:

1. This assay is based on the cited reference.
2. Where Sigma Product or Stock numbers are specified, equivalent reagents may be substituted.

Sigma warrants that the above procedure information is currently utilized at Sigma and that Sigma products conform to the information in Sigma publications. Purchaser must determine the suitability of the information and products for its particular use. Upon purchase of Sigma products, see reverse side of invoice or packing slip for additional terms and conditions of sale.