



Product Information

pBR322 Hae III Digest

Product No. **D 9655**

Lot 114K6115

Store below 0 °C

PRODUCT SUMMARY

Suitable for use as a molecular weight marker for agarose or acrylamide gel electrophoresis.

A₂₆₀/A₂₈₀ Ratio: 1.9

Concentration: 531 µg/ml

COMMENTS

Ethidium bromide background can be reduced by destaining 30-45 minutes in 1X electrophoresis buffer.

Better resolution of the smaller bands can be achieved using a 4% agarose gel consisting of wide range/standard agarose mixture (3:1), Sigma Product No. A7431 at 60V for 3-4 hours or electrophoresis in a 10-20% acrylamide gradient gel until the tracking dye migrates to the bottom of the gel.

STORAGE BUFFER

10 mM Tris-HCl, pH 8.0

0.1 mM EDTA

SUITABILITY ASSAY

pBR322 Hae III digest was prepared for electrophoresis as follows:

0.15-0.3 µg pBR322 Hae III Digest

2 µl gel loading solution (G 2526)

(0.05% w/v bromophenol blue, 40% w/v

sucrose, 0.1 M EDTA pH 8.0)

Q.S. to 7 µl total volume with sterile distilled water or storage buffer.

SUITABILITY ASSAY (continued)

0.15 to 0.3 µg were loaded on a 10-20% acrylamide gradient gel. Gel electrophoresis was performed in 1X TBE (0.089 M Tris-borate, pH 8.3, 0.01M EDTA). The gel was run with appropriate DNA fragment size standards at 95 volts until the tracking dye migrated to the bottom of the gel. After staining 10-15 minutes in 0.6 µg/ml ethidium bromide, 17 bands (51-587 bp) were clearly resolved and the observed pattern was consistent with the expected fragment sizes.

Fragment Sizes: base pairs

587	123
540	104
504	89
458	80
434	64
267	57
234	51
213	21
192	18
184	11
124	8

7/05

Sigma brand products are sold through Sigma-Aldrich, Inc.

Sigma-Aldrich, Inc. warrants that its products conform to the information contained in this and other Sigma-Aldrich publications.

Purchaser must determine the suitability of the product(s) for their particular use. Additional terms and conditions may apply.

Please see reverse side of the invoice or packing slip.