

Product Information

Anti-Synemin (C-terminal region)

produced in rabbit, affinity isolated antibody

Product Number **SAB4200138**

Product Description

Anti-Synemin (C-terminal region) is produced in rabbit using as the immunogen a synthetic peptide corresponding to a sequence at the C-terminal of mouse synemin (GenelD 233335) conjugated to KLH. The corresponding sequence is identical in rat synemin and highly conserved (single amino acid substitution) in human synemin. The antibody is affinity-purified using the immunizing peptide immobilized on agarose.

Anti-Synemin (C-terminal region) specifically recognizes rat synemin. The antibody may be used in various immunochemical methods including immunoblotting (~170 kDa). Staining of the synemin band by immunoblotting is specifically inhibited by the synemin immunizing peptide.

Synemin (also known as desmuslin, DMN), is a unique type VI intermediate filament (IF) protein that like other IFs display a complex tissue-specific expression pattern. The human synemin gene encodes three isoforms generated by alternative splicing, α -synemin (H, 180 kDa), β -synemin (M, 150 kDa) and L-synemin (L, 41 kDa) with overlapping distribution.¹⁻³ The three isoforms share the same head and rod domains, but differ at their C-terminal. Synemin interacts with major IF proteins including desmin, vimentin, and GFAP, and is thought to play an important role in maintaining structural integrity of the cell. Synemin isoforms have been shown to be expressed in muscle and brain, in astrocytes, glia and neuronal cells as well as in the vascular system during development.³⁻⁶ β -synemin localizes to regions of high stress in human skeletal myofibers. The interaction between IFs and adhesion molecules may serve as a mechanism to regulate cell- and tissue-specific attachment of the cytoskeleton to the membrane. In astrocytoma with migratory properties, synemin has been shown to contribute to the actin cytoskeleton dynamics.⁷ In rat and human liver tissue, synemin acts as a bridging protein between IFs and focal adhesions.⁸

Reagent

Supplied as a solution in 0.01 M phosphate buffered saline, pH 7.4, containing 15 mM sodium azide.

Antibody concentration: ~1.5 mg/mL

Precautions and Disclaimer

For R&D use only. Not for drug, household, or other uses. Please consult the Safety Data Sheet for information regarding hazards and safe handling practices.

Storage/Stability

Store at -20 °C. For continuous use, store at 2-8 °C for up to one month. For extended storage, freeze in working aliquots. Repeated freezing and thawing, or storage in "frost-free" freezers, is not recommended. If slight turbidity occurs upon prolonged storage, clarify the solution by centrifugation. Working dilutions should be discarded if not used within 12 hours.

Product Profile

Immunoblotting: a working antibody concentration of 1.5-3.0 μ g/mL is recommended using rat bladder extract (S1 fraction).

Note: In order to obtain best results in various techniques and preparations, it is recommended to determine optimal working dilutions by titration.

References

1. Mizuno, Y., et al., *Proc. Natl. Acad. Sci. USA*, **98**, 6156-6161 (2001).
2. Titeux, M., et al., *Eur. J. Biochem.*, **268**, 6435-6448 (2001).
3. Sultana, S., et al., *Glia*, **30**, 143-153 (2000).
4. Izmiryan, A., et al., *Glia*, **54**, 204-213 (2006).
5. Mizuno, Y., et al., *Muscle & Nerve*, **36**, 497-504 (2007).
6. Izmiryan, A., et al., *Exp. Cell Res.*, **10**, 769-783 (2009).
7. Pan, Y., et al., *FASEB J.*, **22**, 3196-3206 (2008).
8. Uyama, N., et al., *Gut*, **55**, 1276-1289 (2006).

VS,ER,SC,PHC,MAM 07/19-1