

93728 Atto 514 amine

Application



Atto 514 is a new hydrophilic fluorescent label with excellent water solubility. The dye exhibits strong absorption, high fluorescence quantum yield and exceptional thermal and photo-stability. Thus Atto 514 is highly suitable for single-molecule detection applications and high-resolution microscopy such as PALM, dSTORM, STED etc. Additionally the dye highly qualifies to be applied in flow cytometry (FACS), fluorescence in-situ hybridization (FISH) and many more. The fluorescence is excited most efficiently in the range 510 - 535 nm. A suitable source of excitation is the 514 nm line of the Argon-Ion laser.

The **amine** derivative may be used for reactions with activated carboxy-groups like NHS-esters, TFP-esters etc.

Product Description

MW	1024 g/mol
λ_{abs}	511 nm
ϵ_{max}	$1.15 \times 10^5 \text{ M}^{-1} \text{ cm}^{-1}$
λ_{fl}	532 nm
η_{fl}	85 %
τ_{fl}	3.9 ns
CF ₂₆₀	0.21
CF ₂₈₀	0.07

Optical data of the carboxy derivative (in aqueous solution)



Storage: protected from light at -20°C

Precautions and Disclaimer

This product is for R&D use only, not for drug, household, or other uses. Please consult the Material Safety Data Sheet for information regarding hazards and safe handling practices.

The vibrant M and Sigma-Aldrich are trademarks of Merck KGaA, Darmstadt, Germany or its affiliates.

Detailed information on trademarks is available via publicly accessible resources.

© 2018 Merck KGaA, Darmstadt, Germany and/or its affiliates. All Rights Reserved.

The life science business of Merck KGaA, Darmstadt, Germany operates as MilliporeSigma in the US and Canada.

