

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:
holo-Transferrin human - powder, BioReagent, suitable for cell culture, ≥97%

Product Number: **T0665**
CAS Number: 11096-37-0
MDL: MFCD00131337

Formula Weight: 80,000 g/mol
Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Color)	Dark Red to Very Dark Red and Dark Brown-Red to Very Dark Brown-Red
Appearance (Form)	Powder
Solubility (Color)	Faint Yellow to Orange-Red
Solubility (Turbidity)	Clear to Slightly Hazy
50 mg/mL, H ₂ O	
Water (by Karl Fischer)	≤ 8 %
Iron (Fe)	0.10 - 0.35 %
By ICP	
Protein by Biuret	≥ 90 %
Agarose Electrophoresis	≥ 97 %
Endotoxin Assay	≤ 1.0 EU/mg
Cell Culture Test	Pass
Identity	Human Origin
Tested For Infectious Agents	Tested
Recommended Retest Period	-----
4 Years	
Note	-----
Heat treated at minimum 60 deg C for minimum 10 hours	

Specification: PRD.2.ZQ5.10000011777

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

