

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Human IgM (μ -chain specific)–Alkaline Phosphatase antibody produced in goat – affinity isolated antibody, buffered aqueous glycerol solutionProduct Number: **A3275**

MDL: MFCD00162460

Storage Temperature: 2 - 8 °C

TEST	Specification
Appearance (Turbidity)	Clear to Slightly Hazy
Appearance (Color)	Colorless to Light Yellow
Appearance (Form)	Liquid
Protein Content	0.25 - 4.00 mg/ml
Conjugate concentration prior to the addition of BSA	
Direct ELISA Titer-Human IgM	\geq 7000
$< / =$ 10% Cross Reactivity by ELISA	Conforms
with 5 μ g/ml Normal Human IgG, Human IgA (κ & λ), & Bence Jones (κ & λ).	
Note: If either Human IgA κ or λ are unavailable, Normal Human IgA may be substituted.	

Specification: PRD.1.ZQ5.10000018269

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.