

3050 Spruce Street, Saint Louis, MO 63103, USA

Website: www.sigmaaldrich.comEmail USA: techserv@sial.comOutside USA: eurtechserv@sial.com

Product Specification

Product Name:

Anti-Human IgG (γ -chain specific), F(ab')₂ fragment–Peroxidase antibody produced in goat – affinity isolated antibody, buffered aqueous solutionProduct Number: **A2290**

MDL: MFCD00162447

Storage Temperature: -20 °C

TEST	Specification
------	---------------

Appearance (Turbidity)

Clear

Appearance (Color)

Colorless to Light Brown

Appearance (Form)

Liquid

Protein Content

Report Results

Conjugate concentration prior to the addition of BSA.

Direct ELISA Titer-Human IgG

10000 - 30000

Working dilution 1:10,000 - 1:30,000 versus 5 μ g/ml Normal Human IgG.

< / = 10% Cross Reactivity by ELISA

Conforms

Not more than 10% cross-reactivity at the dilution nearest to the working dilution, as determined by ELISA, when tested using 5 μ g/ml of Human IgM kappa & lambda, Human IgA kappa & lambda, and Bence Jones kappa & lambda.

Specification: PRD.2.ZQ5.10000023351

Sigma-Aldrich warrants, that at the time of the quality release or subsequent retest date this product conformed to the information contained in this publication. The current Specification sheet may be available at Sigma-Aldrich.com. For further inquiries, please contact Technical Service. Purchaser must determine the suitability of the product for its particular use. See reverse side of invoice or packing slip for additional terms and conditions of sale.

